

# Soldering Controller **OMEGA** Instruction Manual 【Ethernet Communication】-1



Thank you for purchasing the OMEGA.  
Read these instructions thoroughly for proper use of this machine.  
Make sure to read "Safety Notes" before you use machine.  
This information protects you from possible dangers during use.

**Apollo Seiko Ltd.**

## Safety Notes

---

- This manual includes the important information to use this machine safely. This also includes useful information to prevent injury or damage to property. Please read this manual carefully prior to connecting or operating the OMEGA.
- Keep this manual near the machine at all times.

### Supply only specified voltage

- Do not connect to a power supply greater than the specified voltage. If voltage is exceeded, electrical shock and /or damage to the unit may occur.
- Make sure that the electrical outlet is properly grounded. If the outlet is not properly grounded, electrical shock and/or damage to the unit may occur.

### Working ambient temperature and relative humidity

- This machine has been designed for use between 10~40 degrees C, 10%~85%.
- Do not use this machine exceeding these conditions.

### Setting temperature of the heater controller

- Do not set the temperature of the heater controller over 500 degrees C. It may cause a malfunction.

### Handle with care

- This machine is designed to use a solder feeder and hot iron for soldering. Touching a heated soldering iron will cause severe burns. Make sure the iron has cooled down before you are touching it for replacing the iron cartridge.
- Please handle this machine with care. If the machine is dropped or sustains great impact / vibration, it may cause malfunction.

### If you do not use the machine for a long time

- Please turn off the power, remove the power cable and keep it in a dry and cool place.

### If you note malfunction on machine

- If the machine malfunctions, turn off the power immediately and contact the dealer you purchased the machine from.

### The warranty period

- The warranty period is one year after the product is delivered.  
If an unexpected malfunction which our company bears responsibility occurs within
- the warranty period, we repair it in free of charge.

### Immunity from responsibility

- We do not take any responsibility for damage caused by misuse, mistakes, accidents, use in abnormal conditions or natural disasters, such as in an earthquake, a fire etc.
- We do not take any responsibility on contingency loss, (Business loss, Business stop, Overtime, Scrap or Reduced Output) caused by a machine stoppage or any issues with Apollo Seiko spare & consumable parts.
- We do not take any responsibility for losses or damages caused by operating with other means not mentioned in this manual.
- We do not take any responsibility for losses or damages caused by a wrong connection with other equipment.
- If for any reason the internal circuitry is tampered with altered or repaired without written consent of Apollo Seiko, the warranty is null and void. The customer is allowed to make necessary tooling adjustments, replace solder iron tips and make any necessary adjustments to the temperature controller.

## INDEX

---

|  |   |
|--|---|
| Safety Notes .....                             | 2 |
| INDEX.....                                     | 3 |
| 1. Communication .....                         | 4 |
| 1.1 Ethernet Communication Specification ..... | 4 |
| 1.2 Communication Procedure .....              | 4 |
| 1.3 Network Frame Configuration.....           | 4 |
| 1.4 MBAP Header Configuration .....            | 5 |
| 1.5 PUD Configuration.....                     | 5 |
| 1.6 Identifier (Code) List .....               | 8 |

## 1. Communication


---

### 1.1 Ethernet Communication Specification

OMEGA controller and the host computer can communicate each other by an Ethernet connection.

The communication uses TCP/IP protocol and reads / writes the data by MODBUS/TCP.


### 1.2 Communication Procedure



When there is not any command (request) from the host computer for more than 60 sec. after connected, the connection is disconnected.

### 1.3 Network Frame Configuration

The frame configuration of MODBUS/TCP is as following:



MBAP Header (MODBUS Application Protocol Header) :  
Header to recognize that it is MODBUS/TCP Protocol

PDU (Simple Protocol Unit): The main unit of the data communication

## 1.4 MBAP Header Configuration

MBAP Header (MODBUS Application Protocol Header) is constituted of the following 7 bytes.

|    |                |       |     |
|----|----------------|-------|-----|
| a) | Transaction ID | Upper | 00H |
|    |                | Lower | 01H |
| b) | Protocol ID    | Upper | 00H |
|    |                | Lower | 00H |
| c) | Field Length   | Upper | 00H |
|    |                | Lower | 06H |
| d) | Unit ID        |       | 01H |

## 1.5 PUD Configuration

### 1.5.1 The Configuration of the Read Request Message

|    |                            |       |     |                            |
|----|----------------------------|-------|-----|----------------------------|
| e) | Function Code              |       | 03H |                            |
| f) | Register Address           | Upper | 01H | The first register address |
|    |                            | Lower | 00H |                            |
| g) | The Number of the Register | Upper | 00H |                            |
|    |                            | Lower | 02H |                            |

### 1.5.2 The Configuration of the Write Request Message

|    |  |       |     |                                   |
|----|--|-------|-----|-----------------------------------|
| e) | Function Code                                  |       | 10H |                                   |
| f) | Register Address                               | Upper | 01H | The first register address        |
|    |  | Lower | 00H |                                   |
| g) | The Number of the Register                     | Upper | 00H |                                   |
|    |  | Lower | 02H |                                   |
| h) | The Number of Bytes                            |       | 04H | The number of the register×2      |
| i) | Data to the First Register<br>(The lower word) | Upper | 00H | ③                                 |
|    |  | Lower | 00H | ④ The data constitution is ①②③④H. |
|    | Data to the First Register<br>(The upper word) | Upper | 00H | ① (① expresses 1 byte)            |
|    |  | Lower | 00H | ②                                 |

### 1.5.3 The Configuration of the Response Message to the Read Request

|    |  |       |     |                                   |
|----|--|-------|-----|-----------------------------------|
| e) | Function Code                                  |       | 03H |                                   |
| h) | The Number of Bytes                            |       | 04H | The number of the register×2      |
| i) | Data to the First Register<br>(The lower word) | Upper | 0AH | ③                                 |
|    |  | Lower | A1H | ④ The data constitution is ①②③④H. |
|    | Data to the First Register<br>(The upper word) | Upper | 00H | ① (① expresses 1 byte)            |
|    |  | Lower | 00H | ②                                 |

#### 1.5.4 The Configuration of the Response Message to the Write Request

|    |                            |       |                            |     |
|----|----------------------------|-------|----------------------------|-----|
| e) | Function Code              | 10H   | The first register address |     |
| f) | Register Address           | Upper |                            | 01H |
|    |                            | Lower |                            | 00H |
| g) | The Number of the Register | Upper |                            | 00H |
|    |                            | Lower | 02H                        |     |

#### 1.5.5 The Configuration of the Response Message When an Error Occurs

|    |               |     |
|----|---------------|-----|
| e) | Function Code | 83H |
| j) | Error Code    | 03H |

The value of Request Function Code +80H is entered to the Function Code.

#### 1.5.6 Code Explanation

- a) Transaction ID  
It specifies any number which identifies the transaction in a host computer. OMEGA controller returns the value which received from the host computer as a response.
- b) Protocol ID  
In the case of Modbus/TCP Protocol, it specifies "0".
- c) Field Length  
It specifies the number of Byte after Unit ID.
- d) Unit ID  
It is the address of the object which the host computer communicates with (OMEGA controller).  
It is the slave address in Modbus RTU.
- e) Function Code  
Enter the code of 03H or 10H.  
03H: When it reads the data from the OMEGA controller  
10H: When it writes the data to the OMEGA controller
- f) Register Address  
It specifies the position of the reading data or the writing data by 2 bytes.
- g) The Number of the Register  
It specifies the number of the register which reading / writing.  
When writing, because of the numbers of the register is fixed to 2, specify 0002H.  
When reading, it is possible to specify the numbers of the register to a maximum of 64(0040H).
- h) The Number of Byte  
It specifies "the numbers of the register which reads and writes" ×2.
- i) Data Part  
It specifies the data which is written to the register. The data is fixed to 4 bytes.  
It writes the data which omitted the decimal point.

## j) Error Code

If there is an error in the message from the host computer, it is incorporated in "Response Message" from the OMEGA controller and returns.

If there are a multiplex error, the error number which has a higher number is incorporated.

The details of the errors are as following table.

| Error Number | Error Details   |
|--------------|---|
| 01           | It received an unsupported function code.   |
| 02           | It specified an unsupported Modbus address.   |
| 03           | The value data is not within "the setting range which is specified individually by the setting item". |
| 04           | The number of the register is specifying an address which is not in the identification code list.     |
| 05           | It received a writing message during automatic operation.   |

## 1.6 Identifier (Code) List

| No. | Address |        | Name                        | Reading / Writing | Remarks        |
|-----|---------|--------|-----------------------------|-------------------|----------------|
|     | DEC     | HEX    |                             |                   |                |
| 1   | 40001   | 0x0000 | PV Value                    | R                 |                |
| 2   | 40003   | 0x0002 | SV Value                    | R                 |                |
| 3   | 40005   | 0x0004 | Set WK No.                  | R                 |                |
| 4   | 40007   | 0x0006 |                             |                   |                |
| 5   | 40009   | 0x0008 |                             |                   |                |
| 6   | 40011   | 0x000A |                             |                   |                |
| 7   | 40013   | 0x000C | SCREEN SAVER                | R                 | Same as 0x0168 |
| 8   | 40015   | 0x000E | Input Information Monitor 1 | R                 |                |
| 9   | 40017   | 0x0010 | Input Information Monitor 2 | R                 |                |
| 10  | 40019   | 0x0012 | Output Information Monitor  | R                 |                |
| 11  | 40021   | 0x0014 | Error Information Monitor   | R                 |                |
| 12  | 40023   | 0x0016 | State Monitor               | R                 |                |
| 13  | 40025   | 0x0018 |                             |                   |                |
| 14  | 40027   | 0x001A |                             |                   |                |
| 15  | 40029   | 0x001C |                             |                   |                |
| 16  | 40031   | 0x001E |                             |                   |                |
| 17  | 40257   | 0x0100 | Alarm Hi                    | R/W               |                |
| 18  | 40259   | 0x0102 | Alarm Lo                    | R/W               |                |
| 19  | 40261   | 0x0104 | Temp                        | R/W               |                |
| 20  | 40263   | 0x0106 | SV2 Temp Enable             | R/W               |                |
| 21  | 40265   | 0x0108 | SV2 Temp                    | R/W               |                |
| 22  | 40267   | 0x010A | Wait Temp                   | R/W               |                |
| 23  | 40269   | 0x010C | Feed                        | R/W               |                |
| 24  | 40271   | 0x010E | Heat                        | R/W               |                |
| 25  | 40273   | 0x0110 | Iron U / D                  | R/W               |                |
| 26  | 40275   | 0x0112 | U / D Time                  | R/W               |                |
| 27  | 40277   | 0x0114 | Heat Auto                   | R/W               |                |
| 28  | 40279   | 0x0116 | Temp Lim                    | R/W               |                |
| 29  | 40281   | 0x0118 | Ms-Speed                    | R/W               |                |
| 30  | 40283   | 0x011A | Feed Cal                    | R/W               |                |
| 31  | 40285   | 0x011C | TIP                         | R/W               |                |
| 32  | 40287   | 0x011E | PVF1                        | R/W               |                |
| 33  | 40289   | 0x0120 | T1P                         | R/W               |                |
| 34  | 40291   | 0x0122 | T1I                         | R/W               |                |
| 35  | 40293   | 0x0124 | T1D                         | R/W               |                |
| 36  | 40295   | 0x0126 | T1Z                         | R/W               |                |
| 37  | 40297   | 0x0128 | T1G                         | R/W               |                |
| 38  | 40299   | 0x012A | T1PX1                       | R/W               |                |
| 39  | 40301   | 0x012C | T1PX2                       | R/W               |                |
| 40  | 40303   | 0x012E | T1PY1                       | R/W               |                |
| 41  | 40305   | 0x0130 | T1PY2                       | R/W               |                |
| 42  | 40307   | 0x0132 | T2P                         | R/W               |                |
| 43  | 40309   | 0x0134 | T2I                         | R/W               |                |
| 44  | 40311   | 0x0136 | T2D                         | R/W               |                |
| 45  | 40313   | 0x0138 | T2Z                         | R/W               |                |
| 46  | 40315   | 0x013A | T2G                         | R/W               |                |
| 47  | 40317   | 0x013C | T2PX1                       | R/W               |                |
| 48  | 40319   | 0x013E | T2PX2                       | R/W               |                |
| 49  | 40321   | 0x0140 | T2PY1                       | R/W               |                |



| No. | Address |        | Name                     | Reading / Writing | Remarks |
|-----|---------|--------|--------------------------|-------------------|---------|
|     | DEC     | HEX    |                          |                   |         |
| 50  | 40323   | 0x0142 | T2PY2                    | R/W               |         |
| 51  | 40325   | 0x0144 | Wait Time                | R/W               |         |
| 52  | 40327   | 0x0146 | Password Enable          | R/W               |         |
| 53  | 40329   | 0x0148 | Password Number          | R/W               |         |
| 54  | 40331   | 0x014A | Type                     | R/W               |         |
| 55  | 40333   | 0x014C | TEMP RISE DEVIATION      | R/W               |         |
| 56  | 40335   | 0x014E | TEMP RISE SENS           | R/W               |         |
| 57  | 40337   | 0x0150 | TEMP GOOD DEVIATION H    | R/W               |         |
| 58  | 40339   | 0x0152 | TEMP GOOD DEVIATION L    | R/W               |         |
| 59  | 40341   | 0x0154 | TEMP GOOD SENS           | R/W               |         |
| 60  | 40343   | 0x0156 | PID TYPE                 | R/W               |         |
| 61  | 40345   | 0x0158 | TYPE B MODE              | R/W               |         |
| 62  | 40347   | 0x015A | CTRL P CYCLE             | R/W               |         |
| 63  | 40349   | 0x015C | ARW                      | R/W               |         |
| 64  | 40351   | 0x015E | LOOP ERR PV              | R/W               |         |
| 65  | 40353   | 0x0160 | LOOP ERR CTRL            | R/W               |         |
| 66  | 40355   | 0x0162 | LOOP ERR PV CHANGE       | R/W               |         |
| 67  | 40357   | 0x0164 | LOOP ERR TIME            | R/W               |         |
| 68  | 40359   | 0x0166 | FILTER TIME              | R/W               |         |
| 69  | 40361   | 0x0168 | SCREEN SAVER             | R/W               |         |
| 70  | 40363   | 0x016A |                          |                   |         |
| 71  | 40365   | 0x016C |                          |                   |         |
| 72  | 40367   | 0x016E |                          |                   |         |
| 73  |         |        |                          |                   |         |
| 74  | 40385   | 0x0180 | MAC Address 1            | R                 |         |
| 75  | 40387   | 0x0182 | MAC Address 2            | R                 |         |
| 76  | 40389   | 0x0184 | MAC Address 3            | R                 |         |
| 77  | 40391   | 0x0186 | IP ADDRESS1              | R/W               |         |
| 78  | 40393   | 0x0188 | IP ADDRESS2              | R/W               |         |
| 79  | 40395   | 0x018A | SUBNET MASK1             | R/W               |         |
| 80  | 40397   | 0x018C | SUBNET MASK2             | R/W               |         |
| 81  | 40399   | 0x018E | DEFAULT GATEWAY1         | R/W               |         |
| 82  | 40401   | 0x0190 | DEFAULT GATEWAY2         | R/W               |         |
| 83  | 40403   | 0x0192 | PORT NUMBER              | R/W               |         |
| 84  |         |        |                          |                   |         |
| 85  | 44081   | 0x0FF0 | Iron Up / Down           | WK000             | R/W     |
| 86  | 44083   | 0x0FF2 | Air Blow Time            | WK000             | R/W     |
| 87  | 44085   | 0x0FF4 | Wait Time after Air Blow | WK000             | R/W     |
| 88  | 44087   | 0x0FF6 |                          |                   |         |
| 89  | 44089   | 0x0FF8 |                          |                   |         |
| 90  | 44091   | 0x0FFA |                          |                   |         |
| 91  | 44093   | 0x0FFC |                          |                   |         |
| 92  | 44095   | 0x0FFE |                          |                   |         |
| 93  | 44097   | 0x1000 | SV2 Time                 | WK101             | R/W     |
| 94  | 44099   | 0x1002 | 1st Amount               | WK101             | R/W     |
| 95  | 44101   | 0x1004 | 1st Speed                | WK101             | R/W     |
| 96  | 44103   | 0x1006 | 1st Rev Amount           | WK101             | R/W     |
| 97  | 44105   | 0x1008 | 1st Rev Speed            | WK101             | R/W     |
| 98  | 44107   | 0x100A | 2nd Amount               | WK101             | R/W     |
| 99  | 44109   | 0x100C | 2nd Speed                | WK101             | R/W     |
| 100 | 44111   | 0x100E | 2nd Rev Amount           | WK101             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 101 | 44113   | 0x1010 | 2nd Rev Speed  | WK101             | R/W     |
| 102 | 44115   | 0x1012 | Reserve        | WK101             | R/W     |
| 103 | 44117   | 0x1014 | Reserve        | WK101             | R/W     |
| 104 | 44119   | 0x1016 | Reserve        | WK101             | R/W     |
| 105 | 44121   | 0x1018 | Reserve        | WK101             | R/W     |
| 106 | 44123   | 0x101A | Pre-heat Time  | WK101             | R/W     |
| 107 | 44125   | 0x101C | Heating Time   | WK101             | R/W     |
| 108 | 44127   | 0x101E | Reserve        | WK101             | R/W     |
| 109 | 44129   | 0x1020 | Reserve        | WK101             | R/W     |
| 110 | 44131   | 0x1022 | SV2 Time       | WK102             | R/W     |
| 111 | 44133   | 0x1024 | 1st Amount     | WK102             | R/W     |
| 112 | 44135   | 0x1026 | 1st Speed      | WK102             | R/W     |
| 113 | 44137   | 0x1028 | 1st Rev Amount | WK102             | R/W     |
| 114 | 44139   | 0x102A | 1st Rev Speed  | WK102             | R/W     |
| 115 | 44141   | 0x102C | 2nd Amount     | WK102             | R/W     |
| 116 | 44143   | 0x102E | 2nd Speed      | WK102             | R/W     |
| 117 | 44145   | 0x1030 | 2nd Rev Amount | WK102             | R/W     |
| 118 | 44147   | 0x1032 | 2nd Rev Speed  | WK102             | R/W     |
| 119 | 44149   | 0x1034 | Reserve        | WK102             | R/W     |
| 120 | 44151   | 0x1036 | Reserve        | WK102             | R/W     |
| 121 | 44153   | 0x1038 | Reserve        | WK102             | R/W     |
| 122 | 44155   | 0x103A | Reserve        | WK102             | R/W     |
| 123 | 44157   | 0x103C | Pre-heat Time  | WK102             | R/W     |
| 124 | 44159   | 0x103E | Heating Time   | WK102             | R/W     |
| 125 | 44161   | 0x1040 | Reserve        | WK102             | R/W     |
| 126 | 44163   | 0x1042 | Reserve        | WK102             | R/W     |
| 127 | 44165   | 0x1044 | SV2 Time       | WK103             | R/W     |
| 128 | 44167   | 0x1046 | 1st Amount     | WK103             | R/W     |
| 129 | 44169   | 0x1048 | 1st Speed      | WK103             | R/W     |
| 130 | 44171   | 0x104A | 1st Rev Amount | WK103             | R/W     |
| 131 | 44173   | 0x104C | 1st Rev Speed  | WK103             | R/W     |
| 132 | 44175   | 0x104E | 2nd Amount     | WK103             | R/W     |
| 133 | 44177   | 0x1050 | 2nd Speed      | WK103             | R/W     |
| 134 | 44179   | 0x1052 | 2nd Rev Amount | WK103             | R/W     |
| 135 | 44181   | 0x1054 | 2nd Rev Speed  | WK103             | R/W     |
| 136 | 44183   | 0x1056 | Reserve        | WK103             | R/W     |
| 137 | 44185   | 0x1058 | Reserve        | WK103             | R/W     |
| 138 | 44187   | 0x105A | Reserve        | WK103             | R/W     |
| 139 | 44189   | 0x105C | Reserve        | WK103             | R/W     |
| 140 | 44191   | 0x105E | Pre-heat Time  | WK103             | R/W     |
| 141 | 44193   | 0x1060 | Heating Time   | WK103             | R/W     |
| 142 | 44195   | 0x1062 | Reserve        | WK103             | R/W     |
| 143 | 44197   | 0x1064 | Reserve        | WK103             | R/W     |
| 144 | 44199   | 0x1066 | SV2 Time       | WK104             | R/W     |
| 145 | 44201   | 0x1068 | 1st Amount     | WK104             | R/W     |
| 146 | 44203   | 0x106A | 1st Speed      | WK104             | R/W     |
| 147 | 44205   | 0x106C | 1st Rev Amount | WK104             | R/W     |
| 148 | 44207   | 0x106E | 1st Rev Speed  | WK104             | R/W     |
| 149 | 44209   | 0x1070 | 2nd Amount     | WK104             | R/W     |
| 150 | 44211   | 0x1072 | 2nd Speed      | WK104             | R/W     |
| 151 | 44213   | 0x1074 | 2nd Rev Amount | WK104             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 152 | 44215   | 0x1076 | 2nd Rev Speed  | WK104             | R/W     |
| 153 | 44217   | 0x1078 | Reserve        | WK104             | R/W     |
| 154 | 44219   | 0x107A | Reserve        | WK104             | R/W     |
| 155 | 44221   | 0x107C | Reserve        | WK104             | R/W     |
| 156 | 44223   | 0x107E | Reserve        | WK104             | R/W     |
| 157 | 44225   | 0x1080 | Pre-heat Time  | WK104             | R/W     |
| 158 | 44227   | 0x1082 | Heating Time   | WK104             | R/W     |
| 159 | 44229   | 0x1084 | Reserve        | WK104             | R/W     |
| 160 | 44231   | 0x1086 | Reserve        | WK104             | R/W     |
| 161 | 44233   | 0x1088 | SV2 Time       | WK105             | R/W     |
| 162 | 44235   | 0x108A | 1st Amount     | WK105             | R/W     |
| 163 | 44237   | 0x108C | 1st Speed      | WK105             | R/W     |
| 164 | 44239   | 0x108E | 1st Rev Amount | WK105             | R/W     |
| 165 | 44241   | 0x1090 | 1st Rev Speed  | WK105             | R/W     |
| 166 | 44243   | 0x1092 | 2nd Amount     | WK105             | R/W     |
| 167 | 44245   | 0x1094 | 2nd Speed      | WK105             | R/W     |
| 168 | 44247   | 0x1096 | 2nd Rev Amount | WK105             | R/W     |
| 169 | 44249   | 0x1098 | 2nd Rev Speed  | WK105             | R/W     |
| 170 | 44251   | 0x109A | Reserve        | WK105             | R/W     |
| 171 | 44253   | 0x109C | Reserve        | WK105             | R/W     |
| 172 | 44255   | 0x109E | Reserve        | WK105             | R/W     |
| 173 | 44257   | 0x10A0 | Reserve        | WK105             | R/W     |
| 174 | 44259   | 0x10A2 | Pre-heat Time  | WK105             | R/W     |
| 175 | 44261   | 0x10A4 | Heating Time   | WK105             | R/W     |
| 176 | 44263   | 0x10A6 | Reserve        | WK105             | R/W     |
| 177 | 44265   | 0x10A8 | Reserve        | WK105             | R/W     |
| 178 | 44267   | 0x10AA | SV2 Time       | WK106             | R/W     |
| 179 | 44269   | 0x10AC | 1st Amount     | WK106             | R/W     |
| 180 | 44271   | 0x10AE | 1st Speed      | WK106             | R/W     |
| 181 | 44273   | 0x10B0 | 1st Rev Amount | WK106             | R/W     |
| 182 | 44275   | 0x10B2 | 1st Rev Speed  | WK106             | R/W     |
| 183 | 44277   | 0x10B4 | 2nd Amount     | WK106             | R/W     |
| 184 | 44279   | 0x10B6 | 2nd Speed      | WK106             | R/W     |
| 185 | 44281   | 0x10B8 | 2nd Rev Amount | WK106             | R/W     |
| 186 | 44283   | 0x10BA | 2nd Rev Speed  | WK106             | R/W     |
| 187 | 44285   | 0x10BC | Reserve        | WK106             | R/W     |
| 188 | 44287   | 0x10BE | Reserve        | WK106             | R/W     |
| 189 | 44289   | 0x10C0 | Reserve        | WK106             | R/W     |
| 190 | 44291   | 0x10C2 | Reserve        | WK106             | R/W     |
| 191 | 44293   | 0x10C4 | Pre-heat Time  | WK106             | R/W     |
| 192 | 44295   | 0x10C6 | Heating Time   | WK106             | R/W     |
| 193 | 44297   | 0x10C8 | Reserve        | WK106             | R/W     |
| 194 | 44299   | 0x10CA | Reserve        | WK106             | R/W     |
| 195 | 44301   | 0x10CC | SV2 Time       | WK107             | R/W     |
| 196 | 44303   | 0x10CE | 1st Amount     | WK107             | R/W     |
| 197 | 44305   | 0x10D0 | 1st Speed      | WK107             | R/W     |
| 198 | 44307   | 0x10D2 | 1st Rev Amount | WK107             | R/W     |
| 199 | 44309   | 0x10D4 | 1st Rev Speed  | WK107             | R/W     |
| 200 | 44311   | 0x10D6 | 2nd Amount     | WK107             | R/W     |
| 201 | 44313   | 0x10D8 | 2nd Speed      | WK107             | R/W     |
| 202 | 44315   | 0x10DA | 2nd Rev Amount | WK107             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 203 | 44317   | 0x10DC | 2nd Rev Speed  | WK107             | R/W     |
| 204 | 44319   | 0x10DE | Reserve        | WK107             | R/W     |
| 205 | 44321   | 0x10E0 | Reserve        | WK107             | R/W     |
| 206 | 44323   | 0x10E2 | Reserve        | WK107             | R/W     |
| 207 | 44325   | 0x10E4 | Reserve        | WK107             | R/W     |
| 208 | 44327   | 0x10E6 | Pre-heat Time  | WK107             | R/W     |
| 209 | 44329   | 0x10E8 | Heating Time   | WK107             | R/W     |
| 210 | 44331   | 0x10EA | Reserve        | WK107             | R/W     |
| 211 | 44333   | 0x10EC | Reserve        | WK107             | R/W     |
| 212 | 44335   | 0x10EE | SV2 Time       | WK108             | R/W     |
| 213 | 44337   | 0x10F0 | 1st Amount     | WK108             | R/W     |
| 214 | 44339   | 0x10F2 | 1st Speed      | WK108             | R/W     |
| 215 | 44341   | 0x10F4 | 1st Rev Amount | WK108             | R/W     |
| 216 | 44343   | 0x10F6 | 1st Rev Speed  | WK108             | R/W     |
| 217 | 44345   | 0x10F8 | 2nd Amount     | WK108             | R/W     |
| 218 | 44347   | 0x10FA | 2nd Speed      | WK108             | R/W     |
| 219 | 44349   | 0x10FC | 2nd Rev Amount | WK108             | R/W     |
| 220 | 44351   | 0x10FE | 2nd Rev Speed  | WK108             | R/W     |
| 221 | 44353   | 0x1100 | Reserve        | WK108             | R/W     |
| 222 | 44355   | 0x1102 | Reserve        | WK108             | R/W     |
| 223 | 44357   | 0x1104 | Reserve        | WK108             | R/W     |
| 224 | 44359   | 0x1106 | Reserve        | WK108             | R/W     |
| 225 | 44361   | 0x1108 | Pre-heat Time  | WK108             | R/W     |
| 226 | 44363   | 0x110A | Heating Time   | WK108             | R/W     |
| 227 | 44365   | 0x110C | Reserve        | WK108             | R/W     |
| 228 | 44367   | 0x110E | Reserve        | WK108             | R/W     |
| 229 | 44369   | 0x1110 | SV2 Time       | WK109             | R/W     |
| 230 | 44371   | 0x1112 | 1st Amount     | WK109             | R/W     |
| 231 | 44373   | 0x1114 | 1st Speed      | WK109             | R/W     |
| 232 | 44375   | 0x1116 | 1st Rev Amount | WK109             | R/W     |
| 233 | 44377   | 0x1118 | 1st Rev Speed  | WK109             | R/W     |
| 234 | 44379   | 0x111A | 2nd Amount     | WK109             | R/W     |
| 235 | 44381   | 0x111C | 2nd Speed      | WK109             | R/W     |
| 236 | 44383   | 0x111E | 2nd Rev Amount | WK109             | R/W     |
| 237 | 44385   | 0x1120 | 2nd Rev Speed  | WK109             | R/W     |
| 238 | 44387   | 0x1122 | Reserve        | WK109             | R/W     |
| 239 | 44389   | 0x1124 | Reserve        | WK109             | R/W     |
| 240 | 44391   | 0x1126 | Reserve        | WK109             | R/W     |
| 241 | 44393   | 0x1128 | Reserve        | WK109             | R/W     |
| 242 | 44395   | 0x112A | Pre-heat Time  | WK109             | R/W     |
| 243 | 44397   | 0x112C | Heating Time   | WK109             | R/W     |
| 244 | 44399   | 0x112E | Reserve        | WK109             | R/W     |
| 245 | 44401   | 0x1130 | Reserve        | WK109             | R/W     |
| 246 | 44403   | 0x1132 | SV2 Time       | WK110             | R/W     |
| 247 | 44405   | 0x1134 | 1st Amount     | WK110             | R/W     |
| 248 | 44407   | 0x1136 | 1st Speed      | WK110             | R/W     |
| 249 | 44409   | 0x1138 | 1st Rev Amount | WK110             | R/W     |
| 250 | 44411   | 0x113A | 1st Rev Speed  | WK110             | R/W     |
| 251 | 44413   | 0x113C | 2nd Amount     | WK110             | R/W     |
| 252 | 44415   | 0x113E | 2nd Speed      | WK110             | R/W     |
| 253 | 44417   | 0x1140 | 2nd Rev Amount | WK110             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 254 | 44419   | 0x1142 | 2nd Rev Speed  | WK110             | R/W     |
| 255 | 44421   | 0x1144 | Reserve        | WK110             | R/W     |
| 256 | 44423   | 0x1146 | Reserve        | WK110             | R/W     |
| 257 | 44425   | 0x1148 | Reserve        | WK110             | R/W     |
| 258 | 44427   | 0x114A | Reserve        | WK110             | R/W     |
| 259 | 44429   | 0x114C | Pre-heat Time  | WK110             | R/W     |
| 260 | 44431   | 0x114E | Heating Time   | WK110             | R/W     |
| 261 | 44433   | 0x1150 | Reserve        | WK110             | R/W     |
| 262 | 44435   | 0x1152 | Reserve        | WK110             | R/W     |
| 263 | 44437   | 0x1154 | SV2 Time       | WK111             | R/W     |
| 264 | 44439   | 0x1156 | 1st Amount     | WK111             | R/W     |
| 265 | 44441   | 0x1158 | 1st Speed      | WK111             | R/W     |
| 266 | 44443   | 0x115A | 1st Rev Amount | WK111             | R/W     |
| 267 | 44445   | 0x115C | 1st Rev Speed  | WK111             | R/W     |
| 268 | 44447   | 0x115E | 2nd Amount     | WK111             | R/W     |
| 269 | 44449   | 0x1160 | 2nd Speed      | WK111             | R/W     |
| 270 | 44451   | 0x1162 | 2nd Rev Amount | WK111             | R/W     |
| 271 | 44453   | 0x1164 | 2nd Rev Speed  | WK111             | R/W     |
| 272 | 44455   | 0x1166 | Reserve        | WK111             | R/W     |
| 273 | 44457   | 0x1168 | Reserve        | WK111             | R/W     |
| 274 | 44459   | 0x116A | Reserve        | WK111             | R/W     |
| 275 | 44461   | 0x116C | Reserve        | WK111             | R/W     |
| 276 | 44463   | 0x116E | Pre-heat Time  | WK111             | R/W     |
| 277 | 44465   | 0x1170 | Heating Time   | WK111             | R/W     |
| 278 | 44467   | 0x1172 | Reserve        | WK111             | R/W     |
| 279 | 44469   | 0x1174 | Reserve        | WK111             | R/W     |
| 280 | 44471   | 0x1176 | SV2 Time       | WK112             | R/W     |
| 281 | 44473   | 0x1178 | 1st Amount     | WK112             | R/W     |
| 282 | 44475   | 0x117A | 1st Speed      | WK112             | R/W     |
| 283 | 44477   | 0x117C | 1st Rev Amount | WK112             | R/W     |
| 284 | 44479   | 0x117E | 1st Rev Speed  | WK112             | R/W     |
| 285 | 44481   | 0x1180 | 2nd Amount     | WK112             | R/W     |
| 286 | 44483   | 0x1182 | 2nd Speed      | WK112             | R/W     |
| 287 | 44485   | 0x1184 | 2nd Rev Amount | WK112             | R/W     |
| 288 | 44487   | 0x1186 | 2nd Rev Speed  | WK112             | R/W     |
| 289 | 44489   | 0x1188 | Reserve        | WK112             | R/W     |
| 290 | 44491   | 0x118A | Reserve        | WK112             | R/W     |
| 291 | 44493   | 0x118C | Reserve        | WK112             | R/W     |
| 292 | 44495   | 0x118E | Reserve        | WK112             | R/W     |
| 293 | 44497   | 0x1190 | Pre-heat Time  | WK112             | R/W     |
| 294 | 44499   | 0x1192 | Heating Time   | WK112             | R/W     |
| 295 | 44501   | 0x1194 | Reserve        | WK112             | R/W     |
| 296 | 44503   | 0x1196 | Reserve        | WK112             | R/W     |
| 297 | 44505   | 0x1198 | SV2 Time       | WK113             | R/W     |
| 298 | 44507   | 0x119A | 1st Amount     | WK113             | R/W     |
| 299 | 44509   | 0x119C | 1st Speed      | WK113             | R/W     |
| 300 | 44511   | 0x119E | 1st Rev Amount | WK113             | R/W     |
| 301 | 44513   | 0x11A0 | 1st Rev Speed  | WK113             | R/W     |
| 302 | 44515   | 0x11A2 | 2nd Amount     | WK113             | R/W     |
| 303 | 44517   | 0x11A4 | 2nd Speed      | WK113             | R/W     |
| 304 | 44519   | 0x11A6 | 2nd Rev Amount | WK113             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 305 | 44521   | 0x11A8 | 2nd Rev Speed  | WK113             | R/W     |
| 306 | 44523   | 0x11AA | Reserve        | WK113             | R/W     |
| 307 | 44525   | 0x11AC | Reserve        | WK113             | R/W     |
| 308 | 44527   | 0x11AE | Reserve        | WK113             | R/W     |
| 309 | 44529   | 0x11B0 | Reserve        | WK113             | R/W     |
| 310 | 44531   | 0x11B2 | Pre-heat Time  | WK113             | R/W     |
| 311 | 44533   | 0x11B4 | Heating Time   | WK113             | R/W     |
| 312 | 44535   | 0x11B6 | Reserve        | WK113             | R/W     |
| 313 | 44537   | 0x11B8 | Reserve        | WK113             | R/W     |
| 314 | 44539   | 0x11BA | SV2 Time       | WK114             | R/W     |
| 315 | 44541   | 0x11BC | 1st Amount     | WK114             | R/W     |
| 316 | 44543   | 0x11BE | 1st Speed      | WK114             | R/W     |
| 317 | 44545   | 0x11C0 | 1st Rev Amount | WK114             | R/W     |
| 318 | 44547   | 0x11C2 | 1st Rev Speed  | WK114             | R/W     |
| 319 | 44549   | 0x11C4 | 2nd Amount     | WK114             | R/W     |
| 320 | 44551   | 0x11C6 | 2nd Speed      | WK114             | R/W     |
| 321 | 44553   | 0x11C8 | 2nd Rev Amount | WK114             | R/W     |
| 322 | 44555   | 0x11CA | 2nd Rev Speed  | WK114             | R/W     |
| 323 | 44557   | 0x11CC | Reserve        | WK114             | R/W     |
| 324 | 44559   | 0x11CE | Reserve        | WK114             | R/W     |
| 325 | 44561   | 0x11D0 | Reserve        | WK114             | R/W     |
| 326 | 44563   | 0x11D2 | Reserve        | WK114             | R/W     |
| 327 | 44565   | 0x11D4 | Pre-heat Time  | WK114             | R/W     |
| 328 | 44567   | 0x11D6 | Heating Time   | WK114             | R/W     |
| 329 | 44569   | 0x11D8 | Reserve        | WK114             | R/W     |
| 330 | 44571   | 0x11DA | Reserve        | WK114             | R/W     |
| 331 | 44573   | 0x11DC | SV2 Time       | WK115             | R/W     |
| 332 | 44575   | 0x11DE | 1st Amount     | WK115             | R/W     |
| 333 | 44577   | 0x11E0 | 1st Speed      | WK115             | R/W     |
| 334 | 44579   | 0x11E2 | 1st Rev Amount | WK115             | R/W     |
| 335 | 44581   | 0x11E4 | 1st Rev Speed  | WK115             | R/W     |
| 336 | 44583   | 0x11E6 | 2nd Amount     | WK115             | R/W     |
| 337 | 44585   | 0x11E8 | 2nd Speed      | WK115             | R/W     |
| 338 | 44587   | 0x11EA | 2nd Rev Amount | WK115             | R/W     |
| 339 | 44589   | 0x11EC | 2nd Rev Speed  | WK115             | R/W     |
| 340 | 44591   | 0x11EE | Reserve        | WK115             | R/W     |
| 341 | 44593   | 0x11F0 | Reserve        | WK115             | R/W     |
| 342 | 44595   | 0x11F2 | Reserve        | WK115             | R/W     |
| 343 | 44597   | 0x11F4 | Reserve        | WK115             | R/W     |
| 344 | 44599   | 0x11F6 | Pre-heat Time  | WK115             | R/W     |
| 345 | 44601   | 0x11F8 | Heating Time   | WK115             | R/W     |
| 346 | 44603   | 0x11FA | Reserve        | WK115             | R/W     |
| 347 | 44605   | 0x11FC | Reserve        | WK115             | R/W     |
| 348 | 44607   | 0x11FE | SV2 Time       | WK116             | R/W     |
| 349 | 44609   | 0x1200 | 1st Amount     | WK116             | R/W     |
| 350 | 44611   | 0x1202 | 1st Speed      | WK116             | R/W     |
| 351 | 44613   | 0x1204 | 1st Rev Amount | WK116             | R/W     |
| 352 | 44615   | 0x1206 | 1st Rev Speed  | WK116             | R/W     |
| 353 | 44617   | 0x1208 | 2nd Amount     | WK116             | R/W     |
| 354 | 44619   | 0x120A | 2nd Speed      | WK116             | R/W     |
| 355 | 44621   | 0x120C | 2nd Rev Amount | WK116             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 356 | 44623   | 0x120E | 2nd Rev Speed  | WK116             | R/W     |
| 357 | 44625   | 0x1210 | Reserve        | WK116             | R/W     |
| 358 | 44627   | 0x1212 | Reserve        | WK116             | R/W     |
| 359 | 44629   | 0x1214 | Reserve        | WK116             | R/W     |
| 360 | 44631   | 0x1216 | Reserve        | WK116             | R/W     |
| 361 | 44633   | 0x1218 | Pre-heat Time  | WK116             | R/W     |
| 362 | 44635   | 0x121A | Heating Time   | WK116             | R/W     |
| 363 | 44637   | 0x121C | Reserve        | WK116             | R/W     |
| 364 | 44639   | 0x121E | Reserve        | WK116             | R/W     |
| 365 | 44641   | 0x1220 | SV2 Time       | WK117             | R/W     |
| 366 | 44643   | 0x1222 | 1st Amount     | WK117             | R/W     |
| 367 | 44645   | 0x1224 | 1st Speed      | WK117             | R/W     |
| 368 | 44647   | 0x1226 | 1st Rev Amount | WK117             | R/W     |
| 369 | 44649   | 0x1228 | 1st Rev Speed  | WK117             | R/W     |
| 370 | 44651   | 0x122A | 2nd Amount     | WK117             | R/W     |
| 371 | 44653   | 0x122C | 2nd Speed      | WK117             | R/W     |
| 372 | 44655   | 0x122E | 2nd Rev Amount | WK117             | R/W     |
| 373 | 44657   | 0x1230 | 2nd Rev Speed  | WK117             | R/W     |
| 374 | 44659   | 0x1232 | Reserve        | WK117             | R/W     |
| 375 | 44661   | 0x1234 | Reserve        | WK117             | R/W     |
| 376 | 44663   | 0x1236 | Reserve        | WK117             | R/W     |
| 377 | 44665   | 0x1238 | Reserve        | WK117             | R/W     |
| 378 | 44667   | 0x123A | Pre-heat Time  | WK117             | R/W     |
| 379 | 44669   | 0x123C | Heating Time   | WK117             | R/W     |
| 380 | 44671   | 0x123E | Reserve        | WK117             | R/W     |
| 381 | 44673   | 0x1240 | Reserve        | WK117             | R/W     |
| 382 | 44675   | 0x1242 | SV2 Time       | WK118             | R/W     |
| 383 | 44677   | 0x1244 | 1st Amount     | WK118             | R/W     |
| 384 | 44679   | 0x1246 | 1st Speed      | WK118             | R/W     |
| 385 | 44681   | 0x1248 | 1st Rev Amount | WK118             | R/W     |
| 386 | 44683   | 0x124A | 1st Rev Speed  | WK118             | R/W     |
| 387 | 44685   | 0x124C | 2nd Amount     | WK118             | R/W     |
| 388 | 44687   | 0x124E | 2nd Speed      | WK118             | R/W     |
| 389 | 44689   | 0x1250 | 2nd Rev Amount | WK118             | R/W     |
| 390 | 44691   | 0x1252 | 2nd Rev Speed  | WK118             | R/W     |
| 391 | 44693   | 0x1254 | Reserve        | WK118             | R/W     |
| 392 | 44695   | 0x1256 | Reserve        | WK118             | R/W     |
| 393 | 44697   | 0x1258 | Reserve        | WK118             | R/W     |
| 394 | 44699   | 0x125A | Reserve        | WK118             | R/W     |
| 395 | 44701   | 0x125C | Pre-heat Time  | WK118             | R/W     |
| 396 | 44703   | 0x125E | Heating Time   | WK118             | R/W     |
| 397 | 44705   | 0x1260 | Reserve        | WK118             | R/W     |
| 398 | 44707   | 0x1262 | Reserve        | WK118             | R/W     |
| 399 | 44709   | 0x1264 | SV2 Time       | WK119             | R/W     |
| 400 | 44711   | 0x1266 | 1st Amount     | WK119             | R/W     |
| 401 | 44713   | 0x1268 | 1st Speed      | WK119             | R/W     |
| 402 | 44715   | 0x126A | 1st Rev Amount | WK119             | R/W     |
| 403 | 44717   | 0x126C | 1st Rev Speed  | WK119             | R/W     |
| 404 | 44719   | 0x126E | 2nd Amount     | WK119             | R/W     |
| 405 | 44721   | 0x1270 | 2nd Speed      | WK119             | R/W     |
| 406 | 44723   | 0x1272 | 2nd Rev Amount | WK119             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 407 | 44725   | 0x1274 | 2nd Rev Speed  | WK119             | R/W     |
| 408 | 44727   | 0x1276 | Reserve        | WK119             | R/W     |
| 409 | 44729   | 0x1278 | Reserve        | WK119             | R/W     |
| 410 | 44731   | 0x127A | Reserve        | WK119             | R/W     |
| 411 | 44733   | 0x127C | Reserve        | WK119             | R/W     |
| 412 | 44735   | 0x127E | Pre-heat Time  | WK119             | R/W     |
| 413 | 44737   | 0x1280 | Heating Time   | WK119             | R/W     |
| 414 | 44739   | 0x1282 | Reserve        | WK119             | R/W     |
| 415 | 44741   | 0x1284 | Reserve        | WK119             | R/W     |
| 416 | 44743   | 0x1286 | SV2 Time       | WK120             | R/W     |
| 417 | 44745   | 0x1288 | 1st Amount     | WK120             | R/W     |
| 418 | 44747   | 0x128A | 1st Speed      | WK120             | R/W     |
| 419 | 44749   | 0x128C | 1st Rev Amount | WK120             | R/W     |
| 420 | 44751   | 0x128E | 1st Rev Speed  | WK120             | R/W     |
| 421 | 44753   | 0x1290 | 2nd Amount     | WK120             | R/W     |
| 422 | 44755   | 0x1292 | 2nd Speed      | WK120             | R/W     |
| 423 | 44757   | 0x1294 | 2nd Rev Amount | WK120             | R/W     |
| 424 | 44759   | 0x1296 | 2nd Rev Speed  | WK120             | R/W     |
| 425 | 44761   | 0x1298 | Reserve        | WK120             | R/W     |
| 426 | 44763   | 0x129A | Reserve        | WK120             | R/W     |
| 427 | 44765   | 0x129C | Reserve        | WK120             | R/W     |
| 428 | 44767   | 0x129E | Reserve        | WK120             | R/W     |
| 429 | 44769   | 0x12A0 | Pre-heat Time  | WK120             | R/W     |
| 430 | 44771   | 0x12A2 | Heating Time   | WK120             | R/W     |
| 431 | 44773   | 0x12A4 | Reserve        | WK120             | R/W     |
| 432 | 44775   | 0x12A6 | Reserve        | WK120             | R/W     |
| 433 | 44777   | 0x12A8 | SV2 Time       | WK121             | R/W     |
| 434 | 44779   | 0x12AA | 1st Amount     | WK121             | R/W     |
| 435 | 44781   | 0x12AC | 1st Speed      | WK121             | R/W     |
| 436 | 44783   | 0x12AE | 1st Rev Amount | WK121             | R/W     |
| 437 | 44785   | 0x12B0 | 1st Rev Speed  | WK121             | R/W     |
| 438 | 44787   | 0x12B2 | 2nd Amount     | WK121             | R/W     |
| 439 | 44789   | 0x12B4 | 2nd Speed      | WK121             | R/W     |
| 440 | 44791   | 0x12B6 | 2nd Rev Amount | WK121             | R/W     |
| 441 | 44793   | 0x12B8 | 2nd Rev Speed  | WK121             | R/W     |
| 442 | 44795   | 0x12BA | Reserve        | WK121             | R/W     |
| 443 | 44797   | 0x12BC | Reserve        | WK121             | R/W     |
| 444 | 44799   | 0x12BE | Reserve        | WK121             | R/W     |
| 445 | 44801   | 0x12C0 | Reserve        | WK121             | R/W     |
| 446 | 44803   | 0x12C2 | Pre-heat Time  | WK121             | R/W     |
| 447 | 44805   | 0x12C4 | Heating Time   | WK121             | R/W     |
| 448 | 44807   | 0x12C6 | Reserve        | WK121             | R/W     |
| 449 | 44809   | 0x12C8 | Reserve        | WK121             | R/W     |
| 450 | 44811   | 0x12CA | SV2 Time       | WK122             | R/W     |
| 451 | 44813   | 0x12CC | 1st Amount     | WK122             | R/W     |
| 452 | 44815   | 0x12CE | 1st Speed      | WK122             | R/W     |
| 453 | 44817   | 0x12D0 | 1st Rev Amount | WK122             | R/W     |
| 454 | 44819   | 0x12D2 | 1st Rev Speed  | WK122             | R/W     |
| 455 | 44821   | 0x12D4 | 2nd Amount     | WK122             | R/W     |
| 456 | 44823   | 0x12D6 | 2nd Speed      | WK122             | R/W     |
| 457 | 44825   | 0x12D8 | 2nd Rev Amount | WK122             | R/W     |



| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 458 | 44827   | 0x12DA | 2nd Rev Speed  | WK122             | R/W     |
| 459 | 44829   | 0x12DC | Reserve        | WK122             | R/W     |
| 460 | 44831   | 0x12DE | Reserve        | WK122             | R/W     |
| 461 | 44833   | 0x12E0 | Reserve        | WK122             | R/W     |
| 462 | 44835   | 0x12E2 | Reserve        | WK122             | R/W     |
| 463 | 44837   | 0x12E4 | Pre-heat Time  | WK122             | R/W     |
| 464 | 44839   | 0x12E6 | Heating Time   | WK122             | R/W     |
| 465 | 44841   | 0x12E8 | Reserve        | WK122             | R/W     |
| 466 | 44843   | 0x12EA | Reserve        | WK122             | R/W     |
| 467 | 44845   | 0x12EC | SV2 Time       | WK123             | R/W     |
| 468 | 44847   | 0x12EE | 1st Amount     | WK123             | R/W     |
| 469 | 44849   | 0x12F0 | 1st Speed      | WK123             | R/W     |
| 470 | 44851   | 0x12F2 | 1st Rev Amount | WK123             | R/W     |
| 471 | 44853   | 0x12F4 | 1st Rev Speed  | WK123             | R/W     |
| 472 | 44855   | 0x12F6 | 2nd Amount     | WK123             | R/W     |
| 473 | 44857   | 0x12F8 | 2nd Speed      | WK123             | R/W     |
| 474 | 44859   | 0x12FA | 2nd Rev Amount | WK123             | R/W     |
| 475 | 44861   | 0x12FC | 2nd Rev Speed  | WK123             | R/W     |
| 476 | 44863   | 0x12FE | Reserve        | WK123             | R/W     |
| 477 | 44865   | 0x1300 | Reserve        | WK123             | R/W     |
| 478 | 44867   | 0x1302 | Reserve        | WK123             | R/W     |
| 479 | 44869   | 0x1304 | Reserve        | WK123             | R/W     |
| 480 | 44871   | 0x1306 | Pre-heat Time  | WK123             | R/W     |
| 481 | 44873   | 0x1308 | Heating Time   | WK123             | R/W     |
| 482 | 44875   | 0x130A | Reserve        | WK123             | R/W     |
| 483 | 44877   | 0x130C | Reserve        | WK123             | R/W     |
| 484 | 44879   | 0x130E | SV2 Time       | WK124             | R/W     |
| 485 | 44881   | 0x1310 | 1st Amount     | WK124             | R/W     |
| 486 | 44883   | 0x1312 | 1st Speed      | WK124             | R/W     |
| 487 | 44885   | 0x1314 | 1st Rev Amount | WK124             | R/W     |
| 488 | 44887   | 0x1316 | 1st Rev Speed  | WK124             | R/W     |
| 489 | 44889   | 0x1318 | 2nd Amount     | WK124             | R/W     |
| 490 | 44891   | 0x131A | 2nd Speed      | WK124             | R/W     |
| 491 | 44893   | 0x131C | 2nd Rev Amount | WK124             | R/W     |
| 492 | 44895   | 0x131E | 2nd Rev Speed  | WK124             | R/W     |
| 493 | 44897   | 0x1320 | Reserve        | WK124             | R/W     |
| 494 | 44899   | 0x1322 | Reserve        | WK124             | R/W     |
| 495 | 44901   | 0x1324 | Reserve        | WK124             | R/W     |
| 496 | 44903   | 0x1326 | Reserve        | WK124             | R/W     |
| 497 | 44905   | 0x1328 | Pre-heat Time  | WK124             | R/W     |
| 498 | 44907   | 0x132A | Heating Time   | WK124             | R/W     |
| 499 | 44909   | 0x132C | Reserve        | WK124             | R/W     |
| 500 | 44911   | 0x132E | Reserve        | WK124             | R/W     |
| 501 | 44913   | 0x1330 | SV2 Time       | WK125             | R/W     |
| 502 | 44915   | 0x1332 | 1st Amount     | WK125             | R/W     |
| 503 | 44917   | 0x1334 | 1st Speed      | WK125             | R/W     |
| 504 | 44919   | 0x1336 | 1st Rev Amount | WK125             | R/W     |
| 505 | 44921   | 0x1338 | 1st Rev Speed  | WK125             | R/W     |
| 506 | 44923   | 0x133A | 2nd Amount     | WK125             | R/W     |
| 507 | 44925   | 0x133C | 2nd Speed      | WK125             | R/W     |
| 508 | 44927   | 0x133E | 2nd Rev Amount | WK125             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 509 | 44929   | 0x1340 | 2nd Rev Speed  | WK125             | R/W     |
| 510 | 44931   | 0x1342 | Reserve        | WK125             | R/W     |
| 511 | 44933   | 0x1344 | Reserve        | WK125             | R/W     |
| 512 | 44935   | 0x1346 | Reserve        | WK125             | R/W     |
| 513 | 44937   | 0x1348 | Reserve        | WK125             | R/W     |
| 514 | 44939   | 0x134A | Pre-heat Time  | WK125             | R/W     |
| 515 | 44941   | 0x134C | Heating Time   | WK125             | R/W     |
| 516 | 44943   | 0x134E | Reserve        | WK125             | R/W     |
| 517 | 44945   | 0x1350 | Reserve        | WK125             | R/W     |
| 518 | 44947   | 0x1352 | SV2 Time       | WK126             | R/W     |
| 519 | 44949   | 0x1354 | 1st Amount     | WK126             | R/W     |
| 520 | 44951   | 0x1356 | 1st Speed      | WK126             | R/W     |
| 521 | 44953   | 0x1358 | 1st Rev Amount | WK126             | R/W     |
| 522 | 44955   | 0x135A | 1st Rev Speed  | WK126             | R/W     |
| 523 | 44957   | 0x135C | 2nd Amount     | WK126             | R/W     |
| 524 | 44959   | 0x135E | 2nd Speed      | WK126             | R/W     |
| 525 | 44961   | 0x1360 | 2nd Rev Amount | WK126             | R/W     |
| 526 | 44963   | 0x1362 | 2nd Rev Speed  | WK126             | R/W     |
| 527 | 44965   | 0x1364 | Reserve        | WK126             | R/W     |
| 528 | 44967   | 0x1366 | Reserve        | WK126             | R/W     |
| 529 | 44969   | 0x1368 | Reserve        | WK126             | R/W     |
| 530 | 44971   | 0x136A | Reserve        | WK126             | R/W     |
| 531 | 44973   | 0x136C | Pre-heat Time  | WK126             | R/W     |
| 532 | 44975   | 0x136E | Heating Time   | WK126             | R/W     |
| 533 | 44977   | 0x1370 | Reserve        | WK126             | R/W     |
| 534 | 44979   | 0x1372 | Reserve        | WK126             | R/W     |
| 535 | 44981   | 0x1374 | SV2 Time       | WK127             | R/W     |
| 536 | 44983   | 0x1376 | 1st Amount     | WK127             | R/W     |
| 537 | 44985   | 0x1378 | 1st Speed      | WK127             | R/W     |
| 538 | 44987   | 0x137A | 1st Rev Amount | WK127             | R/W     |
| 539 | 44989   | 0x137C | 1st Rev Speed  | WK127             | R/W     |
| 540 | 44991   | 0x137E | 2nd Amount     | WK127             | R/W     |
| 541 | 44993   | 0x1380 | 2nd Speed      | WK127             | R/W     |
| 542 | 44995   | 0x1382 | 2nd Rev Amount | WK127             | R/W     |
| 543 | 44997   | 0x1384 | 2nd Rev Speed  | WK127             | R/W     |
| 544 | 44999   | 0x1386 | Reserve        | WK127             | R/W     |
| 545 | 45001   | 0x1388 | Reserve        | WK127             | R/W     |
| 546 | 45003   | 0x138A | Reserve        | WK127             | R/W     |
| 547 | 45005   | 0x138C | Reserve        | WK127             | R/W     |
| 548 | 45007   | 0x138E | Pre-heat Time  | WK127             | R/W     |
| 549 | 45009   | 0x1390 | Heating Time   | WK127             | R/W     |
| 550 | 45011   | 0x1392 | Reserve        | WK127             | R/W     |
| 551 | 45013   | 0x1394 | Reserve        | WK127             | R/W     |
| 552 | 45015   | 0x1396 | SV2 Time       | WK128             | R/W     |
| 553 | 45017   | 0x1398 | 1st Amount     | WK128             | R/W     |
| 554 | 45019   | 0x139A | 1st Speed      | WK128             | R/W     |
| 555 | 45021   | 0x139C | 1st Rev Amount | WK128             | R/W     |
| 556 | 45023   | 0x139E | 1st Rev Speed  | WK128             | R/W     |
| 557 | 45025   | 0x13A0 | 2nd Amount     | WK128             | R/W     |
| 558 | 45027   | 0x13A2 | 2nd Speed      | WK128             | R/W     |
| 559 | 45029   | 0x13A4 | 2nd Rev Amount | WK128             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 560 | 45031   | 0x13A6 | 2nd Rev Speed  | WK128             | R/W     |
| 561 | 45033   | 0x13A8 | Reserve        | WK128             | R/W     |
| 562 | 45035   | 0x13AA | Reserve        | WK128             | R/W     |
| 563 | 45037   | 0x13AC | Reserve        | WK128             | R/W     |
| 564 | 45039   | 0x13AE | Reserve        | WK128             | R/W     |
| 565 | 45041   | 0x13B0 | Pre-heat Time  | WK128             | R/W     |
| 566 | 45043   | 0x13B2 | Heating Time   | WK128             | R/W     |
| 567 | 45045   | 0x13B4 | Reserve        | WK128             | R/W     |
| 568 | 45047   | 0x13B6 | Reserve        | WK128             | R/W     |
| 569 | 45049   | 0x13B8 | SV2 Time       | WK129             | R/W     |
| 570 | 45051   | 0x13BA | 1st Amount     | WK129             | R/W     |
| 571 | 45053   | 0x13BC | 1st Speed      | WK129             | R/W     |
| 572 | 45055   | 0x13BE | 1st Rev Amount | WK129             | R/W     |
| 573 | 45057   | 0x13C0 | 1st Rev Speed  | WK129             | R/W     |
| 574 | 45059   | 0x13C2 | 2nd Amount     | WK129             | R/W     |
| 575 | 45061   | 0x13C4 | 2nd Speed      | WK129             | R/W     |
| 576 | 45063   | 0x13C6 | 2nd Rev Amount | WK129             | R/W     |
| 577 | 45065   | 0x13C8 | 2nd Rev Speed  | WK129             | R/W     |
| 578 | 45067   | 0x13CA | Reserve        | WK129             | R/W     |
| 579 | 45069   | 0x13CC | Reserve        | WK129             | R/W     |
| 580 | 45071   | 0x13CE | Reserve        | WK129             | R/W     |
| 581 | 45073   | 0x13D0 | Reserve        | WK129             | R/W     |
| 582 | 45075   | 0x13D2 | Pre-heat Time  | WK129             | R/W     |
| 583 | 45077   | 0x13D4 | Heating Time   | WK129             | R/W     |
| 584 | 45079   | 0x13D6 | Reserve        | WK129             | R/W     |
| 585 | 45081   | 0x13D8 | Reserve        | WK129             | R/W     |
| 586 | 45083   | 0x13DA | SV2 Time       | WK130             | R/W     |
| 587 | 45085   | 0x13DC | 1st Amount     | WK130             | R/W     |
| 588 | 45087   | 0x13DE | 1st Speed      | WK130             | R/W     |
| 589 | 45089   | 0x13E0 | 1st Rev Amount | WK130             | R/W     |
| 590 | 45091   | 0x13E2 | 1st Rev Speed  | WK130             | R/W     |
| 591 | 45093   | 0x13E4 | 2nd Amount     | WK130             | R/W     |
| 592 | 45095   | 0x13E6 | 2nd Speed      | WK130             | R/W     |
| 593 | 45097   | 0x13E8 | 2nd Rev Amount | WK130             | R/W     |
| 594 | 45099   | 0x13EA | 2nd Rev Speed  | WK130             | R/W     |
| 595 | 45101   | 0x13EC | Reserve        | WK130             | R/W     |
| 596 | 45103   | 0x13EE | Reserve        | WK130             | R/W     |
| 597 | 45105   | 0x13F0 | Reserve        | WK130             | R/W     |
| 598 | 45107   | 0x13F2 | Reserve        | WK130             | R/W     |
| 599 | 45109   | 0x13F4 | Pre-heat Time  | WK130             | R/W     |
| 600 | 45111   | 0x13F6 | Heating Time   | WK130             | R/W     |
| 601 | 45113   | 0x13F8 | Reserve        | WK130             | R/W     |
| 602 | 45115   | 0x13FA | Reserve        | WK130             | R/W     |
| 603 | 45117   | 0x13FC | SV2 Time       | WK131             | R/W     |
| 604 | 45119   | 0x13FE | 1st Amount     | WK131             | R/W     |
| 605 | 45121   | 0x1400 | 1st Speed      | WK131             | R/W     |
| 606 | 45123   | 0x1402 | 1st Rev Amount | WK131             | R/W     |
| 607 | 45125   | 0x1404 | 1st Rev Speed  | WK131             | R/W     |
| 608 | 45127   | 0x1406 | 2nd Amount     | WK131             | R/W     |
| 609 | 45129   | 0x1408 | 2nd Speed      | WK131             | R/W     |
| 610 | 45131   | 0x140A | 2nd Rev Amount | WK131             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 611 | 45133   | 0x140C | 2nd Rev Speed  | WK131             | R/W     |
| 612 | 45135   | 0x140E | Reserve        | WK131             | R/W     |
| 613 | 45137   | 0x1410 | Reserve        | WK131             | R/W     |
| 614 | 45139   | 0x1412 | Reserve        | WK131             | R/W     |
| 615 | 45141   | 0x1414 | Reserve        | WK131             | R/W     |
| 616 | 45143   | 0x1416 | Pre-heat Time  | WK131             | R/W     |
| 617 | 45145   | 0x1418 | Heating Time   | WK131             | R/W     |
| 618 | 45147   | 0x141A | Reserve        | WK131             | R/W     |
| 619 | 45149   | 0x141C | Reserve        | WK131             | R/W     |
| 620 | 45151   | 0x141E | SV2 Time       | WK132             | R/W     |
| 621 | 45153   | 0x1420 | 1st Amount     | WK132             | R/W     |
| 622 | 45155   | 0x1422 | 1st Speed      | WK132             | R/W     |
| 623 | 45157   | 0x1424 | 1st Rev Amount | WK132             | R/W     |
| 624 | 45159   | 0x1426 | 1st Rev Speed  | WK132             | R/W     |
| 625 | 45161   | 0x1428 | 2nd Amount     | WK132             | R/W     |
| 626 | 45163   | 0x142A | 2nd Speed      | WK132             | R/W     |
| 627 | 45165   | 0x142C | 2nd Rev Amount | WK132             | R/W     |
| 628 | 45167   | 0x142E | 2nd Rev Speed  | WK132             | R/W     |
| 629 | 45169   | 0x1430 | Reserve        | WK132             | R/W     |
| 630 | 45171   | 0x1432 | Reserve        | WK132             | R/W     |
| 631 | 45173   | 0x1434 | Reserve        | WK132             | R/W     |
| 632 | 45175   | 0x1436 | Reserve        | WK132             | R/W     |
| 633 | 45177   | 0x1438 | Pre-heat Time  | WK132             | R/W     |
| 634 | 45179   | 0x143A | Heating Time   | WK132             | R/W     |
| 635 | 45181   | 0x143C | Reserve        | WK132             | R/W     |
| 636 | 45183   | 0x143E | Reserve        | WK132             | R/W     |
| 637 | 45185   | 0x1440 | SV2 Time       | WK133             | R/W     |
| 638 | 45187   | 0x1442 | 1st Amount     | WK133             | R/W     |
| 639 | 45189   | 0x1444 | 1st Speed      | WK133             | R/W     |
| 640 | 45191   | 0x1446 | 1st Rev Amount | WK133             | R/W     |
| 641 | 45193   | 0x1448 | 1st Rev Speed  | WK133             | R/W     |
| 642 | 45195   | 0x144A | 2nd Amount     | WK133             | R/W     |
| 643 | 45197   | 0x144C | 2nd Speed      | WK133             | R/W     |
| 644 | 45199   | 0x144E | 2nd Rev Amount | WK133             | R/W     |
| 645 | 45201   | 0x1450 | 2nd Rev Speed  | WK133             | R/W     |
| 646 | 45203   | 0x1452 | Reserve        | WK133             | R/W     |
| 647 | 45205   | 0x1454 | Reserve        | WK133             | R/W     |
| 648 | 45207   | 0x1456 | Reserve        | WK133             | R/W     |
| 649 | 45209   | 0x1458 | Reserve        | WK133             | R/W     |
| 650 | 45211   | 0x145A | Pre-heat Time  | WK133             | R/W     |
| 651 | 45213   | 0x145C | Heating Time   | WK133             | R/W     |
| 652 | 45215   | 0x145E | Reserve        | WK133             | R/W     |
| 653 | 45217   | 0x1460 | Reserve        | WK133             | R/W     |
| 654 | 45219   | 0x1462 | SV2 Time       | WK134             | R/W     |
| 655 | 45221   | 0x1464 | 1st Amount     | WK134             | R/W     |
| 656 | 45223   | 0x1466 | 1st Speed      | WK134             | R/W     |
| 657 | 45225   | 0x1468 | 1st Rev Amount | WK134             | R/W     |
| 658 | 45227   | 0x146A | 1st Rev Speed  | WK134             | R/W     |
| 659 | 45229   | 0x146C | 2nd Amount     | WK134             | R/W     |
| 660 | 45231   | 0x146E | 2nd Speed      | WK134             | R/W     |
| 661 | 45233   | 0x1470 | 2nd Rev Amount | WK134             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 662 | 45235   | 0x1472 | 2nd Rev Speed  | WK134             | R/W     |
| 663 | 45237   | 0x1474 | Reserve        | WK134             | R/W     |
| 664 | 45239   | 0x1476 | Reserve        | WK134             | R/W     |
| 665 | 45241   | 0x1478 | Reserve        | WK134             | R/W     |
| 666 | 45243   | 0x147A | Reserve        | WK134             | R/W     |
| 667 | 45245   | 0x147C | Pre-heat Time  | WK134             | R/W     |
| 668 | 45247   | 0x147E | Heating Time   | WK134             | R/W     |
| 669 | 45249   | 0x1480 | Reserve        | WK134             | R/W     |
| 670 | 45251   | 0x1482 | Reserve        | WK134             | R/W     |
| 671 | 45253   | 0x1484 | SV2 Time       | WK135             | R/W     |
| 672 | 45255   | 0x1486 | 1st Amount     | WK135             | R/W     |
| 673 | 45257   | 0x1488 | 1st Speed      | WK135             | R/W     |
| 674 | 45259   | 0x148A | 1st Rev Amount | WK135             | R/W     |
| 675 | 45261   | 0x148C | 1st Rev Speed  | WK135             | R/W     |
| 676 | 45263   | 0x148E | 2nd Amount     | WK135             | R/W     |
| 677 | 45265   | 0x1490 | 2nd Speed      | WK135             | R/W     |
| 678 | 45267   | 0x1492 | 2nd Rev Amount | WK135             | R/W     |
| 679 | 45269   | 0x1494 | 2nd Rev Speed  | WK135             | R/W     |
| 680 | 45271   | 0x1496 | Reserve        | WK135             | R/W     |
| 681 | 45273   | 0x1498 | Reserve        | WK135             | R/W     |
| 682 | 45275   | 0x149A | Reserve        | WK135             | R/W     |
| 683 | 45277   | 0x149C | Reserve        | WK135             | R/W     |
| 684 | 45279   | 0x149E | Pre-heat Time  | WK135             | R/W     |
| 685 | 45281   | 0x14A0 | Heating Time   | WK135             | R/W     |
| 686 | 45283   | 0x14A2 | Reserve        | WK135             | R/W     |
| 687 | 45285   | 0x14A4 | Reserve        | WK135             | R/W     |
| 688 | 45287   | 0x14A6 | SV2 Time       | WK136             | R/W     |
| 689 | 45289   | 0x14A8 | 1st Amount     | WK136             | R/W     |
| 690 | 45291   | 0x14AA | 1st Speed      | WK136             | R/W     |
| 691 | 45293   | 0x14AC | 1st Rev Amount | WK136             | R/W     |
| 692 | 45295   | 0x14AE | 1st Rev Speed  | WK136             | R/W     |
| 693 | 45297   | 0x14B0 | 2nd Amount     | WK136             | R/W     |
| 694 | 45299   | 0x14B2 | 2nd Speed      | WK136             | R/W     |
| 695 | 45301   | 0x14B4 | 2nd Rev Amount | WK136             | R/W     |
| 696 | 45303   | 0x14B6 | 2nd Rev Speed  | WK136             | R/W     |
| 697 | 45305   | 0x14B8 | Reserve        | WK136             | R/W     |
| 698 | 45307   | 0x14BA | Reserve        | WK136             | R/W     |
| 699 | 45309   | 0x14BC | Reserve        | WK136             | R/W     |
| 700 | 45311   | 0x14BE | Reserve        | WK136             | R/W     |
| 701 | 45313   | 0x14C0 | Pre-heat Time  | WK136             | R/W     |
| 702 | 45315   | 0x14C2 | Heating Time   | WK136             | R/W     |
| 703 | 45317   | 0x14C4 | Reserve        | WK136             | R/W     |
| 704 | 45319   | 0x14C6 | Reserve        | WK136             | R/W     |
| 705 | 45321   | 0x14C8 | SV2 Time       | WK137             | R/W     |
| 706 | 45323   | 0x14CA | 1st Amount     | WK137             | R/W     |
| 707 | 45325   | 0x14CC | 1st Speed      | WK137             | R/W     |
| 708 | 45327   | 0x14CE | 1st Rev Amount | WK137             | R/W     |
| 709 | 45329   | 0x14D0 | 1st Rev Speed  | WK137             | R/W     |
| 710 | 45331   | 0x14D2 | 2nd Amount     | WK137             | R/W     |
| 711 | 45333   | 0x14D4 | 2nd Speed      | WK137             | R/W     |
| 712 | 45335   | 0x14D6 | 2nd Rev Amount | WK137             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 713 | 45337   | 0x14D8 | 2nd Rev Speed  | WK137             | R/W     |
| 714 | 45339   | 0x14DA | Reserve        | WK137             | R/W     |
| 715 | 45341   | 0x14DC | Reserve        | WK137             | R/W     |
| 716 | 45343   | 0x14DE | Reserve        | WK137             | R/W     |
| 717 | 45345   | 0x14E0 | Reserve        | WK137             | R/W     |
| 718 | 45347   | 0x14E2 | Pre-heat Time  | WK137             | R/W     |
| 719 | 45349   | 0x14E4 | Heating Time   | WK137             | R/W     |
| 720 | 45351   | 0x14E6 | Reserve        | WK137             | R/W     |
| 721 | 45353   | 0x14E8 | Reserve        | WK137             | R/W     |
| 722 | 45355   | 0x14EA | SV2 Time       | WK138             | R/W     |
| 723 | 45357   | 0x14EC | 1st Amount     | WK138             | R/W     |
| 724 | 45359   | 0x14EE | 1st Speed      | WK138             | R/W     |
| 725 | 45361   | 0x14F0 | 1st Rev Amount | WK138             | R/W     |
| 726 | 45363   | 0x14F2 | 1st Rev Speed  | WK138             | R/W     |
| 727 | 45365   | 0x14F4 | 2nd Amount     | WK138             | R/W     |
| 728 | 45367   | 0x14F6 | 2nd Speed      | WK138             | R/W     |
| 729 | 45369   | 0x14F8 | 2nd Rev Amount | WK138             | R/W     |
| 730 | 45371   | 0x14FA | 2nd Rev Speed  | WK138             | R/W     |
| 731 | 45373   | 0x14FC | Reserve        | WK138             | R/W     |
| 732 | 45375   | 0x14FE | Reserve        | WK138             | R/W     |
| 733 | 45377   | 0x1500 | Reserve        | WK138             | R/W     |
| 734 | 45379   | 0x1502 | Reserve        | WK138             | R/W     |
| 735 | 45381   | 0x1504 | Pre-heat Time  | WK138             | R/W     |
| 736 | 45383   | 0x1506 | Heating Time   | WK138             | R/W     |
| 737 | 45385   | 0x1508 | Reserve        | WK138             | R/W     |
| 738 | 45387   | 0x150A | Reserve        | WK138             | R/W     |
| 739 | 45389   | 0x150C | SV2 Time       | WK139             | R/W     |
| 740 | 45391   | 0x150E | 1st Amount     | WK139             | R/W     |
| 741 | 45393   | 0x1510 | 1st Speed      | WK139             | R/W     |
| 742 | 45395   | 0x1512 | 1st Rev Amount | WK139             | R/W     |
| 743 | 45397   | 0x1514 | 1st Rev Speed  | WK139             | R/W     |
| 744 | 45399   | 0x1516 | 2nd Amount     | WK139             | R/W     |
| 745 | 45401   | 0x1518 | 2nd Speed      | WK139             | R/W     |
| 746 | 45403   | 0x151A | 2nd Rev Amount | WK139             | R/W     |
| 747 | 45405   | 0x151C | 2nd Rev Speed  | WK139             | R/W     |
| 748 | 45407   | 0x151E | Reserve        | WK139             | R/W     |
| 749 | 45409   | 0x1520 | Reserve        | WK139             | R/W     |
| 750 | 45411   | 0x1522 | Reserve        | WK139             | R/W     |
| 751 | 45413   | 0x1524 | Reserve        | WK139             | R/W     |
| 752 | 45415   | 0x1526 | Pre-heat Time  | WK139             | R/W     |
| 753 | 45417   | 0x1528 | Heating Time   | WK139             | R/W     |
| 754 | 45419   | 0x152A | Reserve        | WK139             | R/W     |
| 755 | 45421   | 0x152C | Reserve        | WK139             | R/W     |
| 756 | 45423   | 0x152E | SV2 Time       | WK140             | R/W     |
| 757 | 45425   | 0x1530 | 1st Amount     | WK140             | R/W     |
| 758 | 45427   | 0x1532 | 1st Speed      | WK140             | R/W     |
| 759 | 45429   | 0x1534 | 1st Rev Amount | WK140             | R/W     |
| 760 | 45431   | 0x1536 | 1st Rev Speed  | WK140             | R/W     |
| 761 | 45433   | 0x1538 | 2nd Amount     | WK140             | R/W     |
| 762 | 45435   | 0x153A | 2nd Speed      | WK140             | R/W     |
| 763 | 45437   | 0x153C | 2nd Rev Amount | WK140             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 764 | 45439   | 0x153E | 2nd Rev Speed  | WK140             | R/W     |
| 765 | 45441   | 0x1540 | Reserve        | WK140             | R/W     |
| 766 | 45443   | 0x1542 | Reserve        | WK140             | R/W     |
| 767 | 45445   | 0x1544 | Reserve        | WK140             | R/W     |
| 768 | 45447   | 0x1546 | Reserve        | WK140             | R/W     |
| 769 | 45449   | 0x1548 | Pre-heat Time  | WK140             | R/W     |
| 770 | 45451   | 0x154A | Heating Time   | WK140             | R/W     |
| 771 | 45453   | 0x154C | Reserve        | WK140             | R/W     |
| 772 | 45455   | 0x154E | Reserve        | WK140             | R/W     |
| 773 | 45457   | 0x1550 | SV2 Time       | WK141             | R/W     |
| 774 | 45459   | 0x1552 | 1st Amount     | WK141             | R/W     |
| 775 | 45461   | 0x1554 | 1st Speed      | WK141             | R/W     |
| 776 | 45463   | 0x1556 | 1st Rev Amount | WK141             | R/W     |
| 777 | 45465   | 0x1558 | 1st Rev Speed  | WK141             | R/W     |
| 778 | 45467   | 0x155A | 2nd Amount     | WK141             | R/W     |
| 779 | 45469   | 0x155C | 2nd Speed      | WK141             | R/W     |
| 780 | 45471   | 0x155E | 2nd Rev Amount | WK141             | R/W     |
| 781 | 45473   | 0x1560 | 2nd Rev Speed  | WK141             | R/W     |
| 782 | 45475   | 0x1562 | Reserve        | WK141             | R/W     |
| 783 | 45477   | 0x1564 | Reserve        | WK141             | R/W     |
| 784 | 45479   | 0x1566 | Reserve        | WK141             | R/W     |
| 785 | 45481   | 0x1568 | Reserve        | WK141             | R/W     |
| 786 | 45483   | 0x156A | Pre-heat Time  | WK141             | R/W     |
| 787 | 45485   | 0x156C | Heating Time   | WK141             | R/W     |
| 788 | 45487   | 0x156E | Reserve        | WK141             | R/W     |
| 789 | 45489   | 0x1570 | Reserve        | WK141             | R/W     |
| 790 | 45491   | 0x1572 | SV2 Time       | WK142             | R/W     |
| 791 | 45493   | 0x1574 | 1st Amount     | WK142             | R/W     |
| 792 | 45495   | 0x1576 | 1st Speed      | WK142             | R/W     |
| 793 | 45497   | 0x1578 | 1st Rev Amount | WK142             | R/W     |
| 794 | 45499   | 0x157A | 1st Rev Speed  | WK142             | R/W     |
| 795 | 45501   | 0x157C | 2nd Amount     | WK142             | R/W     |
| 796 | 45503   | 0x157E | 2nd Speed      | WK142             | R/W     |
| 797 | 45505   | 0x1580 | 2nd Rev Amount | WK142             | R/W     |
| 798 | 45507   | 0x1582 | 2nd Rev Speed  | WK142             | R/W     |
| 799 | 45509   | 0x1584 | Reserve        | WK142             | R/W     |
| 800 | 45511   | 0x1586 | Reserve        | WK142             | R/W     |
| 801 | 45513   | 0x1588 | Reserve        | WK142             | R/W     |
| 802 | 45515   | 0x158A | Reserve        | WK142             | R/W     |
| 803 | 45517   | 0x158C | Pre-heat Time  | WK142             | R/W     |
| 804 | 45519   | 0x158E | Heating Time   | WK142             | R/W     |
| 805 | 45521   | 0x1590 | Reserve        | WK142             | R/W     |
| 806 | 45523   | 0x1592 | Reserve        | WK142             | R/W     |
| 807 | 45525   | 0x1594 | SV2 Time       | WK143             | R/W     |
| 808 | 45527   | 0x1596 | 1st Amount     | WK143             | R/W     |
| 809 | 45529   | 0x1598 | 1st Speed      | WK143             | R/W     |
| 810 | 45531   | 0x159A | 1st Rev Amount | WK143             | R/W     |
| 811 | 45533   | 0x159C | 1st Rev Speed  | WK143             | R/W     |
| 812 | 45535   | 0x159E | 2nd Amount     | WK143             | R/W     |
| 813 | 45537   | 0x15A0 | 2nd Speed      | WK143             | R/W     |
| 814 | 45539   | 0x15A2 | 2nd Rev Amount | WK143             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 815 | 45541   | 0x15A4 | 2nd Rev Speed  | WK143             | R/W     |
| 816 | 45543   | 0x15A6 | Reserve        | WK143             | R/W     |
| 817 | 45545   | 0x15A8 | Reserve        | WK143             | R/W     |
| 818 | 45547   | 0x15AA | Reserve        | WK143             | R/W     |
| 819 | 45549   | 0x15AC | Reserve        | WK143             | R/W     |
| 820 | 45551   | 0x15AE | Pre-heat Time  | WK143             | R/W     |
| 821 | 45553   | 0x15B0 | Heating Time   | WK143             | R/W     |
| 822 | 45555   | 0x15B2 | Reserve        | WK143             | R/W     |
| 823 | 45557   | 0x15B4 | Reserve        | WK143             | R/W     |
| 824 | 45559   | 0x15B6 | SV2 Time       | WK144             | R/W     |
| 825 | 45561   | 0x15B8 | 1st Amount     | WK144             | R/W     |
| 826 | 45563   | 0x15BA | 1st Speed      | WK144             | R/W     |
| 827 | 45565   | 0x15BC | 1st Rev Amount | WK144             | R/W     |
| 828 | 45567   | 0x15BE | 1st Rev Speed  | WK144             | R/W     |
| 829 | 45569   | 0x15C0 | 2nd Amount     | WK144             | R/W     |
| 830 | 45571   | 0x15C2 | 2nd Speed      | WK144             | R/W     |
| 831 | 45573   | 0x15C4 | 2nd Rev Amount | WK144             | R/W     |
| 832 | 45575   | 0x15C6 | 2nd Rev Speed  | WK144             | R/W     |
| 833 | 45577   | 0x15C8 | Reserve        | WK144             | R/W     |
| 834 | 45579   | 0x15CA | Reserve        | WK144             | R/W     |
| 835 | 45581   | 0x15CC | Reserve        | WK144             | R/W     |
| 836 | 45583   | 0x15CE | Reserve        | WK144             | R/W     |
| 837 | 45585   | 0x15D0 | Pre-heat Time  | WK144             | R/W     |
| 838 | 45587   | 0x15D2 | Heating Time   | WK144             | R/W     |
| 839 | 45589   | 0x15D4 | Reserve        | WK144             | R/W     |
| 840 | 45591   | 0x15D6 | Reserve        | WK144             | R/W     |
| 841 | 45593   | 0x15D8 | SV2 Time       | WK145             | R/W     |
| 842 | 45595   | 0x15DA | 1st Amount     | WK145             | R/W     |
| 843 | 45597   | 0x15DC | 1st Speed      | WK145             | R/W     |
| 844 | 45599   | 0x15DE | 1st Rev Amount | WK145             | R/W     |
| 845 | 45601   | 0x15E0 | 1st Rev Speed  | WK145             | R/W     |
| 846 | 45603   | 0x15E2 | 2nd Amount     | WK145             | R/W     |
| 847 | 45605   | 0x15E4 | 2nd Speed      | WK145             | R/W     |
| 848 | 45607   | 0x15E6 | 2nd Rev Amount | WK145             | R/W     |
| 849 | 45609   | 0x15E8 | 2nd Rev Speed  | WK145             | R/W     |
| 850 | 45611   | 0x15EA | Reserve        | WK145             | R/W     |
| 851 | 45613   | 0x15EC | Reserve        | WK145             | R/W     |
| 852 | 45615   | 0x15EE | Reserve        | WK145             | R/W     |
| 853 | 45617   | 0x15F0 | Reserve        | WK145             | R/W     |
| 854 | 45619   | 0x15F2 | Pre-heat Time  | WK145             | R/W     |
| 855 | 45621   | 0x15F4 | Heating Time   | WK145             | R/W     |
| 856 | 45623   | 0x15F6 | Reserve        | WK145             | R/W     |
| 857 | 45625   | 0x15F8 | Reserve        | WK145             | R/W     |
| 858 | 45627   | 0x15FA | SV2 Time       | WK146             | R/W     |
| 859 | 45629   | 0x15FC | 1st Amount     | WK146             | R/W     |
| 860 | 45631   | 0x15FE | 1st Speed      | WK146             | R/W     |
| 861 | 45633   | 0x1600 | 1st Rev Amount | WK146             | R/W     |
| 862 | 45635   | 0x1602 | 1st Rev Speed  | WK146             | R/W     |
| 863 | 45637   | 0x1604 | 2nd Amount     | WK146             | R/W     |
| 864 | 45639   | 0x1606 | 2nd Speed      | WK146             | R/W     |
| 865 | 45641   | 0x1608 | 2nd Rev Amount | WK146             | R/W     |



| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 866 | 45643   | 0x160A | 2nd Rev Speed  | WK146             | R/W     |
| 867 | 45645   | 0x160C | Reserve        | WK146             | R/W     |
| 868 | 45647   | 0x160E | Reserve        | WK146             | R/W     |
| 869 | 45649   | 0x1610 | Reserve        | WK146             | R/W     |
| 870 | 45651   | 0x1612 | Reserve        | WK146             | R/W     |
| 871 | 45653   | 0x1614 | Pre-heat Time  | WK146             | R/W     |
| 872 | 45655   | 0x1616 | Heating Time   | WK146             | R/W     |
| 873 | 45657   | 0x1618 | Reserve        | WK146             | R/W     |
| 874 | 45659   | 0x161A | Reserve        | WK146             | R/W     |
| 875 | 45661   | 0x161C | SV2 Time       | WK147             | R/W     |
| 876 | 45663   | 0x161E | 1st Amount     | WK147             | R/W     |
| 877 | 45665   | 0x1620 | 1st Speed      | WK147             | R/W     |
| 878 | 45667   | 0x1622 | 1st Rev Amount | WK147             | R/W     |
| 879 | 45669   | 0x1624 | 1st Rev Speed  | WK147             | R/W     |
| 880 | 45671   | 0x1626 | 2nd Amount     | WK147             | R/W     |
| 881 | 45673   | 0x1628 | 2nd Speed      | WK147             | R/W     |
| 882 | 45675   | 0x162A | 2nd Rev Amount | WK147             | R/W     |
| 883 | 45677   | 0x162C | 2nd Rev Speed  | WK147             | R/W     |
| 884 | 45679   | 0x162E | Reserve        | WK147             | R/W     |
| 885 | 45681   | 0x1630 | Reserve        | WK147             | R/W     |
| 886 | 45683   | 0x1632 | Reserve        | WK147             | R/W     |
| 887 | 45685   | 0x1634 | Reserve        | WK147             | R/W     |
| 888 | 45687   | 0x1636 | Pre-heat Time  | WK147             | R/W     |
| 889 | 45689   | 0x1638 | Heating Time   | WK147             | R/W     |
| 890 | 45691   | 0x163A | Reserve        | WK147             | R/W     |
| 891 | 45693   | 0x163C | Reserve        | WK147             | R/W     |
| 892 | 45695   | 0x163E | SV2 Time       | WK148             | R/W     |
| 893 | 45697   | 0x1640 | 1st Amount     | WK148             | R/W     |
| 894 | 45699   | 0x1642 | 1st Speed      | WK148             | R/W     |
| 895 | 45701   | 0x1644 | 1st Rev Amount | WK148             | R/W     |
| 896 | 45703   | 0x1646 | 1st Rev Speed  | WK148             | R/W     |
| 897 | 45705   | 0x1648 | 2nd Amount     | WK148             | R/W     |
| 898 | 45707   | 0x164A | 2nd Speed      | WK148             | R/W     |
| 899 | 45709   | 0x164C | 2nd Rev Amount | WK148             | R/W     |
| 900 | 45711   | 0x164E | 2nd Rev Speed  | WK148             | R/W     |
| 901 | 45713   | 0x1650 | Reserve        | WK148             | R/W     |
| 902 | 45715   | 0x1652 | Reserve        | WK148             | R/W     |
| 903 | 45717   | 0x1654 | Reserve        | WK148             | R/W     |
| 904 | 45719   | 0x1656 | Reserve        | WK148             | R/W     |
| 905 | 45721   | 0x1658 | Pre-heat Time  | WK148             | R/W     |
| 906 | 45723   | 0x165A | Heating Time   | WK148             | R/W     |
| 907 | 45725   | 0x165C | Reserve        | WK148             | R/W     |
| 908 | 45727   | 0x165E | Reserve        | WK148             | R/W     |
| 909 | 45729   | 0x1660 | SV2 Time       | WK149             | R/W     |
| 910 | 45731   | 0x1662 | 1st Amount     | WK149             | R/W     |
| 911 | 45733   | 0x1664 | 1st Speed      | WK149             | R/W     |
| 912 | 45735   | 0x1666 | 1st Rev Amount | WK149             | R/W     |
| 913 | 45737   | 0x1668 | 1st Rev Speed  | WK149             | R/W     |
| 914 | 45739   | 0x166A | 2nd Amount     | WK149             | R/W     |
| 915 | 45741   | 0x166C | 2nd Speed      | WK149             | R/W     |
| 916 | 45743   | 0x166E | 2nd Rev Amount | WK149             | R/W     |

| No. | Address |        | Name           | Reading / Writing | Remarks |
|-----|---------|--------|----------------|-------------------|---------|
|     | DEC     | HEX    |                |                   |         |
| 917 | 45745   | 0x1670 | 2nd Rev Speed  | WK149             | R/W     |
| 918 | 45747   | 0x1672 | Reserve        | WK149             | R/W     |
| 919 | 45749   | 0x1674 | Reserve        | WK149             | R/W     |
| 920 | 45751   | 0x1676 | Reserve        | WK149             | R/W     |
| 921 | 45753   | 0x1678 | Reserve        | WK149             | R/W     |
| 922 | 45755   | 0x167A | Pre-heat Time  | WK149             | R/W     |
| 923 | 45757   | 0x167C | Heating Time   | WK149             | R/W     |
| 924 | 45759   | 0x167E | Reserve        | WK149             | R/W     |
| 925 | 45761   | 0x1680 | Reserve        | WK149             | R/W     |
| 926 | 45763   | 0x1682 | SV2 Time       | WK150             | R/W     |
| 927 | 45765   | 0x1684 | 1st Amount     | WK150             | R/W     |
| 928 | 45767   | 0x1686 | 1st Speed      | WK150             | R/W     |
| 929 | 45769   | 0x1688 | 1st Rev Amount | WK150             | R/W     |
| 930 | 45771   | 0x168A | 1st Rev Speed  | WK150             | R/W     |
| 931 | 45773   | 0x168C | 2nd Amount     | WK150             | R/W     |
| 932 | 45775   | 0x168E | 2nd Speed      | WK150             | R/W     |
| 933 | 45777   | 0x1690 | 2nd Rev Amount | WK150             | R/W     |
| 934 | 45779   | 0x1692 | 2nd Rev Speed  | WK150             | R/W     |
| 935 | 45781   | 0x1694 | Reserve        | WK150             | R/W     |
| 936 | 45783   | 0x1696 | Reserve        | WK150             | R/W     |
| 937 | 45785   | 0x1698 | Reserve        | WK150             | R/W     |
| 938 | 45787   | 0x169A | Reserve        | WK150             | R/W     |
| 939 | 45789   | 0x169C | Pre-heat Time  | WK150             | R/W     |
| 940 | 45791   | 0x169E | Heating Time   | WK150             | R/W     |
| 941 | 45793   | 0x16A0 | Reserve        | WK150             | R/W     |
| 942 | 45795   | 0x16A2 | Reserve        | WK150             | R/W     |
| 943 | 45797   | 0x16A4 | SV2 Time       | WK151             | R/W     |
| 944 | 45799   | 0x16A6 | 1st Amount     | WK151             | R/W     |
| 945 | 45801   | 0x16A8 | 1st Speed      | WK151             | R/W     |
| 946 | 45803   | 0x16AA | 1st Rev Amount | WK151             | R/W     |
| 947 | 45805   | 0x16AC | 1st Rev Speed  | WK151             | R/W     |
| 948 | 45807   | 0x16AE | 2nd Amount     | WK151             | R/W     |
| 949 | 45809   | 0x16B0 | 2nd Speed      | WK151             | R/W     |
| 950 | 45811   | 0x16B2 | 2nd Rev Amount | WK151             | R/W     |
| 951 | 45813   | 0x16B4 | 2nd Rev Speed  | WK151             | R/W     |
| 952 | 45815   | 0x16B6 | Reserve        | WK151             | R/W     |
| 953 | 45817   | 0x16B8 | Reserve        | WK151             | R/W     |
| 954 | 45819   | 0x16BA | Reserve        | WK151             | R/W     |
| 955 | 45821   | 0x16BC | Reserve        | WK151             | R/W     |
| 956 | 45823   | 0x16BE | Pre-heat Time  | WK151             | R/W     |
| 957 | 45825   | 0x16C0 | Heating Time   | WK151             | R/W     |
| 958 | 45827   | 0x16C2 | Reserve        | WK151             | R/W     |
| 959 | 45829   | 0x16C4 | Reserve        | WK151             | R/W     |
| 960 | 45831   | 0x16C6 | SV2 Time       | WK152             | R/W     |
| 961 | 45833   | 0x16C8 | 1st Amount     | WK152             | R/W     |
| 962 | 45835   | 0x16CA | 1st Speed      | WK152             | R/W     |
| 963 | 45837   | 0x16CC | 1st Rev Amount | WK152             | R/W     |
| 964 | 45839   | 0x16CE | 1st Rev Speed  | WK152             | R/W     |
| 965 | 45841   | 0x16D0 | 2nd Amount     | WK152             | R/W     |
| 966 | 45843   | 0x16D2 | 2nd Speed      | WK152             | R/W     |
| 967 | 45845   | 0x16D4 | 2nd Rev Amount | WK152             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 968  | 45847   | 0x16D6 | 2nd Rev Speed  | WK152             | R/W     |
| 969  | 45849   | 0x16D8 | Reserve        | WK152             | R/W     |
| 970  | 45851   | 0x16DA | Reserve        | WK152             | R/W     |
| 971  | 45853   | 0x16DC | Reserve        | WK152             | R/W     |
| 972  | 45855   | 0x16DE | Reserve        | WK152             | R/W     |
| 973  | 45857   | 0x16E0 | Pre-heat Time  | WK152             | R/W     |
| 974  | 45859   | 0x16E2 | Heating Time   | WK152             | R/W     |
| 975  | 45861   | 0x16E4 | Reserve        | WK152             | R/W     |
| 976  | 45863   | 0x16E6 | Reserve        | WK152             | R/W     |
| 977  | 45865   | 0x16E8 | SV2 Time       | WK153             | R/W     |
| 978  | 45867   | 0x16EA | 1st Amount     | WK153             | R/W     |
| 979  | 45869   | 0x16EC | 1st Speed      | WK153             | R/W     |
| 980  | 45871   | 0x16EE | 1st Rev Amount | WK153             | R/W     |
| 981  | 45873   | 0x16F0 | 1st Rev Speed  | WK153             | R/W     |
| 982  | 45875   | 0x16F2 | 2nd Amount     | WK153             | R/W     |
| 983  | 45877   | 0x16F4 | 2nd Speed      | WK153             | R/W     |
| 984  | 45879   | 0x16F6 | 2nd Rev Amount | WK153             | R/W     |
| 985  | 45881   | 0x16F8 | 2nd Rev Speed  | WK153             | R/W     |
| 986  | 45883   | 0x16FA | Reserve        | WK153             | R/W     |
| 987  | 45885   | 0x16FC | Reserve        | WK153             | R/W     |
| 988  | 45887   | 0x16FE | Reserve        | WK153             | R/W     |
| 989  | 45889   | 0x1700 | Reserve        | WK153             | R/W     |
| 990  | 45891   | 0x1702 | Pre-heat Time  | WK153             | R/W     |
| 991  | 45893   | 0x1704 | Heating Time   | WK153             | R/W     |
| 992  | 45895   | 0x1706 | Reserve        | WK153             | R/W     |
| 993  | 45897   | 0x1708 | Reserve        | WK153             | R/W     |
| 994  | 45899   | 0x170A | SV2 Time       | WK154             | R/W     |
| 995  | 45901   | 0x170C | 1st Amount     | WK154             | R/W     |
| 996  | 45903   | 0x170E | 1st Speed      | WK154             | R/W     |
| 997  | 45905   | 0x1710 | 1st Rev Amount | WK154             | R/W     |
| 998  | 45907   | 0x1712 | 1st Rev Speed  | WK154             | R/W     |
| 999  | 45909   | 0x1714 | 2nd Amount     | WK154             | R/W     |
| 1000 | 45911   | 0x1716 | 2nd Speed      | WK154             | R/W     |
| 1001 | 45913   | 0x1718 | 2nd Rev Amount | WK154             | R/W     |
| 1002 | 45915   | 0x171A | 2nd Rev Speed  | WK154             | R/W     |
| 1003 | 45917   | 0x171C | Reserve        | WK154             | R/W     |
| 1004 | 45919   | 0x171E | Reserve        | WK154             | R/W     |
| 1005 | 45921   | 0x1720 | Reserve        | WK154             | R/W     |
| 1006 | 45923   | 0x1722 | Reserve        | WK154             | R/W     |
| 1007 | 45925   | 0x1724 | Pre-heat Time  | WK154             | R/W     |
| 1008 | 45927   | 0x1726 | Heating Time   | WK154             | R/W     |
| 1009 | 45929   | 0x1728 | Reserve        | WK154             | R/W     |
| 1010 | 45931   | 0x172A | Reserve        | WK154             | R/W     |
| 1011 | 45933   | 0x172C | SV2 Time       | WK155             | R/W     |
| 1012 | 45935   | 0x172E | 1st Amount     | WK155             | R/W     |
| 1013 | 45937   | 0x1730 | 1st Speed      | WK155             | R/W     |
| 1014 | 45939   | 0x1732 | 1st Rev Amount | WK155             | R/W     |
| 1015 | 45941   | 0x1734 | 1st Rev Speed  | WK155             | R/W     |
| 1016 | 45943   | 0x1736 | 2nd Amount     | WK155             | R/W     |
| 1017 | 45945   | 0x1738 | 2nd Speed      | WK155             | R/W     |
| 1018 | 45947   | 0x173A | 2nd Rev Amount | WK155             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1019 | 45949   | 0x173C | 2nd Rev Speed  | WK155             | R/W     |
| 1020 | 45951   | 0x173E | Reserve        | WK155             | R/W     |
| 1021 | 45953   | 0x1740 | Reserve        | WK155             | R/W     |
| 1022 | 45955   | 0x1742 | Reserve        | WK155             | R/W     |
| 1023 | 45957   | 0x1744 | Reserve        | WK155             | R/W     |
| 1024 | 45959   | 0x1746 | Pre-heat Time  | WK155             | R/W     |
| 1025 | 45961   | 0x1748 | Heating Time   | WK155             | R/W     |
| 1026 | 45963   | 0x174A | Reserve        | WK155             | R/W     |
| 1027 | 45965   | 0x174C | Reserve        | WK155             | R/W     |
| 1028 | 45967   | 0x174E | SV2 Time       | WK156             | R/W     |
| 1029 | 45969   | 0x1750 | 1st Amount     | WK156             | R/W     |
| 1030 | 45971   | 0x1752 | 1st Speed      | WK156             | R/W     |
| 1031 | 45973   | 0x1754 | 1st Rev Amount | WK156             | R/W     |
| 1032 | 45975   | 0x1756 | 1st Rev Speed  | WK156             | R/W     |
| 1033 | 45977   | 0x1758 | 2nd Amount     | WK156             | R/W     |
| 1034 | 45979   | 0x175A | 2nd Speed      | WK156             | R/W     |
| 1035 | 45981   | 0x175C | 2nd Rev Amount | WK156             | R/W     |
| 1036 | 45983   | 0x175E | 2nd Rev Speed  | WK156             | R/W     |
| 1037 | 45985   | 0x1760 | Reserve        | WK156             | R/W     |
| 1038 | 45987   | 0x1762 | Reserve        | WK156             | R/W     |
| 1039 | 45989   | 0x1764 | Reserve        | WK156             | R/W     |
| 1040 | 45991   | 0x1766 | Reserve        | WK156             | R/W     |
| 1041 | 45993   | 0x1768 | Pre-heat Time  | WK156             | R/W     |
| 1042 | 45995   | 0x176A | Heating Time   | WK156             | R/W     |
| 1043 | 45997   | 0x176C | Reserve        | WK156             | R/W     |
| 1044 | 45999   | 0x176E | Reserve        | WK156             | R/W     |
| 1045 | 46001   | 0x1770 | SV2 Time       | WK157             | R/W     |
| 1046 | 46003   | 0x1772 | 1st Amount     | WK157             | R/W     |
| 1047 | 46005   | 0x1774 | 1st Speed      | WK157             | R/W     |
| 1048 | 46007   | 0x1776 | 1st Rev Amount | WK157             | R/W     |
| 1049 | 46009   | 0x1778 | 1st Rev Speed  | WK157             | R/W     |
| 1050 | 46011   | 0x177A | 2nd Amount     | WK157             | R/W     |
| 1051 | 46013   | 0x177C | 2nd Speed      | WK157             | R/W     |
| 1052 | 46015   | 0x177E | 2nd Rev Amount | WK157             | R/W     |
| 1053 | 46017   | 0x1780 | 2nd Rev Speed  | WK157             | R/W     |
| 1054 | 46019   | 0x1782 | Reserve        | WK157             | R/W     |
| 1055 | 46021   | 0x1784 | Reserve        | WK157             | R/W     |
| 1056 | 46023   | 0x1786 | Reserve        | WK157             | R/W     |
| 1057 | 46025   | 0x1788 | Reserve        | WK157             | R/W     |
| 1058 | 46027   | 0x178A | Pre-heat Time  | WK157             | R/W     |
| 1059 | 46029   | 0x178C | Heating Time   | WK157             | R/W     |
| 1060 | 46031   | 0x178E | Reserve        | WK157             | R/W     |
| 1061 | 46033   | 0x1790 | Reserve        | WK157             | R/W     |
| 1062 | 46035   | 0x1792 | SV2 Time       | WK158             | R/W     |
| 1063 | 46037   | 0x1794 | 1st Amount     | WK158             | R/W     |
| 1064 | 46039   | 0x1796 | 1st Speed      | WK158             | R/W     |
| 1065 | 46041   | 0x1798 | 1st Rev Amount | WK158             | R/W     |
| 1066 | 46043   | 0x179A | 1st Rev Speed  | WK158             | R/W     |
| 1067 | 46045   | 0x179C | 2nd Amount     | WK158             | R/W     |
| 1068 | 46047   | 0x179E | 2nd Speed      | WK158             | R/W     |
| 1069 | 46049   | 0x17A0 | 2nd Rev Amount | WK158             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1070 | 46051   | 0x17A2 | 2nd Rev Speed  | WK158             | R/W     |
| 1071 | 46053   | 0x17A4 | Reserve        | WK158             | R/W     |
| 1072 | 46055   | 0x17A6 | Reserve        | WK158             | R/W     |
| 1073 | 46057   | 0x17A8 | Reserve        | WK158             | R/W     |
| 1074 | 46059   | 0x17AA | Reserve        | WK158             | R/W     |
| 1075 | 46061   | 0x17AC | Pre-heat Time  | WK158             | R/W     |
| 1076 | 46063   | 0x17AE | Heating Time   | WK158             | R/W     |
| 1077 | 46065   | 0x17B0 | Reserve        | WK158             | R/W     |
| 1078 | 46067   | 0x17B2 | Reserve        | WK158             | R/W     |
| 1079 | 46069   | 0x17B4 | SV2 Time       | WK159             | R/W     |
| 1080 | 46071   | 0x17B6 | 1st Amount     | WK159             | R/W     |
| 1081 | 46073   | 0x17B8 | 1st Speed      | WK159             | R/W     |
| 1082 | 46075   | 0x17BA | 1st Rev Amount | WK159             | R/W     |
| 1083 | 46077   | 0x17BC | 1st Rev Speed  | WK159             | R/W     |
| 1084 | 46079   | 0x17BE | 2nd Amount     | WK159             | R/W     |
| 1085 | 46081   | 0x17C0 | 2nd Speed      | WK159             | R/W     |
| 1086 | 46083   | 0x17C2 | 2nd Rev Amount | WK159             | R/W     |
| 1087 | 46085   | 0x17C4 | 2nd Rev Speed  | WK159             | R/W     |
| 1088 | 46087   | 0x17C6 | Reserve        | WK159             | R/W     |
| 1089 | 46089   | 0x17C8 | Reserve        | WK159             | R/W     |
| 1090 | 46091   | 0x17CA | Reserve        | WK159             | R/W     |
| 1091 | 46093   | 0x17CC | Reserve        | WK159             | R/W     |
| 1092 | 46095   | 0x17CE | Pre-heat Time  | WK159             | R/W     |
| 1093 | 46097   | 0x17D0 | Heating Time   | WK159             | R/W     |
| 1094 | 46099   | 0x17D2 | Reserve        | WK159             | R/W     |
| 1095 | 46101   | 0x17D4 | Reserve        | WK159             | R/W     |
| 1096 | 46103   | 0x17D6 | SV2 Time       | WK160             | R/W     |
| 1097 | 46105   | 0x17D8 | 1st Amount     | WK160             | R/W     |
| 1098 | 46107   | 0x17DA | 1st Speed      | WK160             | R/W     |
| 1099 | 46109   | 0x17DC | 1st Rev Amount | WK160             | R/W     |
| 1100 | 46111   | 0x17DE | 1st Rev Speed  | WK160             | R/W     |
| 1101 | 46113   | 0x17E0 | 2nd Amount     | WK160             | R/W     |
| 1102 | 46115   | 0x17E2 | 2nd Speed      | WK160             | R/W     |
| 1103 | 46117   | 0x17E4 | 2nd Rev Amount | WK160             | R/W     |
| 1104 | 46119   | 0x17E6 | 2nd Rev Speed  | WK160             | R/W     |
| 1105 | 46121   | 0x17E8 | Reserve        | WK160             | R/W     |
| 1106 | 46123   | 0x17EA | Reserve        | WK160             | R/W     |
| 1107 | 46125   | 0x17EC | Reserve        | WK160             | R/W     |
| 1108 | 46127   | 0x17EE | Reserve        | WK160             | R/W     |
| 1109 | 46129   | 0x17F0 | Pre-heat Time  | WK160             | R/W     |
| 1110 | 46131   | 0x17F2 | Heating Time   | WK160             | R/W     |
| 1111 | 46133   | 0x17F4 | Reserve        | WK160             | R/W     |
| 1112 | 46135   | 0x17F6 | Reserve        | WK160             | R/W     |
| 1113 | 46137   | 0x17F8 | SV2 Time       | WK161             | R/W     |
| 1114 | 46139   | 0x17FA | 1st Amount     | WK161             | R/W     |
| 1115 | 46141   | 0x17FC | 1st Speed      | WK161             | R/W     |
| 1116 | 46143   | 0x17FE | 1st Rev Amount | WK161             | R/W     |
| 1117 | 46145   | 0x1800 | 1st Rev Speed  | WK161             | R/W     |
| 1118 | 46147   | 0x1802 | 2nd Amount     | WK161             | R/W     |
| 1119 | 46149   | 0x1804 | 2nd Speed      | WK161             | R/W     |
| 1120 | 46151   | 0x1806 | 2nd Rev Amount | WK161             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1121 | 46153   | 0x1808 | 2nd Rev Speed  | WK161             | R/W     |
| 1122 | 46155   | 0x180A | Reserve        | WK161             | R/W     |
| 1123 | 46157   | 0x180C | Reserve        | WK161             | R/W     |
| 1124 | 46159   | 0x180E | Reserve        | WK161             | R/W     |
| 1125 | 46161   | 0x1810 | Reserve        | WK161             | R/W     |
| 1126 | 46163   | 0x1812 | Pre-heat Time  | WK161             | R/W     |
| 1127 | 46165   | 0x1814 | Heating Time   | WK161             | R/W     |
| 1128 | 46167   | 0x1816 | Reserve        | WK161             | R/W     |
| 1129 | 46169   | 0x1818 | Reserve        | WK161             | R/W     |
| 1130 | 46171   | 0x181A | SV2 Time       | WK162             | R/W     |
| 1131 | 46173   | 0x181C | 1st Amount     | WK162             | R/W     |
| 1132 | 46175   | 0x181E | 1st Speed      | WK162             | R/W     |
| 1133 | 46177   | 0x1820 | 1st Rev Amount | WK162             | R/W     |
| 1134 | 46179   | 0x1822 | 1st Rev Speed  | WK162             | R/W     |
| 1135 | 46181   | 0x1824 | 2nd Amount     | WK162             | R/W     |
| 1136 | 46183   | 0x1826 | 2nd Speed      | WK162             | R/W     |
| 1137 | 46185   | 0x1828 | 2nd Rev Amount | WK162             | R/W     |
| 1138 | 46187   | 0x182A | 2nd Rev Speed  | WK162             | R/W     |
| 1139 | 46189   | 0x182C | Reserve        | WK162             | R/W     |
| 1140 | 46191   | 0x182E | Reserve        | WK162             | R/W     |
| 1141 | 46193   | 0x1830 | Reserve        | WK162             | R/W     |
| 1142 | 46195   | 0x1832 | Reserve        | WK162             | R/W     |
| 1143 | 46197   | 0x1834 | Pre-heat Time  | WK162             | R/W     |
| 1144 | 46199   | 0x1836 | Heating Time   | WK162             | R/W     |
| 1145 | 46201   | 0x1838 | Reserve        | WK162             | R/W     |
| 1146 | 46203   | 0x183A | Reserve        | WK162             | R/W     |
| 1147 | 46205   | 0x183C | SV2 Time       | WK163             | R/W     |
| 1148 | 46207   | 0x183E | 1st Amount     | WK163             | R/W     |
| 1149 | 46209   | 0x1840 | 1st Speed      | WK163             | R/W     |
| 1150 | 46211   | 0x1842 | 1st Rev Amount | WK163             | R/W     |
| 1151 | 46213   | 0x1844 | 1st Rev Speed  | WK163             | R/W     |
| 1152 | 46215   | 0x1846 | 2nd Amount     | WK163             | R/W     |
| 1153 | 46217   | 0x1848 | 2nd Speed      | WK163             | R/W     |
| 1154 | 46219   | 0x184A | 2nd Rev Amount | WK163             | R/W     |
| 1155 | 46221   | 0x184C | 2nd Rev Speed  | WK163             | R/W     |
| 1156 | 46223   | 0x184E | Reserve        | WK163             | R/W     |
| 1157 | 46225   | 0x1850 | Reserve        | WK163             | R/W     |
| 1158 | 46227   | 0x1852 | Reserve        | WK163             | R/W     |
| 1159 | 46229   | 0x1854 | Reserve        | WK163             | R/W     |
| 1160 | 46231   | 0x1856 | Pre-heat Time  | WK163             | R/W     |
| 1161 | 46233   | 0x1858 | Heating Time   | WK163             | R/W     |
| 1162 | 46235   | 0x185A | Reserve        | WK163             | R/W     |
| 1163 | 46237   | 0x185C | Reserve        | WK163             | R/W     |
| 1164 | 46239   | 0x185E | SV2 Time       | WK164             | R/W     |
| 1165 | 46241   | 0x1860 | 1st Amount     | WK164             | R/W     |
| 1166 | 46243   | 0x1862 | 1st Speed      | WK164             | R/W     |
| 1167 | 46245   | 0x1864 | 1st Rev Amount | WK164             | R/W     |
| 1168 | 46247   | 0x1866 | 1st Rev Speed  | WK164             | R/W     |
| 1169 | 46249   | 0x1868 | 2nd Amount     | WK164             | R/W     |
| 1170 | 46251   | 0x186A | 2nd Speed      | WK164             | R/W     |
| 1171 | 46253   | 0x186C | 2nd Rev Amount | WK164             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1172 | 46255   | 0x186E | 2nd Rev Speed  | WK164             | R/W     |
| 1173 | 46257   | 0x1870 | Reserve        | WK164             | R/W     |
| 1174 | 46259   | 0x1872 | Reserve        | WK164             | R/W     |
| 1175 | 46261   | 0x1874 | Reserve        | WK164             | R/W     |
| 1176 | 46263   | 0x1876 | Reserve        | WK164             | R/W     |
| 1177 | 46265   | 0x1878 | Pre-heat Time  | WK164             | R/W     |
| 1178 | 46267   | 0x187A | Heating Time   | WK164             | R/W     |
| 1179 | 46269   | 0x187C | Reserve        | WK164             | R/W     |
| 1180 | 46271   | 0x187E | Reserve        | WK164             | R/W     |
| 1181 | 46273   | 0x1880 | SV2 Time       | WK165             | R/W     |
| 1182 | 46275   | 0x1882 | 1st Amount     | WK165             | R/W     |
| 1183 | 46277   | 0x1884 | 1st Speed      | WK165             | R/W     |
| 1184 | 46279   | 0x1886 | 1st Rev Amount | WK165             | R/W     |
| 1185 | 46281   | 0x1888 | 1st Rev Speed  | WK165             | R/W     |
| 1186 | 46283   | 0x188A | 2nd Amount     | WK165             | R/W     |
| 1187 | 46285   | 0x188C | 2nd Speed      | WK165             | R/W     |
| 1188 | 46287   | 0x188E | 2nd Rev Amount | WK165             | R/W     |
| 1189 | 46289   | 0x1890 | 2nd Rev Speed  | WK165             | R/W     |
| 1190 | 46291   | 0x1892 | Reserve        | WK165             | R/W     |
| 1191 | 46293   | 0x1894 | Reserve        | WK165             | R/W     |
| 1192 | 46295   | 0x1896 | Reserve        | WK165             | R/W     |
| 1193 | 46297   | 0x1898 | Reserve        | WK165             | R/W     |
| 1194 | 46299   | 0x189A | Pre-heat Time  | WK165             | R/W     |
| 1195 | 46301   | 0x189C | Heating Time   | WK165             | R/W     |
| 1196 | 46303   | 0x189E | Reserve        | WK165             | R/W     |
| 1197 | 46305   | 0x18A0 | Reserve        | WK165             | R/W     |
| 1198 | 46307   | 0x18A2 | SV2 Time       | WK166             | R/W     |
| 1199 | 46309   | 0x18A4 | 1st Amount     | WK166             | R/W     |
| 1200 | 46311   | 0x18A6 | 1st Speed      | WK166             | R/W     |
| 1201 | 46313   | 0x18A8 | 1st Rev Amount | WK166             | R/W     |
| 1202 | 46315   | 0x18AA | 1st Rev Speed  | WK166             | R/W     |
| 1203 | 46317   | 0x18AC | 2nd Amount     | WK166             | R/W     |
| 1204 | 46319   | 0x18AE | 2nd Speed      | WK166             | R/W     |
| 1205 | 46321   | 0x18B0 | 2nd Rev Amount | WK166             | R/W     |
| 1206 | 46323   | 0x18B2 | 2nd Rev Speed  | WK166             | R/W     |
| 1207 | 46325   | 0x18B4 | Reserve        | WK166             | R/W     |
| 1208 | 46327   | 0x18B6 | Reserve        | WK166             | R/W     |
| 1209 | 46329   | 0x18B8 | Reserve        | WK166             | R/W     |
| 1210 | 46331   | 0x18BA | Reserve        | WK166             | R/W     |
| 1211 | 46333   | 0x18BC | Pre-heat Time  | WK166             | R/W     |
| 1212 | 46335   | 0x18BE | Heating Time   | WK166             | R/W     |
| 1213 | 46337   | 0x18C0 | Reserve        | WK166             | R/W     |
| 1214 | 46339   | 0x18C2 | Reserve        | WK166             | R/W     |
| 1215 | 46341   | 0x18C4 | SV2 Time       | WK167             | R/W     |
| 1216 | 46343   | 0x18C6 | 1st Amount     | WK167             | R/W     |
| 1217 | 46345   | 0x18C8 | 1st Speed      | WK167             | R/W     |
| 1218 | 46347   | 0x18CA | 1st Rev Amount | WK167             | R/W     |
| 1219 | 46349   | 0x18CC | 1st Rev Speed  | WK167             | R/W     |
| 1220 | 46351   | 0x18CE | 2nd Amount     | WK167             | R/W     |
| 1221 | 46353   | 0x18D0 | 2nd Speed      | WK167             | R/W     |
| 1222 | 46355   | 0x18D2 | 2nd Rev Amount | WK167             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1223 | 46357   | 0x18D4 | 2nd Rev Speed  | WK167             | R/W     |
| 1224 | 46359   | 0x18D6 | Reserve        | WK167             | R/W     |
| 1225 | 46361   | 0x18D8 | Reserve        | WK167             | R/W     |
| 1226 | 46363   | 0x18DA | Reserve        | WK167             | R/W     |
| 1227 | 46365   | 0x18DC | Reserve        | WK167             | R/W     |
| 1228 | 46367   | 0x18DE | Pre-heat Time  | WK167             | R/W     |
| 1229 | 46369   | 0x18E0 | Heating Time   | WK167             | R/W     |
| 1230 | 46371   | 0x18E2 | Reserve        | WK167             | R/W     |
| 1231 | 46373   | 0x18E4 | Reserve        | WK167             | R/W     |
| 1232 | 46375   | 0x18E6 | SV2 Time       | WK168             | R/W     |
| 1233 | 46377   | 0x18E8 | 1st Amount     | WK168             | R/W     |
| 1234 | 46379   | 0x18EA | 1st Speed      | WK168             | R/W     |
| 1235 | 46381   | 0x18EC | 1st Rev Amount | WK168             | R/W     |
| 1236 | 46383   | 0x18EE | 1st Rev Speed  | WK168             | R/W     |
| 1237 | 46385   | 0x18F0 | 2nd Amount     | WK168             | R/W     |
| 1238 | 46387   | 0x18F2 | 2nd Speed      | WK168             | R/W     |
| 1239 | 46389   | 0x18F4 | 2nd Rev Amount | WK168             | R/W     |
| 1240 | 46391   | 0x18F6 | 2nd Rev Speed  | WK168             | R/W     |
| 1241 | 46393   | 0x18F8 | Reserve        | WK168             | R/W     |
| 1242 | 46395   | 0x18FA | Reserve        | WK168             | R/W     |
| 1243 | 46397   | 0x18FC | Reserve        | WK168             | R/W     |
| 1244 | 46399   | 0x18FE | Reserve        | WK168             | R/W     |
| 1245 | 46401   | 0x1900 | Pre-heat Time  | WK168             | R/W     |
| 1246 | 46403   | 0x1902 | Heating Time   | WK168             | R/W     |
| 1247 | 46405   | 0x1904 | Reserve        | WK168             | R/W     |
| 1248 | 46407   | 0x1906 | Reserve        | WK168             | R/W     |
| 1249 | 46409   | 0x1908 | SV2 Time       | WK169             | R/W     |
| 1250 | 46411   | 0x190A | 1st Amount     | WK169             | R/W     |
| 1251 | 46413   | 0x190C | 1st Speed      | WK169             | R/W     |
| 1252 | 46415   | 0x190E | 1st Rev Amount | WK169             | R/W     |
| 1253 | 46417   | 0x1910 | 1st Rev Speed  | WK169             | R/W     |
| 1254 | 46419   | 0x1912 | 2nd Amount     | WK169             | R/W     |
| 1255 | 46421   | 0x1914 | 2nd Speed      | WK169             | R/W     |
| 1256 | 46423   | 0x1916 | 2nd Rev Amount | WK169             | R/W     |
| 1257 | 46425   | 0x1918 | 2nd Rev Speed  | WK169             | R/W     |
| 1258 | 46427   | 0x191A | Reserve        | WK169             | R/W     |
| 1259 | 46429   | 0x191C | Reserve        | WK169             | R/W     |
| 1260 | 46431   | 0x191E | Reserve        | WK169             | R/W     |
| 1261 | 46433   | 0x1920 | Reserve        | WK169             | R/W     |
| 1262 | 46435   | 0x1922 | Pre-heat Time  | WK169             | R/W     |
| 1263 | 46437   | 0x1924 | Heating Time   | WK169             | R/W     |
| 1264 | 46439   | 0x1926 | Reserve        | WK169             | R/W     |
| 1265 | 46441   | 0x1928 | Reserve        | WK169             | R/W     |
| 1266 | 46443   | 0x192A | SV2 Time       | WK170             | R/W     |
| 1267 | 46445   | 0x192C | 1st Amount     | WK170             | R/W     |
| 1268 | 46447   | 0x192E | 1st Speed      | WK170             | R/W     |
| 1269 | 46449   | 0x1930 | 1st Rev Amount | WK170             | R/W     |
| 1270 | 46451   | 0x1932 | 1st Rev Speed  | WK170             | R/W     |
| 1271 | 46453   | 0x1934 | 2nd Amount     | WK170             | R/W     |
| 1272 | 46455   | 0x1936 | 2nd Speed      | WK170             | R/W     |
| 1273 | 46457   | 0x1938 | 2nd Rev Amount | WK170             | R/W     |



| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1274 | 46459   | 0x193A | 2nd Rev Speed  | WK170             | R/W     |
| 1275 | 46461   | 0x193C | Reserve        | WK170             | R/W     |
| 1276 | 46463   | 0x193E | Reserve        | WK170             | R/W     |
| 1277 | 46465   | 0x1940 | Reserve        | WK170             | R/W     |
| 1278 | 46467   | 0x1942 | Reserve        | WK170             | R/W     |
| 1279 | 46469   | 0x1944 | Pre-heat Time  | WK170             | R/W     |
| 1280 | 46471   | 0x1946 | Heating Time   | WK170             | R/W     |
| 1281 | 46473   | 0x1948 | Reserve        | WK170             | R/W     |
| 1282 | 46475   | 0x194A | Reserve        | WK170             | R/W     |
| 1283 | 46477   | 0x194C | SV2 Time       | WK171             | R/W     |
| 1284 | 46479   | 0x194E | 1st Amount     | WK171             | R/W     |
| 1285 | 46481   | 0x1950 | 1st Speed      | WK171             | R/W     |
| 1286 | 46483   | 0x1952 | 1st Rev Amount | WK171             | R/W     |
| 1287 | 46485   | 0x1954 | 1st Rev Speed  | WK171             | R/W     |
| 1288 | 46487   | 0x1956 | 2nd Amount     | WK171             | R/W     |
| 1289 | 46489   | 0x1958 | 2nd Speed      | WK171             | R/W     |
| 1290 | 46491   | 0x195A | 2nd Rev Amount | WK171             | R/W     |
| 1291 | 46493   | 0x195C | 2nd Rev Speed  | WK171             | R/W     |
| 1292 | 46495   | 0x195E | Reserve        | WK171             | R/W     |
| 1293 | 46497   | 0x1960 | Reserve        | WK171             | R/W     |
| 1294 | 46499   | 0x1962 | Reserve        | WK171             | R/W     |
| 1295 | 46501   | 0x1964 | Reserve        | WK171             | R/W     |
| 1296 | 46503   | 0x1966 | Pre-heat Time  | WK171             | R/W     |
| 1297 | 46505   | 0x1968 | Heating Time   | WK171             | R/W     |
| 1298 | 46507   | 0x196A | Reserve        | WK171             | R/W     |
| 1299 | 46509   | 0x196C | Reserve        | WK171             | R/W     |
| 1300 | 46511   | 0x196E | SV2 Time       | WK172             | R/W     |
| 1301 | 46513   | 0x1970 | 1st Amount     | WK172             | R/W     |
| 1302 | 46515   | 0x1972 | 1st Speed      | WK172             | R/W     |
| 1303 | 46517   | 0x1974 | 1st Rev Amount | WK172             | R/W     |
| 1304 | 46519   | 0x1976 | 1st Rev Speed  | WK172             | R/W     |
| 1305 | 46521   | 0x1978 | 2nd Amount     | WK172             | R/W     |
| 1306 | 46523   | 0x197A | 2nd Speed      | WK172             | R/W     |
| 1307 | 46525   | 0x197C | 2nd Rev Amount | WK172             | R/W     |
| 1308 | 46527   | 0x197E | 2nd Rev Speed  | WK172             | R/W     |
| 1309 | 46529   | 0x1980 | Reserve        | WK172             | R/W     |
| 1310 | 46531   | 0x1982 | Reserve        | WK172             | R/W     |
| 1311 | 46533   | 0x1984 | Reserve        | WK172             | R/W     |
| 1312 | 46535   | 0x1986 | Reserve        | WK172             | R/W     |
| 1313 | 46537   | 0x1988 | Pre-heat Time  | WK172             | R/W     |
| 1314 | 46539   | 0x198A | Heating Time   | WK172             | R/W     |
| 1315 | 46541   | 0x198C | Reserve        | WK172             | R/W     |
| 1316 | 46543   | 0x198E | Reserve        | WK172             | R/W     |
| 1317 | 46545   | 0x1990 | SV2 Time       | WK173             | R/W     |
| 1318 | 46547   | 0x1992 | 1st Amount     | WK173             | R/W     |
| 1319 | 46549   | 0x1994 | 1st Speed      | WK173             | R/W     |
| 1320 | 46551   | 0x1996 | 1st Rev Amount | WK173             | R/W     |
| 1321 | 46553   | 0x1998 | 1st Rev Speed  | WK173             | R/W     |
| 1322 | 46555   | 0x199A | 2nd Amount     | WK173             | R/W     |
| 1323 | 46557   | 0x199C | 2nd Speed      | WK173             | R/W     |
| 1324 | 46559   | 0x199E | 2nd Rev Amount | WK173             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1325 | 46561   | 0x19A0 | 2nd Rev Speed  | WK173             | R/W     |
| 1326 | 46563   | 0x19A2 | Reserve        | WK173             | R/W     |
| 1327 | 46565   | 0x19A4 | Reserve        | WK173             | R/W     |
| 1328 | 46567   | 0x19A6 | Reserve        | WK173             | R/W     |
| 1329 | 46569   | 0x19A8 | Reserve        | WK173             | R/W     |
| 1330 | 46571   | 0x19AA | Pre-heat Time  | WK173             | R/W     |
| 1331 | 46573   | 0x19AC | Heating Time   | WK173             | R/W     |
| 1332 | 46575   | 0x19AE | Reserve        | WK173             | R/W     |
| 1333 | 46577   | 0x19B0 | Reserve        | WK173             | R/W     |
| 1334 | 46579   | 0x19B2 | SV2 Time       | WK174             | R/W     |
| 1335 | 46581   | 0x19B4 | 1st Amount     | WK174             | R/W     |
| 1336 | 46583   | 0x19B6 | 1st Speed      | WK174             | R/W     |
| 1337 | 46585   | 0x19B8 | 1st Rev Amount | WK174             | R/W     |
| 1338 | 46587   | 0x19BA | 1st Rev Speed  | WK174             | R/W     |
| 1339 | 46589   | 0x19BC | 2nd Amount     | WK174             | R/W     |
| 1340 | 46591   | 0x19BE | 2nd Speed      | WK174             | R/W     |
| 1341 | 46593   | 0x19C0 | 2nd Rev Amount | WK174             | R/W     |
| 1342 | 46595   | 0x19C2 | 2nd Rev Speed  | WK174             | R/W     |
| 1343 | 46597   | 0x19C4 | Reserve        | WK174             | R/W     |
| 1344 | 46599   | 0x19C6 | Reserve        | WK174             | R/W     |
| 1345 | 46601   | 0x19C8 | Reserve        | WK174             | R/W     |
| 1346 | 46603   | 0x19CA | Reserve        | WK174             | R/W     |
| 1347 | 46605   | 0x19CC | Pre-heat Time  | WK174             | R/W     |
| 1348 | 46607   | 0x19CE | Heating Time   | WK174             | R/W     |
| 1349 | 46609   | 0x19D0 | Reserve        | WK174             | R/W     |
| 1350 | 46611   | 0x19D2 | Reserve        | WK174             | R/W     |
| 1351 | 46613   | 0x19D4 | SV2 Time       | WK175             | R/W     |
| 1352 | 46615   | 0x19D6 | 1st Amount     | WK175             | R/W     |
| 1353 | 46617   | 0x19D8 | 1st Speed      | WK175             | R/W     |
| 1354 | 46619   | 0x19DA | 1st Rev Amount | WK175             | R/W     |
| 1355 | 46621   | 0x19DC | 1st Rev Speed  | WK175             | R/W     |
| 1356 | 46623   | 0x19DE | 2nd Amount     | WK175             | R/W     |
| 1357 | 46625   | 0x19E0 | 2nd Speed      | WK175             | R/W     |
| 1358 | 46627   | 0x19E2 | 2nd Rev Amount | WK175             | R/W     |
| 1359 | 46629   | 0x19E4 | 2nd Rev Speed  | WK175             | R/W     |
| 1360 | 46631   | 0x19E6 | Reserve        | WK175             | R/W     |
| 1361 | 46633   | 0x19E8 | Reserve        | WK175             | R/W     |
| 1362 | 46635   | 0x19EA | Reserve        | WK175             | R/W     |
| 1363 | 46637   | 0x19EC | Reserve        | WK175             | R/W     |
| 1364 | 46639   | 0x19EE | Pre-heat Time  | WK175             | R/W     |
| 1365 | 46641   | 0x19F0 | Heating Time   | WK175             | R/W     |
| 1366 | 46643   | 0x19F2 | Reserve        | WK175             | R/W     |
| 1367 | 46645   | 0x19F4 | Reserve        | WK175             | R/W     |
| 1368 | 46647   | 0x19F6 | SV2 Time       | WK176             | R/W     |
| 1369 | 46649   | 0x19F8 | 1st Amount     | WK176             | R/W     |
| 1370 | 46651   | 0x19FA | 1st Speed      | WK176             | R/W     |
| 1371 | 46653   | 0x19FC | 1st Rev Amount | WK176             | R/W     |
| 1372 | 46655   | 0x19FE | 1st Rev Speed  | WK176             | R/W     |
| 1373 | 46657   | 0x1A00 | 2nd Amount     | WK176             | R/W     |
| 1374 | 46659   | 0x1A02 | 2nd Speed      | WK176             | R/W     |
| 1375 | 46661   | 0x1A04 | 2nd Rev Amount | WK176             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1376 | 46663   | 0x1A06 | 2nd Rev Speed  | WK176             | R/W     |
| 1377 | 46665   | 0x1A08 | Reserve        | WK176             | R/W     |
| 1378 | 46667   | 0x1A0A | Reserve        | WK176             | R/W     |
| 1379 | 46669   | 0x1A0C | Reserve        | WK176             | R/W     |
| 1380 | 46671   | 0x1A0E | Reserve        | WK176             | R/W     |
| 1381 | 46673   | 0x1A10 | Pre-heat Time  | WK176             | R/W     |
| 1382 | 46675   | 0x1A12 | Heating Time   | WK176             | R/W     |
| 1383 | 46677   | 0x1A14 | Reserve        | WK176             | R/W     |
| 1384 | 46679   | 0x1A16 | Reserve        | WK176             | R/W     |
| 1385 | 46681   | 0x1A18 | SV2 Time       | WK177             | R/W     |
| 1386 | 46683   | 0x1A1A | 1st Amount     | WK177             | R/W     |
| 1387 | 46685   | 0x1A1C | 1st Speed      | WK177             | R/W     |
| 1388 | 46687   | 0x1A1E | 1st Rev Amount | WK177             | R/W     |
| 1389 | 46689   | 0x1A20 | 1st Rev Speed  | WK177             | R/W     |
| 1390 | 46691   | 0x1A22 | 2nd Amount     | WK177             | R/W     |
| 1391 | 46693   | 0x1A24 | 2nd Speed      | WK177             | R/W     |
| 1392 | 46695   | 0x1A26 | 2nd Rev Amount | WK177             | R/W     |
| 1393 | 46697   | 0x1A28 | 2nd Rev Speed  | WK177             | R/W     |
| 1394 | 46699   | 0x1A2A | Reserve        | WK177             | R/W     |
| 1395 | 46701   | 0x1A2C | Reserve        | WK177             | R/W     |
| 1396 | 46703   | 0x1A2E | Reserve        | WK177             | R/W     |
| 1397 | 46705   | 0x1A30 | Reserve        | WK177             | R/W     |
| 1398 | 46707   | 0x1A32 | Pre-heat Time  | WK177             | R/W     |
| 1399 | 46709   | 0x1A34 | Heating Time   | WK177             | R/W     |
| 1400 | 46711   | 0x1A36 | Reserve        | WK177             | R/W     |
| 1401 | 46713   | 0x1A38 | Reserve        | WK177             | R/W     |
| 1402 | 46715   | 0x1A3A | SV2 Time       | WK178             | R/W     |
| 1403 | 46717   | 0x1A3C | 1st Amount     | WK178             | R/W     |
| 1404 | 46719   | 0x1A3E | 1st Speed      | WK178             | R/W     |
| 1405 | 46721   | 0x1A40 | 1st Rev Amount | WK178             | R/W     |
| 1406 | 46723   | 0x1A42 | 1st Rev Speed  | WK178             | R/W     |
| 1407 | 46725   | 0x1A44 | 2nd Amount     | WK178             | R/W     |
| 1408 | 46727   | 0x1A46 | 2nd Speed      | WK178             | R/W     |
| 1409 | 46729   | 0x1A48 | 2nd Rev Amount | WK178             | R/W     |
| 1410 | 46731   | 0x1A4A | 2nd Rev Speed  | WK178             | R/W     |
| 1411 | 46733   | 0x1A4C | Reserve        | WK178             | R/W     |
| 1412 | 46735   | 0x1A4E | Reserve        | WK178             | R/W     |
| 1413 | 46737   | 0x1A50 | Reserve        | WK178             | R/W     |
| 1414 | 46739   | 0x1A52 | Reserve        | WK178             | R/W     |
| 1415 | 46741   | 0x1A54 | Pre-heat Time  | WK178             | R/W     |
| 1416 | 46743   | 0x1A56 | Heating Time   | WK178             | R/W     |
| 1417 | 46745   | 0x1A58 | Reserve        | WK178             | R/W     |
| 1418 | 46747   | 0x1A5A | Reserve        | WK178             | R/W     |
| 1419 | 46749   | 0x1A5C | SV2 Time       | WK179             | R/W     |
| 1420 | 46751   | 0x1A5E | 1st Amount     | WK179             | R/W     |
| 1421 | 46753   | 0x1A60 | 1st Speed      | WK179             | R/W     |
| 1422 | 46755   | 0x1A62 | 1st Rev Amount | WK179             | R/W     |
| 1423 | 46757   | 0x1A64 | 1st Rev Speed  | WK179             | R/W     |
| 1424 | 46759   | 0x1A66 | 2nd Amount     | WK179             | R/W     |
| 1425 | 46761   | 0x1A68 | 2nd Speed      | WK179             | R/W     |
| 1426 | 46763   | 0x1A6A | 2nd Rev Amount | WK179             | R/W     |

| No.  | Address |        | Name                 | Reading / Writing | Remarks |
|------|---------|--------|----------------------|-------------------|---------|
|      | DEC     | HEX    |                      |                   |         |
| 1427 | 46765   | 0x1A6C | 2nd Rev Speed WK179  | R/W               |         |
| 1428 | 46767   | 0x1A6E | Reserve WK179        | R/W               |         |
| 1429 | 46769   | 0x1A70 | Reserve WK179        | R/W               |         |
| 1430 | 46771   | 0x1A72 | Reserve WK179        | R/W               |         |
| 1431 | 46773   | 0x1A74 | Reserve WK179        | R/W               |         |
| 1432 | 46775   | 0x1A76 | Pre-heat Time WK179  | R/W               |         |
| 1433 | 46777   | 0x1A78 | Heating Time WK179   | R/W               |         |
| 1434 | 46779   | 0x1A7A | Reserve WK179        | R/W               |         |
| 1435 | 46781   | 0x1A7C | Reserve WK179        | R/W               |         |
| 1436 | 46783   | 0x1A7E | SV2 Time WK180       | R/W               |         |
| 1437 | 46785   | 0x1A80 | 1st Amount WK180     | R/W               |         |
| 1438 | 46787   | 0x1A82 | 1st Speed WK180      | R/W               |         |
| 1439 | 46789   | 0x1A84 | 1st Rev Amount WK180 | R/W               |         |
| 1440 | 46791   | 0x1A86 | 1st Rev Speed WK180  | R/W               |         |
| 1441 | 46793   | 0x1A88 | 2nd Amount WK180     | R/W               |         |
| 1442 | 46795   | 0x1A8A | 2nd Speed WK180      | R/W               |         |
| 1443 | 46797   | 0x1A8C | 2nd Rev Amount WK180 | R/W               |         |
| 1444 | 46799   | 0x1A8E | 2nd Rev Speed WK180  | R/W               |         |
| 1445 | 46801   | 0x1A90 | Reserve WK180        | R/W               |         |
| 1446 | 46803   | 0x1A92 | Reserve WK180        | R/W               |         |
| 1447 | 46805   | 0x1A94 | Reserve WK180        | R/W               |         |
| 1448 | 46807   | 0x1A96 | Reserve WK180        | R/W               |         |
| 1449 | 46809   | 0x1A98 | Pre-heat Time WK180  | R/W               |         |
| 1450 | 46811   | 0x1A9A | Heating Time WK180   | R/W               |         |
| 1451 | 46813   | 0x1A9C | Reserve WK180        | R/W               |         |
| 1452 | 46815   | 0x1A9E | Reserve WK180        | R/W               |         |
| 1453 | 46817   | 0x1AA0 | SV2 Time WK181       | R/W               |         |
| 1454 | 46819   | 0x1AA2 | 1st Amount WK181     | R/W               |         |
| 1455 | 46821   | 0x1AA4 | 1st Speed WK181      | R/W               |         |
| 1456 | 46823   | 0x1AA6 | 1st Rev Amount WK181 | R/W               |         |
| 1457 | 46825   | 0x1AA8 | 1st Rev Speed WK181  | R/W               |         |
| 1458 | 46827   | 0x1AAA | 2nd Amount WK181     | R/W               |         |
| 1459 | 46829   | 0x1AAC | 2nd Speed WK181      | R/W               |         |
| 1460 | 46831   | 0x1AAE | 2nd Rev Amount WK181 | R/W               |         |
| 1461 | 46833   | 0x1AB0 | 2nd Rev Speed WK181  | R/W               |         |
| 1462 | 46835   | 0x1AB2 | Reserve WK181        | R/W               |         |
| 1463 | 46837   | 0x1AB4 | Reserve WK181        | R/W               |         |
| 1464 | 46839   | 0x1AB6 | Reserve WK181        | R/W               |         |
| 1465 | 46841   | 0x1AB8 | Reserve WK181        | R/W               |         |
| 1466 | 46843   | 0x1ABA | Pre-heat Time WK181  | R/W               |         |
| 1467 | 46845   | 0x1ABC | Heating Time WK181   | R/W               |         |
| 1468 | 46847   | 0x1ABE | Reserve WK181        | R/W               |         |
| 1469 | 46849   | 0x1AC0 | Reserve WK181        | R/W               |         |
| 1470 | 46851   | 0x1AC2 | SV2 Time WK182       | R/W               |         |
| 1471 | 46853   | 0x1AC4 | 1st Amount WK182     | R/W               |         |
| 1472 | 46855   | 0x1AC6 | 1st Speed WK182      | R/W               |         |
| 1473 | 46857   | 0x1AC8 | 1st Rev Amount WK182 | R/W               |         |
| 1474 | 46859   | 0x1ACA | 1st Rev Speed WK182  | R/W               |         |
| 1475 | 46861   | 0x1ACC | 2nd Amount WK182     | R/W               |         |
| 1476 | 46863   | 0x1ACE | 2nd Speed WK182      | R/W               |         |
| 1477 | 46865   | 0x1AD0 | 2nd Rev Amount WK182 | R/W               |         |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1478 | 46867   | 0x1AD2 | 2nd Rev Speed  | WK182             | R/W     |
| 1479 | 46869   | 0x1AD4 | Reserve        | WK182             | R/W     |
| 1480 | 46871   | 0x1AD6 | Reserve        | WK182             | R/W     |
| 1481 | 46873   | 0x1AD8 | Reserve        | WK182             | R/W     |
| 1482 | 46875   | 0x1ADA | Reserve        | WK182             | R/W     |
| 1483 | 46877   | 0x1ADC | Pre-heat Time  | WK182             | R/W     |
| 1484 | 46879   | 0x1ADE | Heating Time   | WK182             | R/W     |
| 1485 | 46881   | 0x1AE0 | Reserve        | WK182             | R/W     |
| 1486 | 46883   | 0x1AE2 | Reserve        | WK182             | R/W     |
| 1487 | 46885   | 0x1AE4 | SV2 Time       | WK183             | R/W     |
| 1488 | 46887   | 0x1AE6 | 1st Amount     | WK183             | R/W     |
| 1489 | 46889   | 0x1AE8 | 1st Speed      | WK183             | R/W     |
| 1490 | 46891   | 0x1AEA | 1st Rev Amount | WK183             | R/W     |
| 1491 | 46893   | 0x1AEC | 1st Rev Speed  | WK183             | R/W     |
| 1492 | 46895   | 0x1AEE | 2nd Amount     | WK183             | R/W     |
| 1493 | 46897   | 0x1AF0 | 2nd Speed      | WK183             | R/W     |
| 1494 | 46899   | 0x1AF2 | 2nd Rev Amount | WK183             | R/W     |
| 1495 | 46901   | 0x1AF4 | 2nd Rev Speed  | WK183             | R/W     |
| 1496 | 46903   | 0x1AF6 | Reserve        | WK183             | R/W     |
| 1497 | 46905   | 0x1AF8 | Reserve        | WK183             | R/W     |
| 1498 | 46907   | 0x1AFA | Reserve        | WK183             | R/W     |
| 1499 | 46909   | 0x1AFC | Reserve        | WK183             | R/W     |
| 1500 | 46911   | 0x1AFE | Pre-heat Time  | WK183             | R/W     |
| 1501 | 46913   | 0x1B00 | Heating Time   | WK183             | R/W     |
| 1502 | 46915   | 0x1B02 | Reserve        | WK183             | R/W     |
| 1503 | 46917   | 0x1B04 | Reserve        | WK183             | R/W     |
| 1504 | 46919   | 0x1B06 | SV2 Time       | WK184             | R/W     |
| 1505 | 46921   | 0x1B08 | 1st Amount     | WK184             | R/W     |
| 1506 | 46923   | 0x1B0A | 1st Speed      | WK184             | R/W     |
| 1507 | 46925   | 0x1B0C | 1st Rev Amount | WK184             | R/W     |
| 1508 | 46927   | 0x1B0E | 1st Rev Speed  | WK184             | R/W     |
| 1509 | 46929   | 0x1B10 | 2nd Amount     | WK184             | R/W     |
| 1510 | 46931   | 0x1B12 | 2nd Speed      | WK184             | R/W     |
| 1511 | 46933   | 0x1B14 | 2nd Rev Amount | WK184             | R/W     |
| 1512 | 46935   | 0x1B16 | 2nd Rev Speed  | WK184             | R/W     |
| 1513 | 46937   | 0x1B18 | Reserve        | WK184             | R/W     |
| 1514 | 46939   | 0x1B1A | Reserve        | WK184             | R/W     |
| 1515 | 46941   | 0x1B1C | Reserve        | WK184             | R/W     |
| 1516 | 46943   | 0x1B1E | Reserve        | WK184             | R/W     |
| 1517 | 46945   | 0x1B20 | Pre-heat Time  | WK184             | R/W     |
| 1518 | 46947   | 0x1B22 | Heating Time   | WK184             | R/W     |
| 1519 | 46949   | 0x1B24 | Reserve        | WK184             | R/W     |
| 1520 | 46951   | 0x1B26 | Reserve        | WK184             | R/W     |
| 1521 | 46953   | 0x1B28 | SV2 Time       | WK185             | R/W     |
| 1522 | 46955   | 0x1B2A | 1st Amount     | WK185             | R/W     |
| 1523 | 46957   | 0x1B2C | 1st Speed      | WK185             | R/W     |
| 1524 | 46959   | 0x1B2E | 1st Rev Amount | WK185             | R/W     |
| 1525 | 46961   | 0x1B30 | 1st Rev Speed  | WK185             | R/W     |
| 1526 | 46963   | 0x1B32 | 2nd Amount     | WK185             | R/W     |
| 1527 | 46965   | 0x1B34 | 2nd Speed      | WK185             | R/W     |
| 1528 | 46967   | 0x1B36 | 2nd Rev Amount | WK185             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1529 | 46969   | 0x1B38 | 2nd Rev Speed  | WK185             | R/W     |
| 1530 | 46971   | 0x1B3A | Reserve        | WK185             | R/W     |
| 1531 | 46973   | 0x1B3C | Reserve        | WK185             | R/W     |
| 1532 | 46975   | 0x1B3E | Reserve        | WK185             | R/W     |
| 1533 | 46977   | 0x1B40 | Reserve        | WK185             | R/W     |
| 1534 | 46979   | 0x1B42 | Pre-heat Time  | WK185             | R/W     |
| 1535 | 46981   | 0x1B44 | Heating Time   | WK185             | R/W     |
| 1536 | 46983   | 0x1B46 | Reserve        | WK185             | R/W     |
| 1537 | 46985   | 0x1B48 | Reserve        | WK185             | R/W     |
| 1538 | 46987   | 0x1B4A | SV2 Time       | WK186             | R/W     |
| 1539 | 46989   | 0x1B4C | 1st Amount     | WK186             | R/W     |
| 1540 | 46991   | 0x1B4E | 1st Speed      | WK186             | R/W     |
| 1541 | 46993   | 0x1B50 | 1st Rev Amount | WK186             | R/W     |
| 1542 | 46995   | 0x1B52 | 1st Rev Speed  | WK186             | R/W     |
| 1543 | 46997   | 0x1B54 | 2nd Amount     | WK186             | R/W     |
| 1544 | 46999   | 0x1B56 | 2nd Speed      | WK186             | R/W     |
| 1545 | 47001   | 0x1B58 | 2nd Rev Amount | WK186             | R/W     |
| 1546 | 47003   | 0x1B5A | 2nd Rev Speed  | WK186             | R/W     |
| 1547 | 47005   | 0x1B5C | Reserve        | WK186             | R/W     |
| 1548 | 47007   | 0x1B5E | Reserve        | WK186             | R/W     |
| 1549 | 47009   | 0x1B60 | Reserve        | WK186             | R/W     |
| 1550 | 47011   | 0x1B62 | Reserve        | WK186             | R/W     |
| 1551 | 47013   | 0x1B64 | Pre-heat Time  | WK186             | R/W     |
| 1552 | 47015   | 0x1B66 | Heating Time   | WK186             | R/W     |
| 1553 | 47017   | 0x1B68 | Reserve        | WK186             | R/W     |
| 1554 | 47019   | 0x1B6A | Reserve        | WK186             | R/W     |
| 1555 | 47021   | 0x1B6C | SV2 Time       | WK187             | R/W     |
| 1556 | 47023   | 0x1B6E | 1st Amount     | WK187             | R/W     |
| 1557 | 47025   | 0x1B70 | 1st Speed      | WK187             | R/W     |
| 1558 | 47027   | 0x1B72 | 1st Rev Amount | WK187             | R/W     |
| 1559 | 47029   | 0x1B74 | 1st Rev Speed  | WK187             | R/W     |
| 1560 | 47031   | 0x1B76 | 2nd Amount     | WK187             | R/W     |
| 1561 | 47033   | 0x1B78 | 2nd Speed      | WK187             | R/W     |
| 1562 | 47035   | 0x1B7A | 2nd Rev Amount | WK187             | R/W     |
| 1563 | 47037   | 0x1B7C | 2nd Rev Speed  | WK187             | R/W     |
| 1564 | 47039   | 0x1B7E | Reserve        | WK187             | R/W     |
| 1565 | 47041   | 0x1B80 | Reserve        | WK187             | R/W     |
| 1566 | 47043   | 0x1B82 | Reserve        | WK187             | R/W     |
| 1567 | 47045   | 0x1B84 | Reserve        | WK187             | R/W     |
| 1568 | 47047   | 0x1B86 | Pre-heat Time  | WK187             | R/W     |
| 1569 | 47049   | 0x1B88 | Heating Time   | WK187             | R/W     |
| 1570 | 47051   | 0x1B8A | Reserve        | WK187             | R/W     |
| 1571 | 47053   | 0x1B8C | Reserve        | WK187             | R/W     |
| 1572 | 47055   | 0x1B8E | SV2 Time       | WK188             | R/W     |
| 1573 | 47057   | 0x1B90 | 1st Amount     | WK188             | R/W     |
| 1574 | 47059   | 0x1B92 | 1st Speed      | WK188             | R/W     |
| 1575 | 47061   | 0x1B94 | 1st Rev Amount | WK188             | R/W     |
| 1576 | 47063   | 0x1B96 | 1st Rev Speed  | WK188             | R/W     |
| 1577 | 47065   | 0x1B98 | 2nd Amount     | WK188             | R/W     |
| 1578 | 47067   | 0x1B9A | 2nd Speed      | WK188             | R/W     |
| 1579 | 47069   | 0x1B9C | 2nd Rev Amount | WK188             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1580 | 47071   | 0x1B9E | 2nd Rev Speed  | WK188             | R/W     |
| 1581 | 47073   | 0x1BA0 | Reserve        | WK188             | R/W     |
| 1582 | 47075   | 0x1BA2 | Reserve        | WK188             | R/W     |
| 1583 | 47077   | 0x1BA4 | Reserve        | WK188             | R/W     |
| 1584 | 47079   | 0x1BA6 | Reserve        | WK188             | R/W     |
| 1585 | 47081   | 0x1BA8 | Pre-heat Time  | WK188             | R/W     |
| 1586 | 47083   | 0x1BAA | Heating Time   | WK188             | R/W     |
| 1587 | 47085   | 0x1BAC | Reserve        | WK188             | R/W     |
| 1588 | 47087   | 0x1BAE | Reserve        | WK188             | R/W     |
| 1589 | 47089   | 0x1BB0 | SV2 Time       | WK189             | R/W     |
| 1590 | 47091   | 0x1BB2 | 1st Amount     | WK189             | R/W     |
| 1591 | 47093   | 0x1BB4 | 1st Speed      | WK189             | R/W     |
| 1592 | 47095   | 0x1BB6 | 1st Rev Amount | WK189             | R/W     |
| 1593 | 47097   | 0x1BB8 | 1st Rev Speed  | WK189             | R/W     |
| 1594 | 47099   | 0x1BBA | 2nd Amount     | WK189             | R/W     |
| 1595 | 47101   | 0x1BBC | 2nd Speed      | WK189             | R/W     |
| 1596 | 47103   | 0x1BBE | 2nd Rev Amount | WK189             | R/W     |
| 1597 | 47105   | 0x1BC0 | 2nd Rev Speed  | WK189             | R/W     |
| 1598 | 47107   | 0x1BC2 | Reserve        | WK189             | R/W     |
| 1599 | 47109   | 0x1BC4 | Reserve        | WK189             | R/W     |
| 1600 | 47111   | 0x1BC6 | Reserve        | WK189             | R/W     |
| 1601 | 47113   | 0x1BC8 | Reserve        | WK189             | R/W     |
| 1602 | 47115   | 0x1BCA | Pre-heat Time  | WK189             | R/W     |
| 1603 | 47117   | 0x1BCC | Heating Time   | WK189             | R/W     |
| 1604 | 47119   | 0x1BCE | Reserve        | WK189             | R/W     |
| 1605 | 47121   | 0x1BD0 | Reserve        | WK189             | R/W     |
| 1606 | 47123   | 0x1BD2 | SV2 Time       | WK190             | R/W     |
| 1607 | 47125   | 0x1BD4 | 1st Amount     | WK190             | R/W     |
| 1608 | 47127   | 0x1BD6 | 1st Speed      | WK190             | R/W     |
| 1609 | 47129   | 0x1BD8 | 1st Rev Amount | WK190             | R/W     |
| 1610 | 47131   | 0x1BDA | 1st Rev Speed  | WK190             | R/W     |
| 1611 | 47133   | 0x1BDC | 2nd Amount     | WK190             | R/W     |
| 1612 | 47135   | 0x1BDE | 2nd Speed      | WK190             | R/W     |
| 1613 | 47137   | 0x1BE0 | 2nd Rev Amount | WK190             | R/W     |
| 1614 | 47139   | 0x1BE2 | 2nd Rev Speed  | WK190             | R/W     |
| 1615 | 47141   | 0x1BE4 | Reserve        | WK190             | R/W     |
| 1616 | 47143   | 0x1BE6 | Reserve        | WK190             | R/W     |
| 1617 | 47145   | 0x1BE8 | Reserve        | WK190             | R/W     |
| 1618 | 47147   | 0x1BEA | Reserve        | WK190             | R/W     |
| 1619 | 47149   | 0x1BEC | Pre-heat Time  | WK190             | R/W     |
| 1620 | 47151   | 0x1BEE | Heating Time   | WK190             | R/W     |
| 1621 | 47153   | 0x1BF0 | Reserve        | WK190             | R/W     |
| 1622 | 47155   | 0x1BF2 | Reserve        | WK190             | R/W     |
| 1623 | 47157   | 0x1BF4 | SV2 Time       | WK191             | R/W     |
| 1624 | 47159   | 0x1BF6 | 1st Amount     | WK191             | R/W     |
| 1625 | 47161   | 0x1BF8 | 1st Speed      | WK191             | R/W     |
| 1626 | 47163   | 0x1BFA | 1st Rev Amount | WK191             | R/W     |
| 1627 | 47165   | 0x1BFC | 1st Rev Speed  | WK191             | R/W     |
| 1628 | 47167   | 0x1BFE | 2nd Amount     | WK191             | R/W     |
| 1629 | 47169   | 0x1C00 | 2nd Speed      | WK191             | R/W     |
| 1630 | 47171   | 0x1C02 | 2nd Rev Amount | WK191             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1631 | 47173   | 0x1C04 | 2nd Rev Speed  | WK191             | R/W     |
| 1632 | 47175   | 0x1C06 | Reserve        | WK191             | R/W     |
| 1633 | 47177   | 0x1C08 | Reserve        | WK191             | R/W     |
| 1634 | 47179   | 0x1C0A | Reserve        | WK191             | R/W     |
| 1635 | 47181   | 0x1C0C | Reserve        | WK191             | R/W     |
| 1636 | 47183   | 0x1C0E | Pre-heat Time  | WK191             | R/W     |
| 1637 | 47185   | 0x1C10 | Heating Time   | WK191             | R/W     |
| 1638 | 47187   | 0x1C12 | Reserve        | WK191             | R/W     |
| 1639 | 47189   | 0x1C14 | Reserve        | WK191             | R/W     |
| 1640 | 47191   | 0x1C16 | SV2 Time       | WK192             | R/W     |
| 1641 | 47193   | 0x1C18 | 1st Amount     | WK192             | R/W     |
| 1642 | 47195   | 0x1C1A | 1st Speed      | WK192             | R/W     |
| 1643 | 47197   | 0x1C1C | 1st Rev Amount | WK192             | R/W     |
| 1644 | 47199   | 0x1C1E | 1st Rev Speed  | WK192             | R/W     |
| 1645 | 47201   | 0x1C20 | 2nd Amount     | WK192             | R/W     |
| 1646 | 47203   | 0x1C22 | 2nd Speed      | WK192             | R/W     |
| 1647 | 47205   | 0x1C24 | 2nd Rev Amount | WK192             | R/W     |
| 1648 | 47207   | 0x1C26 | 2nd Rev Speed  | WK192             | R/W     |
| 1649 | 47209   | 0x1C28 | Reserve        | WK192             | R/W     |
| 1650 | 47211   | 0x1C2A | Reserve        | WK192             | R/W     |
| 1651 | 47213   | 0x1C2C | Reserve        | WK192             | R/W     |
| 1652 | 47215   | 0x1C2E | Reserve        | WK192             | R/W     |
| 1653 | 47217   | 0x1C30 | Pre-heat Time  | WK192             | R/W     |
| 1654 | 47219   | 0x1C32 | Heating Time   | WK192             | R/W     |
| 1655 | 47221   | 0x1C34 | Reserve        | WK192             | R/W     |
| 1656 | 47223   | 0x1C36 | Reserve        | WK192             | R/W     |
| 1657 | 47225   | 0x1C38 | SV2 Time       | WK193             | R/W     |
| 1658 | 47227   | 0x1C3A | 1st Amount     | WK193             | R/W     |
| 1659 | 47229   | 0x1C3C | 1st Speed      | WK193             | R/W     |
| 1660 | 47231   | 0x1C3E | 1st Rev Amount | WK193             | R/W     |
| 1661 | 47233   | 0x1C40 | 1st Rev Speed  | WK193             | R/W     |
| 1662 | 47235   | 0x1C42 | 2nd Amount     | WK193             | R/W     |
| 1663 | 47237   | 0x1C44 | 2nd Speed      | WK193             | R/W     |
| 1664 | 47239   | 0x1C46 | 2nd Rev Amount | WK193             | R/W     |
| 1665 | 47241   | 0x1C48 | 2nd Rev Speed  | WK193             | R/W     |
| 1666 | 47243   | 0x1C4A | Reserve        | WK193             | R/W     |
| 1667 | 47245   | 0x1C4C | Reserve        | WK193             | R/W     |
| 1668 | 47247   | 0x1C4E | Reserve        | WK193             | R/W     |
| 1669 | 47249   | 0x1C50 | Reserve        | WK193             | R/W     |
| 1670 | 47251   | 0x1C52 | Pre-heat Time  | WK193             | R/W     |
| 1671 | 47253   | 0x1C54 | Heating Time   | WK193             | R/W     |
| 1672 | 47255   | 0x1C56 | Reserve        | WK193             | R/W     |
| 1673 | 47257   | 0x1C58 | Reserve        | WK193             | R/W     |
| 1674 | 47259   | 0x1C5A | SV2 Time       | WK194             | R/W     |
| 1675 | 47261   | 0x1C5C | 1st Amount     | WK194             | R/W     |
| 1676 | 47263   | 0x1C5E | 1st Speed      | WK194             | R/W     |
| 1677 | 47265   | 0x1C60 | 1st Rev Amount | WK194             | R/W     |
| 1678 | 47267   | 0x1C62 | 1st Rev Speed  | WK194             | R/W     |
| 1679 | 47269   | 0x1C64 | 2nd Amount     | WK194             | R/W     |
| 1680 | 47271   | 0x1C66 | 2nd Speed      | WK194             | R/W     |
| 1681 | 47273   | 0x1C68 | 2nd Rev Amount | WK194             | R/W     |



| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1682 | 47275   | 0x1C6A | 2nd Rev Speed  | WK194             | R/W     |
| 1683 | 47277   | 0x1C6C | Reserve        | WK194             | R/W     |
| 1684 | 47279   | 0x1C6E | Reserve        | WK194             | R/W     |
| 1685 | 47281   | 0x1C70 | Reserve        | WK194             | R/W     |
| 1686 | 47283   | 0x1C72 | Reserve        | WK194             | R/W     |
| 1687 | 47285   | 0x1C74 | Pre-heat Time  | WK194             | R/W     |
| 1688 | 47287   | 0x1C76 | Heating Time   | WK194             | R/W     |
| 1689 | 47289   | 0x1C78 | Reserve        | WK194             | R/W     |
| 1690 | 47291   | 0x1C7A | Reserve        | WK194             | R/W     |
| 1691 | 47293   | 0x1C7C | SV2 Time       | WK195             | R/W     |
| 1692 | 47295   | 0x1C7E | 1st Amount     | WK195             | R/W     |
| 1693 | 47297   | 0x1C80 | 1st Speed      | WK195             | R/W     |
| 1694 | 47299   | 0x1C82 | 1st Rev Amount | WK195             | R/W     |
| 1695 | 47301   | 0x1C84 | 1st Rev Speed  | WK195             | R/W     |
| 1696 | 47303   | 0x1C86 | 2nd Amount     | WK195             | R/W     |
| 1697 | 47305   | 0x1C88 | 2nd Speed      | WK195             | R/W     |
| 1698 | 47307   | 0x1C8A | 2nd Rev Amount | WK195             | R/W     |
| 1699 | 47309   | 0x1C8C | 2nd Rev Speed  | WK195             | R/W     |
| 1700 | 47311   | 0x1C8E | Reserve        | WK195             | R/W     |
| 1701 | 47313   | 0x1C90 | Reserve        | WK195             | R/W     |
| 1702 | 47315   | 0x1C92 | Reserve        | WK195             | R/W     |
| 1703 | 47317   | 0x1C94 | Reserve        | WK195             | R/W     |
| 1704 | 47319   | 0x1C96 | Pre-heat Time  | WK195             | R/W     |
| 1705 | 47321   | 0x1C98 | Heating Time   | WK195             | R/W     |
| 1706 | 47323   | 0x1C9A | Reserve        | WK195             | R/W     |
| 1707 | 47325   | 0x1C9C | Reserve        | WK195             | R/W     |
| 1708 | 47327   | 0x1C9E | SV2 Time       | WK196             | R/W     |
| 1709 | 47329   | 0x1CA0 | 1st Amount     | WK196             | R/W     |
| 1710 | 47331   | 0x1CA2 | 1st Speed      | WK196             | R/W     |
| 1711 | 47333   | 0x1CA4 | 1st Rev Amount | WK196             | R/W     |
| 1712 | 47335   | 0x1CA6 | 1st Rev Speed  | WK196             | R/W     |
| 1713 | 47337   | 0x1CA8 | 2nd Amount     | WK196             | R/W     |
| 1714 | 47339   | 0x1CAA | 2nd Speed      | WK196             | R/W     |
| 1715 | 47341   | 0x1CAC | 2nd Rev Amount | WK196             | R/W     |
| 1716 | 47343   | 0x1CAE | 2nd Rev Speed  | WK196             | R/W     |
| 1717 | 47345   | 0x1CB0 | Reserve        | WK196             | R/W     |
| 1718 | 47347   | 0x1CB2 | Reserve        | WK196             | R/W     |
| 1719 | 47349   | 0x1CB4 | Reserve        | WK196             | R/W     |
| 1720 | 47351   | 0x1CB6 | Reserve        | WK196             | R/W     |
| 1721 | 47353   | 0x1CB8 | Pre-heat Time  | WK196             | R/W     |
| 1722 | 47355   | 0x1CBA | Heating Time   | WK196             | R/W     |
| 1723 | 47357   | 0x1CBC | Reserve        | WK196             | R/W     |
| 1724 | 47359   | 0x1CBE | Reserve        | WK196             | R/W     |
| 1725 | 47361   | 0x1CC0 | SV2 Time       | WK197             | R/W     |
| 1726 | 47363   | 0x1CC2 | 1st Amount     | WK197             | R/W     |
| 1727 | 47365   | 0x1CC4 | 1st Speed      | WK197             | R/W     |
| 1728 | 47367   | 0x1CC6 | 1st Rev Amount | WK197             | R/W     |
| 1729 | 47369   | 0x1CC8 | 1st Rev Speed  | WK197             | R/W     |
| 1730 | 47371   | 0x1CCA | 2nd Amount     | WK197             | R/W     |
| 1731 | 47373   | 0x1CCC | 2nd Speed      | WK197             | R/W     |
| 1732 | 47375   | 0x1CCE | 2nd Rev Amount | WK197             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1733 | 47377   | 0x1CD0 | 2nd Rev Speed  | WK197             | R/W     |
| 1734 | 47379   | 0x1CD2 | Reserve        | WK197             | R/W     |
| 1735 | 47381   | 0x1CD4 | Reserve        | WK197             | R/W     |
| 1736 | 47383   | 0x1CD6 | Reserve        | WK197             | R/W     |
| 1737 | 47385   | 0x1CD8 | Reserve        | WK197             | R/W     |
| 1738 | 47387   | 0x1CDA | Pre-heat Time  | WK197             | R/W     |
| 1739 | 47389   | 0x1CDC | Heating Time   | WK197             | R/W     |
| 1740 | 47391   | 0x1CDE | Reserve        | WK197             | R/W     |
| 1741 | 47393   | 0x1CE0 | Reserve        | WK197             | R/W     |
| 1742 | 47395   | 0x1CE2 | SV2 Time       | WK198             | R/W     |
| 1743 | 47397   | 0x1CE4 | 1st Amount     | WK198             | R/W     |
| 1744 | 47399   | 0x1CE6 | 1st Speed      | WK198             | R/W     |
| 1745 | 47401   | 0x1CE8 | 1st Rev Amount | WK198             | R/W     |
| 1746 | 47403   | 0x1CEA | 1st Rev Speed  | WK198             | R/W     |
| 1747 | 47405   | 0x1CEC | 2nd Amount     | WK198             | R/W     |
| 1748 | 47407   | 0x1CEE | 2nd Speed      | WK198             | R/W     |
| 1749 | 47409   | 0x1CF0 | 2nd Rev Amount | WK198             | R/W     |
| 1750 | 47411   | 0x1CF2 | 2nd Rev Speed  | WK198             | R/W     |
| 1751 | 47413   | 0x1CF4 | Reserve        | WK198             | R/W     |
| 1752 | 47415   | 0x1CF6 | Reserve        | WK198             | R/W     |
| 1753 | 47417   | 0x1CF8 | Reserve        | WK198             | R/W     |
| 1754 | 47419   | 0x1CFA | Reserve        | WK198             | R/W     |
| 1755 | 47421   | 0x1CFC | Pre-heat Time  | WK198             | R/W     |
| 1756 | 47423   | 0x1CFE | Heating Time   | WK198             | R/W     |
| 1757 | 47425   | 0x1D00 | Reserve        | WK198             | R/W     |
| 1758 | 47427   | 0x1D02 | Reserve        | WK198             | R/W     |
| 1759 | 47429   | 0x1D04 | SV2 Time       | WK199             | R/W     |
| 1760 | 47431   | 0x1D06 | 1st Amount     | WK199             | R/W     |
| 1761 | 47433   | 0x1D08 | 1st Speed      | WK199             | R/W     |
| 1762 | 47435   | 0x1D0A | 1st Rev Amount | WK199             | R/W     |
| 1763 | 47437   | 0x1D0C | 1st Rev Speed  | WK199             | R/W     |
| 1764 | 47439   | 0x1D0E | 2nd Amount     | WK199             | R/W     |
| 1765 | 47441   | 0x1D10 | 2nd Speed      | WK199             | R/W     |
| 1766 | 47443   | 0x1D12 | 2nd Rev Amount | WK199             | R/W     |
| 1767 | 47445   | 0x1D14 | 2nd Rev Speed  | WK199             | R/W     |
| 1768 | 47447   | 0x1D16 | Reserve        | WK199             | R/W     |
| 1769 | 47449   | 0x1D18 | Reserve        | WK199             | R/W     |
| 1770 | 47451   | 0x1D1A | Reserve        | WK199             | R/W     |
| 1771 | 47453   | 0x1D1C | Reserve        | WK199             | R/W     |
| 1772 | 47455   | 0x1D1E | Pre-heat Time  | WK199             | R/W     |
| 1773 | 47457   | 0x1D20 | Heating Time   | WK199             | R/W     |
| 1774 | 47459   | 0x1D22 | Reserve        | WK199             | R/W     |
| 1775 | 47461   | 0x1D24 | Reserve        | WK199             | R/W     |
| 1776 | 47463   | 0x1D26 |                |                   |         |
| 1777 | 47465   | 0x1D28 |                |                   |         |
| 1778 | 47467   | 0x1D2A |                |                   |         |
| 1779 | 47469   | 0x1D2C |                |                   |         |
| 1780 | 47471   | 0x1D2E |                |                   |         |
| 1781 |         |        |                |                   |         |
| 1782 | 48193   | 0x2000 | SV2 Time       | WK201             | R/W     |
| 1783 | 48195   | 0x2002 | 1st Amount     | WK201             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1784 | 48197   | 0x2004 | 1st Speed      | WK201             | R/W     |
| 1785 | 48199   | 0x2006 | 1st Rev Amount | WK201             | R/W     |
| 1786 | 48201   | 0x2008 | 1st Rev Speed  | WK201             | R/W     |
| 1787 | 48203   | 0x200A | 2nd Amount     | WK201             | R/W     |
| 1788 | 48205   | 0x200C | 2nd Speed      | WK201             | R/W     |
| 1789 | 48207   | 0x200E | 2nd Rev Amount | WK201             | R/W     |
| 1790 | 48209   | 0x2010 | 2nd Rev Speed  | WK201             | R/W     |
| 1791 | 48211   | 0x2012 | 3rd Amount     | WK201             | R/W     |
| 1792 | 48213   | 0x2014 | 3rd Speed      | WK201             | R/W     |
| 1793 | 48215   | 0x2016 | 3rd Rev Amount | WK201             | R/W     |
| 1794 | 48217   | 0x2018 | 3rd Rev Speed  | WK201             | R/W     |
| 1795 | 48219   | 0x201A | Pre-heat Time  | WK201             | R/W     |
| 1796 | 48221   | 0x201C | Heating Time   | WK201             | R/W     |
| 1797 | 48223   | 0x201E | Reserve        | WK201             | R/W     |
| 1798 | 48225   | 0x2020 | Reserve        | WK201             | R/W     |
| 1799 | 48227   | 0x2022 | SV2 Time       | WK202             | R/W     |
| 1800 | 48229   | 0x2024 | 1st Amount     | WK202             | R/W     |
| 1801 | 48231   | 0x2026 | 1st Speed      | WK202             | R/W     |
| 1802 | 48233   | 0x2028 | 1st Rev Amount | WK202             | R/W     |
| 1803 | 48235   | 0x202A | 1st Rev Speed  | WK202             | R/W     |
| 1804 | 48237   | 0x202C | 2nd Amount     | WK202             | R/W     |
| 1805 | 48239   | 0x202E | 2nd Speed      | WK202             | R/W     |
| 1806 | 48241   | 0x2030 | 2nd Rev Amount | WK202             | R/W     |
| 1807 | 48243   | 0x2032 | 2nd Rev Speed  | WK202             | R/W     |
| 1808 | 48245   | 0x2034 | 3rd Amount     | WK202             | R/W     |
| 1809 | 48247   | 0x2036 | 3rd Speed      | WK202             | R/W     |
| 1810 | 48249   | 0x2038 | 3rd Rev Amount | WK202             | R/W     |
| 1811 | 48251   | 0x203A | 3rd Rev Speed  | WK202             | R/W     |
| 1812 | 48253   | 0x203C | Pre-heat Time  | WK202             | R/W     |
| 1813 | 48255   | 0x203E | Heating Time   | WK202             | R/W     |
| 1814 | 48257   | 0x2040 | Reserve        | WK202             | R/W     |
| 1815 | 48259   | 0x2042 | Reserve        | WK202             | R/W     |
| 1816 | 48261   | 0x2044 | SV2 Time       | WK203             | R/W     |
| 1817 | 48263   | 0x2046 | 1st Amount     | WK203             | R/W     |
| 1818 | 48265   | 0x2048 | 1st Speed      | WK203             | R/W     |
| 1819 | 48267   | 0x204A | 1st Rev Amount | WK203             | R/W     |
| 1820 | 48269   | 0x204C | 1st Rev Speed  | WK203             | R/W     |
| 1821 | 48271   | 0x204E | 2nd Amount     | WK203             | R/W     |
| 1822 | 48273   | 0x2050 | 2nd Speed      | WK203             | R/W     |
| 1823 | 48275   | 0x2052 | 2nd Rev Amount | WK203             | R/W     |
| 1824 | 48277   | 0x2054 | 2nd Rev Speed  | WK203             | R/W     |
| 1825 | 48279   | 0x2056 | 3rd Amount     | WK203             | R/W     |
| 1826 | 48281   | 0x2058 | 3rd Speed      | WK203             | R/W     |
| 1827 | 48283   | 0x205A | 3rd Rev Amount | WK203             | R/W     |
| 1828 | 48285   | 0x205C | 3rd Rev Speed  | WK203             | R/W     |
| 1829 | 48287   | 0x205E | Pre-heat Time  | WK203             | R/W     |
| 1830 | 48289   | 0x2060 | Heating Time   | WK203             | R/W     |
| 1831 | 48291   | 0x2062 | Reserve        | WK203             | R/W     |
| 1832 | 48293   | 0x2064 | Reserve        | WK203             | R/W     |
| 1833 | 48295   | 0x2066 | SV2 Time       | WK204             | R/W     |
| 1834 | 48297   | 0x2068 | 1st Amount     | WK204             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1835 | 48299   | 0x206A | 1st Speed      | WK204             | R/W     |
| 1836 | 48301   | 0x206C | 1st Rev Amount | WK204             | R/W     |
| 1837 | 48303   | 0x206E | 1st Rev Speed  | WK204             | R/W     |
| 1838 | 48305   | 0x2070 | 2nd Amount     | WK204             | R/W     |
| 1839 | 48307   | 0x2072 | 2nd Speed      | WK204             | R/W     |
| 1840 | 48309   | 0x2074 | 2nd Rev Amount | WK204             | R/W     |
| 1841 | 48311   | 0x2076 | 2nd Rev Speed  | WK204             | R/W     |
| 1842 | 48313   | 0x2078 | 3rd Amount     | WK204             | R/W     |
| 1843 | 48315   | 0x207A | 3rd Speed      | WK204             | R/W     |
| 1844 | 48317   | 0x207C | 3rd Rev Amount | WK204             | R/W     |
| 1845 | 48319   | 0x207E | 3rd Rev Speed  | WK204             | R/W     |
| 1846 | 48321   | 0x2080 | Pre-heat Time  | WK204             | R/W     |
| 1847 | 48323   | 0x2082 | Heating Time   | WK204             | R/W     |
| 1848 | 48325   | 0x2084 | Reserve        | WK204             | R/W     |
| 1849 | 48327   | 0x2086 | Reserve        | WK204             | R/W     |
| 1850 | 48329   | 0x2088 | SV2 Time       | WK205             | R/W     |
| 1851 | 48331   | 0x208A | 1st Amount     | WK205             | R/W     |
| 1852 | 48333   | 0x208C | 1st Speed      | WK205             | R/W     |
| 1853 | 48335   | 0x208E | 1st Rev Amount | WK205             | R/W     |
| 1854 | 48337   | 0x2090 | 1st Rev Speed  | WK205             | R/W     |
| 1855 | 48339   | 0x2092 | 2nd Amount     | WK205             | R/W     |
| 1856 | 48341   | 0x2094 | 2nd Speed      | WK205             | R/W     |
| 1857 | 48343   | 0x2096 | 2nd Rev Amount | WK205             | R/W     |
| 1858 | 48345   | 0x2098 | 2nd Rev Speed  | WK205             | R/W     |
| 1859 | 48347   | 0x209A | 3rd Amount     | WK205             | R/W     |
| 1860 | 48349   | 0x209C | 3rd Speed      | WK205             | R/W     |
| 1861 | 48351   | 0x209E | 3rd Rev Amount | WK205             | R/W     |
| 1862 | 48353   | 0x20A0 | 3rd Rev Speed  | WK205             | R/W     |
| 1863 | 48355   | 0x20A2 | Pre-heat Time  | WK205             | R/W     |
| 1864 | 48357   | 0x20A4 | Heating Time   | WK205             | R/W     |
| 1865 | 48359   | 0x20A6 | Reserve        | WK205             | R/W     |
| 1866 | 48361   | 0x20A8 | Reserve        | WK205             | R/W     |
| 1867 | 48363   | 0x20AA | SV2 Time       | WK206             | R/W     |
| 1868 | 48365   | 0x20AC | 1st Amount     | WK206             | R/W     |
| 1869 | 48367   | 0x20AE | 1st Speed      | WK206             | R/W     |
| 1870 | 48369   | 0x20B0 | 1st Rev Amount | WK206             | R/W     |
| 1871 | 48371   | 0x20B2 | 1st Rev Speed  | WK206             | R/W     |
| 1872 | 48373   | 0x20B4 | 2nd Amount     | WK206             | R/W     |
| 1873 | 48375   | 0x20B6 | 2nd Speed      | WK206             | R/W     |
| 1874 | 48377   | 0x20B8 | 2nd Rev Amount | WK206             | R/W     |
| 1875 | 48379   | 0x20BA | 2nd Rev Speed  | WK206             | R/W     |
| 1876 | 48381   | 0x20BC | 3rd Amount     | WK206             | R/W     |
| 1877 | 48383   | 0x20BE | 3rd Speed      | WK206             | R/W     |
| 1878 | 48385   | 0x20C0 | 3rd Rev Amount | WK206             | R/W     |
| 1879 | 48387   | 0x20C2 | 3rd Rev Speed  | WK206             | R/W     |
| 1880 | 48389   | 0x20C4 | Pre-heat Time  | WK206             | R/W     |
| 1881 | 48391   | 0x20C6 | Heating Time   | WK206             | R/W     |
| 1882 | 48393   | 0x20C8 | Reserve        | WK206             | R/W     |
| 1883 | 48395   | 0x20CA | Reserve        | WK206             | R/W     |
| 1884 | 48397   | 0x20CC | SV2 Time       | WK207             | R/W     |
| 1885 | 48399   | 0x20CE | 1st Amount     | WK207             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1886 | 48401   | 0x20D0 | 1st Speed      | WK207             | R/W     |
| 1887 | 48403   | 0x20D2 | 1st Rev Amount | WK207             | R/W     |
| 1888 | 48405   | 0x20D4 | 1st Rev Speed  | WK207             | R/W     |
| 1889 | 48407   | 0x20D6 | 2nd Amount     | WK207             | R/W     |
| 1890 | 48409   | 0x20D8 | 2nd Speed      | WK207             | R/W     |
| 1891 | 48411   | 0x20DA | 2nd Rev Amount | WK207             | R/W     |
| 1892 | 48413   | 0x20DC | 2nd Rev Speed  | WK207             | R/W     |
| 1893 | 48415   | 0x20DE | 3rd Amount     | WK207             | R/W     |
| 1894 | 48417   | 0x20E0 | 3rd Speed      | WK207             | R/W     |
| 1895 | 48419   | 0x20E2 | 3rd Rev Amount | WK207             | R/W     |
| 1896 | 48421   | 0x20E4 | 3rd Rev Speed  | WK207             | R/W     |
| 1897 | 48423   | 0x20E6 | Pre-heat Time  | WK207             | R/W     |
| 1898 | 48425   | 0x20E8 | Heating Time   | WK207             | R/W     |
| 1899 | 48427   | 0x20EA | Reserve        | WK207             | R/W     |
| 1900 | 48429   | 0x20EC | Reserve        | WK207             | R/W     |
| 1901 | 48431   | 0x20EE | SV2 Time       | WK208             | R/W     |
| 1902 | 48433   | 0x20F0 | 1st Amount     | WK208             | R/W     |
| 1903 | 48435   | 0x20F2 | 1st Speed      | WK208             | R/W     |
| 1904 | 48437   | 0x20F4 | 1st Rev Amount | WK208             | R/W     |
| 1905 | 48439   | 0x20F6 | 1st Rev Speed  | WK208             | R/W     |
| 1906 | 48441   | 0x20F8 | 2nd Amount     | WK208             | R/W     |
| 1907 | 48443   | 0x20FA | 2nd Speed      | WK208             | R/W     |
| 1908 | 48445   | 0x20FC | 2nd Rev Amount | WK208             | R/W     |
| 1909 | 48447   | 0x20FE | 2nd Rev Speed  | WK208             | R/W     |
| 1910 | 48449   | 0x2100 | 3rd Amount     | WK208             | R/W     |
| 1911 | 48451   | 0x2102 | 3rd Speed      | WK208             | R/W     |
| 1912 | 48453   | 0x2104 | 3rd Rev Amount | WK208             | R/W     |
| 1913 | 48455   | 0x2106 | 3rd Rev Speed  | WK208             | R/W     |
| 1914 | 48457   | 0x2108 | Pre-heat Time  | WK208             | R/W     |
| 1915 | 48459   | 0x210A | Heating Time   | WK208             | R/W     |
| 1916 | 48461   | 0x210C | Reserve        | WK208             | R/W     |
| 1917 | 48463   | 0x210E | Reserve        | WK208             | R/W     |
| 1918 | 48465   | 0x2110 | SV2 Time       | WK209             | R/W     |
| 1919 | 48467   | 0x2112 | 1st Amount     | WK209             | R/W     |
| 1920 | 48469   | 0x2114 | 1st Speed      | WK209             | R/W     |
| 1921 | 48471   | 0x2116 | 1st Rev Amount | WK209             | R/W     |
| 1922 | 48473   | 0x2118 | 1st Rev Speed  | WK209             | R/W     |
| 1923 | 48475   | 0x211A | 2nd Amount     | WK209             | R/W     |
| 1924 | 48477   | 0x211C | 2nd Speed      | WK209             | R/W     |
| 1925 | 48479   | 0x211E | 2nd Rev Amount | WK209             | R/W     |
| 1926 | 48481   | 0x2120 | 2nd Rev Speed  | WK209             | R/W     |
| 1927 | 48483   | 0x2122 | 3rd Amount     | WK209             | R/W     |
| 1928 | 48485   | 0x2124 | 3rd Speed      | WK209             | R/W     |
| 1929 | 48487   | 0x2126 | 3rd Rev Amount | WK209             | R/W     |
| 1930 | 48489   | 0x2128 | 3rd Rev Speed  | WK209             | R/W     |
| 1931 | 48491   | 0x212A | Pre-heat Time  | WK209             | R/W     |
| 1932 | 48493   | 0x212C | Heating Time   | WK209             | R/W     |
| 1933 | 48495   | 0x212E | Reserve        | WK209             | R/W     |
| 1934 | 48497   | 0x2130 | Reserve        | WK209             | R/W     |
| 1935 | 48499   | 0x2132 | SV2 Time       | WK210             | R/W     |
| 1936 | 48501   | 0x2134 | 1st Amount     | WK210             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1937 | 48503   | 0x2136 | 1st Speed      | WK210             | R/W     |
| 1938 | 48505   | 0x2138 | 1st Rev Amount | WK210             | R/W     |
| 1939 | 48507   | 0x213A | 1st Rev Speed  | WK210             | R/W     |
| 1940 | 48509   | 0x213C | 2nd Amount     | WK210             | R/W     |
| 1941 | 48511   | 0x213E | 2nd Speed      | WK210             | R/W     |
| 1942 | 48513   | 0x2140 | 2nd Rev Amount | WK210             | R/W     |
| 1943 | 48515   | 0x2142 | 2nd Rev Speed  | WK210             | R/W     |
| 1944 | 48517   | 0x2144 | 3rd Amount     | WK210             | R/W     |
| 1945 | 48519   | 0x2146 | 3rd Speed      | WK210             | R/W     |
| 1946 | 48521   | 0x2148 | 3rd Rev Amount | WK210             | R/W     |
| 1947 | 48523   | 0x214A | 3rd Rev Speed  | WK210             | R/W     |
| 1948 | 48525   | 0x214C | Pre-heat Time  | WK210             | R/W     |
| 1949 | 48527   | 0x214E | Heating Time   | WK210             | R/W     |
| 1950 | 48529   | 0x2150 | Reserve        | WK210             | R/W     |
| 1951 | 48531   | 0x2152 | Reserve        | WK210             | R/W     |
| 1952 | 48533   | 0x2154 | SV2 Time       | WK211             | R/W     |
| 1953 | 48535   | 0x2156 | 1st Amount     | WK211             | R/W     |
| 1954 | 48537   | 0x2158 | 1st Speed      | WK211             | R/W     |
| 1955 | 48539   | 0x215A | 1st Rev Amount | WK211             | R/W     |
| 1956 | 48541   | 0x215C | 1st Rev Speed  | WK211             | R/W     |
| 1957 | 48543   | 0x215E | 2nd Amount     | WK211             | R/W     |
| 1958 | 48545   | 0x2160 | 2nd Speed      | WK211             | R/W     |
| 1959 | 48547   | 0x2162 | 2nd Rev Amount | WK211             | R/W     |
| 1960 | 48549   | 0x2164 | 2nd Rev Speed  | WK211             | R/W     |
| 1961 | 48551   | 0x2166 | 3rd Amount     | WK211             | R/W     |
| 1962 | 48553   | 0x2168 | 3rd Speed      | WK211             | R/W     |
| 1963 | 48555   | 0x216A | 3rd Rev Amount | WK211             | R/W     |
| 1964 | 48557   | 0x216C | 3rd Rev Speed  | WK211             | R/W     |
| 1965 | 48559   | 0x216E | Pre-heat Time  | WK211             | R/W     |
| 1966 | 48561   | 0x2170 | Heating Time   | WK211             | R/W     |
| 1967 | 48563   | 0x2172 | Reserve        | WK211             | R/W     |
| 1968 | 48565   | 0x2174 | Reserve        | WK211             | R/W     |
| 1969 | 48567   | 0x2176 | SV2 Time       | WK212             | R/W     |
| 1970 | 48569   | 0x2178 | 1st Amount     | WK212             | R/W     |
| 1971 | 48571   | 0x217A | 1st Speed      | WK212             | R/W     |
| 1972 | 48573   | 0x217C | 1st Rev Amount | WK212             | R/W     |
| 1973 | 48575   | 0x217E | 1st Rev Speed  | WK212             | R/W     |
| 1974 | 48577   | 0x2180 | 2nd Amount     | WK212             | R/W     |
| 1975 | 48579   | 0x2182 | 2nd Speed      | WK212             | R/W     |
| 1976 | 48581   | 0x2184 | 2nd Rev Amount | WK212             | R/W     |
| 1977 | 48583   | 0x2186 | 2nd Rev Speed  | WK212             | R/W     |
| 1978 | 48585   | 0x2188 | 3rd Amount     | WK212             | R/W     |
| 1979 | 48587   | 0x218A | 3rd Speed      | WK212             | R/W     |
| 1980 | 48589   | 0x218C | 3rd Rev Amount | WK212             | R/W     |
| 1981 | 48591   | 0x218E | 3rd Rev Speed  | WK212             | R/W     |
| 1982 | 48593   | 0x2190 | Pre-heat Time  | WK212             | R/W     |
| 1983 | 48595   | 0x2192 | Heating Time   | WK212             | R/W     |
| 1984 | 48597   | 0x2194 | Reserve        | WK212             | R/W     |
| 1985 | 48599   | 0x2196 | Reserve        | WK212             | R/W     |
| 1986 | 48601   | 0x2198 | SV2 Time       | WK213             | R/W     |
| 1987 | 48603   | 0x219A | 1st Amount     | WK213             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 1988 | 48605   | 0x219C | 1st Speed      | WK213             | R/W     |
| 1989 | 48607   | 0x219E | 1st Rev Amount | WK213             | R/W     |
| 1990 | 48609   | 0x21A0 | 1st Rev Speed  | WK213             | R/W     |
| 1991 | 48611   | 0x21A2 | 2nd Amount     | WK213             | R/W     |
| 1992 | 48613   | 0x21A4 | 2nd Speed      | WK213             | R/W     |
| 1993 | 48615   | 0x21A6 | 2nd Rev Amount | WK213             | R/W     |
| 1994 | 48617   | 0x21A8 | 2nd Rev Speed  | WK213             | R/W     |
| 1995 | 48619   | 0x21AA | 3rd Amount     | WK213             | R/W     |
| 1996 | 48621   | 0x21AC | 3rd Speed      | WK213             | R/W     |
| 1997 | 48623   | 0x21AE | 3rd Rev Amount | WK213             | R/W     |
| 1998 | 48625   | 0x21B0 | 3rd Rev Speed  | WK213             | R/W     |
| 1999 | 48627   | 0x21B2 | Pre-heat Time  | WK213             | R/W     |
| 2000 | 48629   | 0x21B4 | Heating Time   | WK213             | R/W     |
| 2001 | 48631   | 0x21B6 | Reserve        | WK213             | R/W     |
| 2002 | 48633   | 0x21B8 | Reserve        | WK213             | R/W     |
| 2003 | 48635   | 0x21BA | SV2 Time       | WK214             | R/W     |
| 2004 | 48637   | 0x21BC | 1st Amount     | WK214             | R/W     |
| 2005 | 48639   | 0x21BE | 1st Speed      | WK214             | R/W     |
| 2006 | 48641   | 0x21C0 | 1st Rev Amount | WK214             | R/W     |
| 2007 | 48643   | 0x21C2 | 1st Rev Speed  | WK214             | R/W     |
| 2008 | 48645   | 0x21C4 | 2nd Amount     | WK214             | R/W     |
| 2009 | 48647   | 0x21C6 | 2nd Speed      | WK214             | R/W     |
| 2010 | 48649   | 0x21C8 | 2nd Rev Amount | WK214             | R/W     |
| 2011 | 48651   | 0x21CA | 2nd Rev Speed  | WK214             | R/W     |
| 2012 | 48653   | 0x21CC | 3rd Amount     | WK214             | R/W     |
| 2013 | 48655   | 0x21CE | 3rd Speed      | WK214             | R/W     |
| 2014 | 48657   | 0x21D0 | 3rd Rev Amount | WK214             | R/W     |
| 2015 | 48659   | 0x21D2 | 3rd Rev Speed  | WK214             | R/W     |
| 2016 | 48661   | 0x21D4 | Pre-heat Time  | WK214             | R/W     |
| 2017 | 48663   | 0x21D6 | Heating Time   | WK214             | R/W     |
| 2018 | 48665   | 0x21D8 | Reserve        | WK214             | R/W     |
| 2019 | 48667   | 0x21DA | Reserve        | WK214             | R/W     |
| 2020 | 48669   | 0x21DC | SV2 Time       | WK215             | R/W     |
| 2021 | 48671   | 0x21DE | 1st Amount     | WK215             | R/W     |
| 2022 | 48673   | 0x21E0 | 1st Speed      | WK215             | R/W     |
| 2023 | 48675   | 0x21E2 | 1st Rev Amount | WK215             | R/W     |
| 2024 | 48677   | 0x21E4 | 1st Rev Speed  | WK215             | R/W     |
| 2025 | 48679   | 0x21E6 | 2nd Amount     | WK215             | R/W     |
| 2026 | 48681   | 0x21E8 | 2nd Speed      | WK215             | R/W     |
| 2027 | 48683   | 0x21EA | 2nd Rev Amount | WK215             | R/W     |
| 2028 | 48685   | 0x21EC | 2nd Rev Speed  | WK215             | R/W     |
| 2029 | 48687   | 0x21EE | 3rd Amount     | WK215             | R/W     |
| 2030 | 48689   | 0x21F0 | 3rd Speed      | WK215             | R/W     |
| 2031 | 48691   | 0x21F2 | 3rd Rev Amount | WK215             | R/W     |
| 2032 | 48693   | 0x21F4 | 3rd Rev Speed  | WK215             | R/W     |
| 2033 | 48695   | 0x21F6 | Pre-heat Time  | WK215             | R/W     |
| 2034 | 48697   | 0x21F8 | Heating Time   | WK215             | R/W     |
| 2035 | 48699   | 0x21FA | Reserve        | WK215             | R/W     |
| 2036 | 48701   | 0x21FC | Reserve        | WK215             | R/W     |
| 2037 | 48703   | 0x21FE | SV2 Time       | WK216             | R/W     |
| 2038 | 48705   | 0x2200 | 1st Amount     | WK216             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2039 | 48707   | 0x2202 | 1st Speed      | WK216             | R/W     |
| 2040 | 48709   | 0x2204 | 1st Rev Amount | WK216             | R/W     |
| 2041 | 48711   | 0x2206 | 1st Rev Speed  | WK216             | R/W     |
| 2042 | 48713   | 0x2208 | 2nd Amount     | WK216             | R/W     |
| 2043 | 48715   | 0x220A | 2nd Speed      | WK216             | R/W     |
| 2044 | 48717   | 0x220C | 2nd Rev Amount | WK216             | R/W     |
| 2045 | 48719   | 0x220E | 2nd Rev Speed  | WK216             | R/W     |
| 2046 | 48721   | 0x2210 | 3rd Amount     | WK216             | R/W     |
| 2047 | 48723   | 0x2212 | 3rd Speed      | WK216             | R/W     |
| 2048 | 48725   | 0x2214 | 3rd Rev Amount | WK216             | R/W     |
| 2049 | 48727   | 0x2216 | 3rd Rev Speed  | WK216             | R/W     |
| 2050 | 48729   | 0x2218 | Pre-heat Time  | WK216             | R/W     |
| 2051 | 48731   | 0x221A | Heating Time   | WK216             | R/W     |
| 2052 | 48733   | 0x221C | Reserve        | WK216             | R/W     |
| 2053 | 48735   | 0x221E | Reserve        | WK216             | R/W     |
| 2054 | 48737   | 0x2220 | SV2 Time       | WK217             | R/W     |
| 2055 | 48739   | 0x2222 | 1st Amount     | WK217             | R/W     |
| 2056 | 48741   | 0x2224 | 1st Speed      | WK217             | R/W     |
| 2057 | 48743   | 0x2226 | 1st Rev Amount | WK217             | R/W     |
| 2058 | 48745   | 0x2228 | 1st Rev Speed  | WK217             | R/W     |
| 2059 | 48747   | 0x222A | 2nd Amount     | WK217             | R/W     |
| 2060 | 48749   | 0x222C | 2nd Speed      | WK217             | R/W     |
| 2061 | 48751   | 0x222E | 2nd Rev Amount | WK217             | R/W     |
| 2062 | 48753   | 0x2230 | 2nd Rev Speed  | WK217             | R/W     |
| 2063 | 48755   | 0x2232 | 3rd Amount     | WK217             | R/W     |
| 2064 | 48757   | 0x2234 | 3rd Speed      | WK217             | R/W     |
| 2065 | 48759   | 0x2236 | 3rd Rev Amount | WK217             | R/W     |
| 2066 | 48761   | 0x2238 | 3rd Rev Speed  | WK217             | R/W     |
| 2067 | 48763   | 0x223A | Pre-heat Time  | WK217             | R/W     |
| 2068 | 48765   | 0x223C | Heating Time   | WK217             | R/W     |
| 2069 | 48767   | 0x223E | Reserve        | WK217             | R/W     |
| 2070 | 48769   | 0x2240 | Reserve        | WK217             | R/W     |
| 2071 | 48771   | 0x2242 | SV2 Time       | WK218             | R/W     |
| 2072 | 48773   | 0x2244 | 1st Amount     | WK218             | R/W     |
| 2073 | 48775   | 0x2246 | 1st Speed      | WK218             | R/W     |
| 2074 | 48777   | 0x2248 | 1st Rev Amount | WK218             | R/W     |
| 2075 | 48779   | 0x224A | 1st Rev Speed  | WK218             | R/W     |
| 2076 | 48781   | 0x224C | 2nd Amount     | WK218             | R/W     |
| 2077 | 48783   | 0x224E | 2nd Speed      | WK218             | R/W     |
| 2078 | 48785   | 0x2250 | 2nd Rev Amount | WK218             | R/W     |
| 2079 | 48787   | 0x2252 | 2nd Rev Speed  | WK218             | R/W     |
| 2080 | 48789   | 0x2254 | 3rd Amount     | WK218             | R/W     |
| 2081 | 48791   | 0x2256 | 3rd Speed      | WK218             | R/W     |
| 2082 | 48793   | 0x2258 | 3rd Rev Amount | WK218             | R/W     |
| 2083 | 48795   | 0x225A | 3rd Rev Speed  | WK218             | R/W     |
| 2084 | 48797   | 0x225C | Pre-heat Time  | WK218             | R/W     |
| 2085 | 48799   | 0x225E | Heating Time   | WK218             | R/W     |
| 2086 | 48801   | 0x2260 | Reserve        | WK218             | R/W     |
| 2087 | 48803   | 0x2262 | Reserve        | WK218             | R/W     |
| 2088 | 48805   | 0x2264 | SV2 Time       | WK219             | R/W     |
| 2089 | 48807   | 0x2266 | 1st Amount     | WK219             | R/W     |



| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2090 | 48809   | 0x2268 | 1st Speed      | WK219             | R/W     |
| 2091 | 48811   | 0x226A | 1st Rev Amount | WK219             | R/W     |
| 2092 | 48813   | 0x226C | 1st Rev Speed  | WK219             | R/W     |
| 2093 | 48815   | 0x226E | 2nd Amount     | WK219             | R/W     |
| 2094 | 48817   | 0x2270 | 2nd Speed      | WK219             | R/W     |
| 2095 | 48819   | 0x2272 | 2nd Rev Amount | WK219             | R/W     |
| 2096 | 48821   | 0x2274 | 2nd Rev Speed  | WK219             | R/W     |
| 2097 | 48823   | 0x2276 | 3rd Amount     | WK219             | R/W     |
| 2098 | 48825   | 0x2278 | 3rd Speed      | WK219             | R/W     |
| 2099 | 48827   | 0x227A | 3rd Rev Amount | WK219             | R/W     |
| 2100 | 48829   | 0x227C | 3rd Rev Speed  | WK219             | R/W     |
| 2101 | 48831   | 0x227E | Pre-heat Time  | WK219             | R/W     |
| 2102 | 48833   | 0x2280 | Heating Time   | WK219             | R/W     |
| 2103 | 48835   | 0x2282 | Reserve        | WK219             | R/W     |
| 2104 | 48837   | 0x2284 | Reserve        | WK219             | R/W     |
| 2105 | 48839   | 0x2286 | SV2 Time       | WK220             | R/W     |
| 2106 | 48841   | 0x2288 | 1st Amount     | WK220             | R/W     |
| 2107 | 48843   | 0x228A | 1st Speed      | WK220             | R/W     |
| 2108 | 48845   | 0x228C | 1st Rev Amount | WK220             | R/W     |
| 2109 | 48847   | 0x228E | 1st Rev Speed  | WK220             | R/W     |
| 2110 | 48849   | 0x2290 | 2nd Amount     | WK220             | R/W     |
| 2111 | 48851   | 0x2292 | 2nd Speed      | WK220             | R/W     |
| 2112 | 48853   | 0x2294 | 2nd Rev Amount | WK220             | R/W     |
| 2113 | 48855   | 0x2296 | 2nd Rev Speed  | WK220             | R/W     |
| 2114 | 48857   | 0x2298 | 3rd Amount     | WK220             | R/W     |
| 2115 | 48859   | 0x229A | 3rd Speed      | WK220             | R/W     |
| 2116 | 48861   | 0x229C | 3rd Rev Amount | WK220             | R/W     |
| 2117 | 48863   | 0x229E | 3rd Rev Speed  | WK220             | R/W     |
| 2118 | 48865   | 0x22A0 | Pre-heat Time  | WK220             | R/W     |
| 2119 | 48867   | 0x22A2 | Heating Time   | WK220             | R/W     |
| 2120 | 48869   | 0x22A4 | Reserve        | WK220             | R/W     |
| 2121 | 48871   | 0x22A6 | Reserve        | WK220             | R/W     |
| 2122 | 48873   | 0x22A8 | SV2 Time       | WK221             | R/W     |
| 2123 | 48875   | 0x22AA | 1st Amount     | WK221             | R/W     |
| 2124 | 48877   | 0x22AC | 1st Speed      | WK221             | R/W     |
| 2125 | 48879   | 0x22AE | 1st Rev Amount | WK221             | R/W     |
| 2126 | 48881   | 0x22B0 | 1st Rev Speed  | WK221             | R/W     |
| 2127 | 48883   | 0x22B2 | 2nd Amount     | WK221             | R/W     |
| 2128 | 48885   | 0x22B4 | 2nd Speed      | WK221             | R/W     |
| 2129 | 48887   | 0x22B6 | 2nd Rev Amount | WK221             | R/W     |
| 2130 | 48889   | 0x22B8 | 2nd Rev Speed  | WK221             | R/W     |
| 2131 | 48891   | 0x22BA | 3rd Amount     | WK221             | R/W     |
| 2132 | 48893   | 0x22BC | 3rd Speed      | WK221             | R/W     |
| 2133 | 48895   | 0x22BE | 3rd Rev Amount | WK221             | R/W     |
| 2134 | 48897   | 0x22C0 | 3rd Rev Speed  | WK221             | R/W     |
| 2135 | 48899   | 0x22C2 | Pre-heat Time  | WK221             | R/W     |
| 2136 | 48901   | 0x22C4 | Heating Time   | WK221             | R/W     |
| 2137 | 48903   | 0x22C6 | Reserve        | WK221             | R/W     |
| 2138 | 48905   | 0x22C8 | Reserve        | WK221             | R/W     |
| 2139 | 48907   | 0x22CA | SV2 Time       | WK222             | R/W     |
| 2140 | 48909   | 0x22CC | 1st Amount     | WK222             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2141 | 48911   | 0x22CE | 1st Speed      | WK222             | R/W     |
| 2142 | 48913   | 0x22D0 | 1st Rev Amount | WK222             | R/W     |
| 2143 | 48915   | 0x22D2 | 1st Rev Speed  | WK222             | R/W     |
| 2144 | 48917   | 0x22D4 | 2nd Amount     | WK222             | R/W     |
| 2145 | 48919   | 0x22D6 | 2nd Speed      | WK222             | R/W     |
| 2146 | 48921   | 0x22D8 | 2nd Rev Amount | WK222             | R/W     |
| 2147 | 48923   | 0x22DA | 2nd Rev Speed  | WK222             | R/W     |
| 2148 | 48925   | 0x22DC | 3rd Amount     | WK222             | R/W     |
| 2149 | 48927   | 0x22DE | 3rd Speed      | WK222             | R/W     |
| 2150 | 48929   | 0x22E0 | 3rd Rev Amount | WK222             | R/W     |
| 2151 | 48931   | 0x22E2 | 3rd Rev Speed  | WK222             | R/W     |
| 2152 | 48933   | 0x22E4 | Pre-heat Time  | WK222             | R/W     |
| 2153 | 48935   | 0x22E6 | Heating Time   | WK222             | R/W     |
| 2154 | 48937   | 0x22E8 | Reserve        | WK222             | R/W     |
| 2155 | 48939   | 0x22EA | Reserve        | WK222             | R/W     |
| 2156 | 48941   | 0x22EC | SV2 Time       | WK223             | R/W     |
| 2157 | 48943   | 0x22EE | 1st Amount     | WK223             | R/W     |
| 2158 | 48945   | 0x22F0 | 1st Speed      | WK223             | R/W     |
| 2159 | 48947   | 0x22F2 | 1st Rev Amount | WK223             | R/W     |
| 2160 | 48949   | 0x22F4 | 1st Rev Speed  | WK223             | R/W     |
| 2161 | 48951   | 0x22F6 | 2nd Amount     | WK223             | R/W     |
| 2162 | 48953   | 0x22F8 | 2nd Speed      | WK223             | R/W     |
| 2163 | 48955   | 0x22FA | 2nd Rev Amount | WK223             | R/W     |
| 2164 | 48957   | 0x22FC | 2nd Rev Speed  | WK223             | R/W     |
| 2165 | 48959   | 0x22FE | 3rd Amount     | WK223             | R/W     |
| 2166 | 48961   | 0x2300 | 3rd Speed      | WK223             | R/W     |
| 2167 | 48963   | 0x2302 | 3rd Rev Amount | WK223             | R/W     |
| 2168 | 48965   | 0x2304 | 3rd Rev Speed  | WK223             | R/W     |
| 2169 | 48967   | 0x2306 | Pre-heat Time  | WK223             | R/W     |
| 2170 | 48969   | 0x2308 | Heating Time   | WK223             | R/W     |
| 2171 | 48971   | 0x230A | Reserve        | WK223             | R/W     |
| 2172 | 48973   | 0x230C | Reserve        | WK223             | R/W     |
| 2173 | 48975   | 0x230E | SV2 Time       | WK224             | R/W     |
| 2174 | 48977   | 0x2310 | 1st Amount     | WK224             | R/W     |
| 2175 | 48979   | 0x2312 | 1st Speed      | WK224             | R/W     |
| 2176 | 48981   | 0x2314 | 1st Rev Amount | WK224             | R/W     |
| 2177 | 48983   | 0x2316 | 1st Rev Speed  | WK224             | R/W     |
| 2178 | 48985   | 0x2318 | 2nd Amount     | WK224             | R/W     |
| 2179 | 48987   | 0x231A | 2nd Speed      | WK224             | R/W     |
| 2180 | 48989   | 0x231C | 2nd Rev Amount | WK224             | R/W     |
| 2181 | 48991   | 0x231E | 2nd Rev Speed  | WK224             | R/W     |
| 2182 | 48993   | 0x2320 | 3rd Amount     | WK224             | R/W     |
| 2183 | 48995   | 0x2322 | 3rd Speed      | WK224             | R/W     |
| 2184 | 48997   | 0x2324 | 3rd Rev Amount | WK224             | R/W     |
| 2185 | 48999   | 0x2326 | 3rd Rev Speed  | WK224             | R/W     |
| 2186 | 49001   | 0x2328 | Pre-heat Time  | WK224             | R/W     |
| 2187 | 49003   | 0x232A | Heating Time   | WK224             | R/W     |
| 2188 | 49005   | 0x232C | Reserve        | WK224             | R/W     |
| 2189 | 49007   | 0x232E | Reserve        | WK224             | R/W     |
| 2190 | 49009   | 0x2330 | SV2 Time       | WK225             | R/W     |
| 2191 | 49011   | 0x2332 | 1st Amount     | WK225             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2192 | 49013   | 0x2334 | 1st Speed      | WK225             | R/W     |
| 2193 | 49015   | 0x2336 | 1st Rev Amount | WK225             | R/W     |
| 2194 | 49017   | 0x2338 | 1st Rev Speed  | WK225             | R/W     |
| 2195 | 49019   | 0x233A | 2nd Amount     | WK225             | R/W     |
| 2196 | 49021   | 0x233C | 2nd Speed      | WK225             | R/W     |
| 2197 | 49023   | 0x233E | 2nd Rev Amount | WK225             | R/W     |
| 2198 | 49025   | 0x2340 | 2nd Rev Speed  | WK225             | R/W     |
| 2199 | 49027   | 0x2342 | 3rd Amount     | WK225             | R/W     |
| 2200 | 49029   | 0x2344 | 3rd Speed      | WK225             | R/W     |
| 2201 | 49031   | 0x2346 | 3rd Rev Amount | WK225             | R/W     |
| 2202 | 49033   | 0x2348 | 3rd Rev Speed  | WK225             | R/W     |
| 2203 | 49035   | 0x234A | Pre-heat Time  | WK225             | R/W     |
| 2204 | 49037   | 0x234C | Heating Time   | WK225             | R/W     |
| 2205 | 49039   | 0x234E | Reserve        | WK225             | R/W     |
| 2206 | 49041   | 0x2350 | Reserve        | WK225             | R/W     |
| 2207 | 49043   | 0x2352 | SV2 Time       | WK226             | R/W     |
| 2208 | 49045   | 0x2354 | 1st Amount     | WK226             | R/W     |
| 2209 | 49047   | 0x2356 | 1st Speed      | WK226             | R/W     |
| 2210 | 49049   | 0x2358 | 1st Rev Amount | WK226             | R/W     |
| 2211 | 49051   | 0x235A | 1st Rev Speed  | WK226             | R/W     |
| 2212 | 49053   | 0x235C | 2nd Amount     | WK226             | R/W     |
| 2213 | 49055   | 0x235E | 2nd Speed      | WK226             | R/W     |
| 2214 | 49057   | 0x2360 | 2nd Rev Amount | WK226             | R/W     |
| 2215 | 49059   | 0x2362 | 2nd Rev Speed  | WK226             | R/W     |
| 2216 | 49061   | 0x2364 | 3rd Amount     | WK226             | R/W     |
| 2217 | 49063   | 0x2366 | 3rd Speed      | WK226             | R/W     |
| 2218 | 49065   | 0x2368 | 3rd Rev Amount | WK226             | R/W     |
| 2219 | 49067   | 0x236A | 3rd Rev Speed  | WK226             | R/W     |
| 2220 | 49069   | 0x236C | Pre-heat Time  | WK226             | R/W     |
| 2221 | 49071   | 0x236E | Heating Time   | WK226             | R/W     |
| 2222 | 49073   | 0x2370 | Reserve        | WK226             | R/W     |
| 2223 | 49075   | 0x2372 | Reserve        | WK226             | R/W     |
| 2224 | 49077   | 0x2374 | SV2 Time       | WK227             | R/W     |
| 2225 | 49079   | 0x2376 | 1st Amount     | WK227             | R/W     |
| 2226 | 49081   | 0x2378 | 1st Speed      | WK227             | R/W     |
| 2227 | 49083   | 0x237A | 1st Rev Amount | WK227             | R/W     |
| 2228 | 49085   | 0x237C | 1st Rev Speed  | WK227             | R/W     |
| 2229 | 49087   | 0x237E | 2nd Amount     | WK227             | R/W     |
| 2230 | 49089   | 0x2380 | 2nd Speed      | WK227             | R/W     |
| 2231 | 49091   | 0x2382 | 2nd Rev Amount | WK227             | R/W     |
| 2232 | 49093   | 0x2384 | 2nd Rev Speed  | WK227             | R/W     |
| 2233 | 49095   | 0x2386 | 3rd Amount     | WK227             | R/W     |
| 2234 | 49097   | 0x2388 | 3rd Speed      | WK227             | R/W     |
| 2235 | 49099   | 0x238A | 3rd Rev Amount | WK227             | R/W     |
| 2236 | 49101   | 0x238C | 3rd Rev Speed  | WK227             | R/W     |
| 2237 | 49103   | 0x238E | Pre-heat Time  | WK227             | R/W     |
| 2238 | 49105   | 0x2390 | Heating Time   | WK227             | R/W     |
| 2239 | 49107   | 0x2392 | Reserve        | WK227             | R/W     |
| 2240 | 49109   | 0x2394 | Reserve        | WK227             | R/W     |
| 2241 | 49111   | 0x2396 | SV2 Time       | WK228             | R/W     |
| 2242 | 49113   | 0x2398 | 1st Amount     | WK228             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2243 | 49115   | 0x239A | 1st Speed      | WK228             | R/W     |
| 2244 | 49117   | 0x239C | 1st Rev Amount | WK228             | R/W     |
| 2245 | 49119   | 0x239E | 1st Rev Speed  | WK228             | R/W     |
| 2246 | 49121   | 0x23A0 | 2nd Amount     | WK228             | R/W     |
| 2247 | 49123   | 0x23A2 | 2nd Speed      | WK228             | R/W     |
| 2248 | 49125   | 0x23A4 | 2nd Rev Amount | WK228             | R/W     |
| 2249 | 49127   | 0x23A6 | 2nd Rev Speed  | WK228             | R/W     |
| 2250 | 49129   | 0x23A8 | 3rd Amount     | WK228             | R/W     |
| 2251 | 49131   | 0x23AA | 3rd Speed      | WK228             | R/W     |
| 2252 | 49133   | 0x23AC | 3rd Rev Amount | WK228             | R/W     |
| 2253 | 49135   | 0x23AE | 3rd Rev Speed  | WK228             | R/W     |
| 2254 | 49137   | 0x23B0 | Pre-heat Time  | WK228             | R/W     |
| 2255 | 49139   | 0x23B2 | Heating Time   | WK228             | R/W     |
| 2256 | 49141   | 0x23B4 | Reserve        | WK228             | R/W     |
| 2257 | 49143   | 0x23B6 | Reserve        | WK228             | R/W     |
| 2258 | 49145   | 0x23B8 | SV2 Time       | WK229             | R/W     |
| 2259 | 49147   | 0x23BA | 1st Amount     | WK229             | R/W     |
| 2260 | 49149   | 0x23BC | 1st Speed      | WK229             | R/W     |
| 2261 | 49151   | 0x23BE | 1st Rev Amount | WK229             | R/W     |
| 2262 | 49153   | 0x23C0 | 1st Rev Speed  | WK229             | R/W     |
| 2263 | 49155   | 0x23C2 | 2nd Amount     | WK229             | R/W     |
| 2264 | 49157   | 0x23C4 | 2nd Speed      | WK229             | R/W     |
| 2265 | 49159   | 0x23C6 | 2nd Rev Amount | WK229             | R/W     |
| 2266 | 49161   | 0x23C8 | 2nd Rev Speed  | WK229             | R/W     |
| 2267 | 49163   | 0x23CA | 3rd Amount     | WK229             | R/W     |
| 2268 | 49165   | 0x23CC | 3rd Speed      | WK229             | R/W     |
| 2269 | 49167   | 0x23CE | 3rd Rev Amount | WK229             | R/W     |
| 2270 | 49169   | 0x23D0 | 3rd Rev Speed  | WK229             | R/W     |
| 2271 | 49171   | 0x23D2 | Pre-heat Time  | WK229             | R/W     |
| 2272 | 49173   | 0x23D4 | Heating Time   | WK229             | R/W     |
| 2273 | 49175   | 0x23D6 | Reserve        | WK229             | R/W     |
| 2274 | 49177   | 0x23D8 | Reserve        | WK229             | R/W     |
| 2275 | 49179   | 0x23DA | SV2 Time       | WK230             | R/W     |
| 2276 | 49181   | 0x23DC | 1st Amount     | WK230             | R/W     |
| 2277 | 49183   | 0x23DE | 1st Speed      | WK230             | R/W     |
| 2278 | 49185   | 0x23E0 | 1st Rev Amount | WK230             | R/W     |
| 2279 | 49187   | 0x23E2 | 1st Rev Speed  | WK230             | R/W     |
| 2280 | 49189   | 0x23E4 | 2nd Amount     | WK230             | R/W     |
| 2281 | 49191   | 0x23E6 | 2nd Speed      | WK230             | R/W     |
| 2282 | 49193   | 0x23E8 | 2nd Rev Amount | WK230             | R/W     |
| 2283 | 49195   | 0x23EA | 2nd Rev Speed  | WK230             | R/W     |
| 2284 | 49197   | 0x23EC | 3rd Amount     | WK230             | R/W     |
| 2285 | 49199   | 0x23EE | 3rd Speed      | WK230             | R/W     |
| 2286 | 49201   | 0x23F0 | 3rd Rev Amount | WK230             | R/W     |
| 2287 | 49203   | 0x23F2 | 3rd Rev Speed  | WK230             | R/W     |
| 2288 | 49205   | 0x23F4 | Pre-heat Time  | WK230             | R/W     |
| 2289 | 49207   | 0x23F6 | Heating Time   | WK230             | R/W     |
| 2290 | 49209   | 0x23F8 | Reserve        | WK230             | R/W     |
| 2291 | 49211   | 0x23FA | Reserve        | WK230             | R/W     |
| 2292 | 49213   | 0x23FC | SV2 Time       | WK231             | R/W     |
| 2293 | 49215   | 0x23FE | 1st Amount     | WK231             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2294 | 49217   | 0x2400 | 1st Speed      | WK231             | R/W     |
| 2295 | 49219   | 0x2402 | 1st Rev Amount | WK231             | R/W     |
| 2296 | 49221   | 0x2404 | 1st Rev Speed  | WK231             | R/W     |
| 2297 | 49223   | 0x2406 | 2nd Amount     | WK231             | R/W     |
| 2298 | 49225   | 0x2408 | 2nd Speed      | WK231             | R/W     |
| 2299 | 49227   | 0x240A | 2nd Rev Amount | WK231             | R/W     |
| 2300 | 49229   | 0x240C | 2nd Rev Speed  | WK231             | R/W     |
| 2301 | 49231   | 0x240E | 3rd Amount     | WK231             | R/W     |
| 2302 | 49233   | 0x2410 | 3rd Speed      | WK231             | R/W     |
| 2303 | 49235   | 0x2412 | 3rd Rev Amount | WK231             | R/W     |
| 2304 | 49237   | 0x2414 | 3rd Rev Speed  | WK231             | R/W     |
| 2305 | 49239   | 0x2416 | Pre-heat Time  | WK231             | R/W     |
| 2306 | 49241   | 0x2418 | Heating Time   | WK231             | R/W     |
| 2307 | 49243   | 0x241A | Reserve        | WK231             | R/W     |
| 2308 | 49245   | 0x241C | Reserve        | WK231             | R/W     |
| 2309 | 49247   | 0x241E | SV2 Time       | WK232             | R/W     |
| 2310 | 49249   | 0x2420 | 1st Amount     | WK232             | R/W     |
| 2311 | 49251   | 0x2422 | 1st Speed      | WK232             | R/W     |
| 2312 | 49253   | 0x2424 | 1st Rev Amount | WK232             | R/W     |
| 2313 | 49255   | 0x2426 | 1st Rev Speed  | WK232             | R/W     |
| 2314 | 49257   | 0x2428 | 2nd Amount     | WK232             | R/W     |
| 2315 | 49259   | 0x242A | 2nd Speed      | WK232             | R/W     |
| 2316 | 49261   | 0x242C | 2nd Rev Amount | WK232             | R/W     |
| 2317 | 49263   | 0x242E | 2nd Rev Speed  | WK232             | R/W     |
| 2318 | 49265   | 0x2430 | 3rd Amount     | WK232             | R/W     |
| 2319 | 49267   | 0x2432 | 3rd Speed      | WK232             | R/W     |
| 2320 | 49269   | 0x2434 | 3rd Rev Amount | WK232             | R/W     |
| 2321 | 49271   | 0x2436 | 3rd Rev Speed  | WK232             | R/W     |
| 2322 | 49273   | 0x2438 | Pre-heat Time  | WK232             | R/W     |
| 2323 | 49275   | 0x243A | Heating Time   | WK232             | R/W     |
| 2324 | 49277   | 0x243C | Reserve        | WK232             | R/W     |
| 2325 | 49279   | 0x243E | Reserve        | WK232             | R/W     |
| 2326 | 49281   | 0x2440 | SV2 Time       | WK233             | R/W     |
| 2327 | 49283   | 0x2442 | 1st Amount     | WK233             | R/W     |
| 2328 | 49285   | 0x2444 | 1st Speed      | WK233             | R/W     |
| 2329 | 49287   | 0x2446 | 1st Rev Amount | WK233             | R/W     |
| 2330 | 49289   | 0x2448 | 1st Rev Speed  | WK233             | R/W     |
| 2331 | 49291   | 0x244A | 2nd Amount     | WK233             | R/W     |
| 2332 | 49293   | 0x244C | 2nd Speed      | WK233             | R/W     |
| 2333 | 49295   | 0x244E | 2nd Rev Amount | WK233             | R/W     |
| 2334 | 49297   | 0x2450 | 2nd Rev Speed  | WK233             | R/W     |
| 2335 | 49299   | 0x2452 | 3rd Amount     | WK233             | R/W     |
| 2336 | 49301   | 0x2454 | 3rd Speed      | WK233             | R/W     |
| 2337 | 49303   | 0x2456 | 3rd Rev Amount | WK233             | R/W     |
| 2338 | 49305   | 0x2458 | 3rd Rev Speed  | WK233             | R/W     |
| 2339 | 49307   | 0x245A | Pre-heat Time  | WK233             | R/W     |
| 2340 | 49309   | 0x245C | Heating Time   | WK233             | R/W     |
| 2341 | 49311   | 0x245E | Reserve        | WK233             | R/W     |
| 2342 | 49313   | 0x2460 | Reserve        | WK233             | R/W     |
| 2343 | 49315   | 0x2462 | SV2 Time       | WK234             | R/W     |
| 2344 | 49317   | 0x2464 | 1st Amount     | WK234             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2345 | 49319   | 0x2466 | 1st Speed      | WK234             | R/W     |
| 2346 | 49321   | 0x2468 | 1st Rev Amount | WK234             | R/W     |
| 2347 | 49323   | 0x246A | 1st Rev Speed  | WK234             | R/W     |
| 2348 | 49325   | 0x246C | 2nd Amount     | WK234             | R/W     |
| 2349 | 49327   | 0x246E | 2nd Speed      | WK234             | R/W     |
| 2350 | 49329   | 0x2470 | 2nd Rev Amount | WK234             | R/W     |
| 2351 | 49331   | 0x2472 | 2nd Rev Speed  | WK234             | R/W     |
| 2352 | 49333   | 0x2474 | 3rd Amount     | WK234             | R/W     |
| 2353 | 49335   | 0x2476 | 3rd Speed      | WK234             | R/W     |
| 2354 | 49337   | 0x2478 | 3rd Rev Amount | WK234             | R/W     |
| 2355 | 49339   | 0x247A | 3rd Rev Speed  | WK234             | R/W     |
| 2356 | 49341   | 0x247C | Pre-heat Time  | WK234             | R/W     |
| 2357 | 49343   | 0x247E | Heating Time   | WK234             | R/W     |
| 2358 | 49345   | 0x2480 | Reserve        | WK234             | R/W     |
| 2359 | 49347   | 0x2482 | Reserve        | WK234             | R/W     |
| 2360 | 49349   | 0x2484 | SV2 Time       | WK235             | R/W     |
| 2361 | 49351   | 0x2486 | 1st Amount     | WK235             | R/W     |
| 2362 | 49353   | 0x2488 | 1st Speed      | WK235             | R/W     |
| 2363 | 49355   | 0x248A | 1st Rev Amount | WK235             | R/W     |
| 2364 | 49357   | 0x248C | 1st Rev Speed  | WK235             | R/W     |
| 2365 | 49359   | 0x248E | 2nd Amount     | WK235             | R/W     |
| 2366 | 49361   | 0x2490 | 2nd Speed      | WK235             | R/W     |
| 2367 | 49363   | 0x2492 | 2nd Rev Amount | WK235             | R/W     |
| 2368 | 49365   | 0x2494 | 2nd Rev Speed  | WK235             | R/W     |
| 2369 | 49367   | 0x2496 | 3rd Amount     | WK235             | R/W     |
| 2370 | 49369   | 0x2498 | 3rd Speed      | WK235             | R/W     |
| 2371 | 49371   | 0x249A | 3rd Rev Amount | WK235             | R/W     |
| 2372 | 49373   | 0x249C | 3rd Rev Speed  | WK235             | R/W     |
| 2373 | 49375   | 0x249E | Pre-heat Time  | WK235             | R/W     |
| 2374 | 49377   | 0x24A0 | Heating Time   | WK235             | R/W     |
| 2375 | 49379   | 0x24A2 | Reserve        | WK235             | R/W     |
| 2376 | 49381   | 0x24A4 | Reserve        | WK235             | R/W     |
| 2377 | 49383   | 0x24A6 | SV2 Time       | WK236             | R/W     |
| 2378 | 49385   | 0x24A8 | 1st Amount     | WK236             | R/W     |
| 2379 | 49387   | 0x24AA | 1st Speed      | WK236             | R/W     |
| 2380 | 49389   | 0x24AC | 1st Rev Amount | WK236             | R/W     |
| 2381 | 49391   | 0x24AE | 1st Rev Speed  | WK236             | R/W     |
| 2382 | 49393   | 0x24B0 | 2nd Amount     | WK236             | R/W     |
| 2383 | 49395   | 0x24B2 | 2nd Speed      | WK236             | R/W     |
| 2384 | 49397   | 0x24B4 | 2nd Rev Amount | WK236             | R/W     |
| 2385 | 49399   | 0x24B6 | 2nd Rev Speed  | WK236             | R/W     |
| 2386 | 49401   | 0x24B8 | 3rd Amount     | WK236             | R/W     |
| 2387 | 49403   | 0x24BA | 3rd Speed      | WK236             | R/W     |
| 2388 | 49405   | 0x24BC | 3rd Rev Amount | WK236             | R/W     |
| 2389 | 49407   | 0x24BE | 3rd Rev Speed  | WK236             | R/W     |
| 2390 | 49409   | 0x24C0 | Pre-heat Time  | WK236             | R/W     |
| 2391 | 49411   | 0x24C2 | Heating Time   | WK236             | R/W     |
| 2392 | 49413   | 0x24C4 | Reserve        | WK236             | R/W     |
| 2393 | 49415   | 0x24C6 | Reserve        | WK236             | R/W     |
| 2394 | 49417   | 0x24C8 | SV2 Time       | WK237             | R/W     |
| 2395 | 49419   | 0x24CA | 1st Amount     | WK237             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2396 | 49421   | 0x24CC | 1st Speed      | WK237             | R/W     |
| 2397 | 49423   | 0x24CE | 1st Rev Amount | WK237             | R/W     |
| 2398 | 49425   | 0x24D0 | 1st Rev Speed  | WK237             | R/W     |
| 2399 | 49427   | 0x24D2 | 2nd Amount     | WK237             | R/W     |
| 2400 | 49429   | 0x24D4 | 2nd Speed      | WK237             | R/W     |
| 2401 | 49431   | 0x24D6 | 2nd Rev Amount | WK237             | R/W     |
| 2402 | 49433   | 0x24D8 | 2nd Rev Speed  | WK237             | R/W     |
| 2403 | 49435   | 0x24DA | 3rd Amount     | WK237             | R/W     |
| 2404 | 49437   | 0x24DC | 3rd Speed      | WK237             | R/W     |
| 2405 | 49439   | 0x24DE | 3rd Rev Amount | WK237             | R/W     |
| 2406 | 49441   | 0x24E0 | 3rd Rev Speed  | WK237             | R/W     |
| 2407 | 49443   | 0x24E2 | Pre-heat Time  | WK237             | R/W     |
| 2408 | 49445   | 0x24E4 | Heating Time   | WK237             | R/W     |
| 2409 | 49447   | 0x24E6 | Reserve        | WK237             | R/W     |
| 2410 | 49449   | 0x24E8 | Reserve        | WK237             | R/W     |
| 2411 | 49451   | 0x24EA | SV2 Time       | WK238             | R/W     |
| 2412 | 49453   | 0x24EC | 1st Amount     | WK238             | R/W     |
| 2413 | 49455   | 0x24EE | 1st Speed      | WK238             | R/W     |
| 2414 | 49457   | 0x24F0 | 1st Rev Amount | WK238             | R/W     |
| 2415 | 49459   | 0x24F2 | 1st Rev Speed  | WK238             | R/W     |
| 2416 | 49461   | 0x24F4 | 2nd Amount     | WK238             | R/W     |
| 2417 | 49463   | 0x24F6 | 2nd Speed      | WK238             | R/W     |
| 2418 | 49465   | 0x24F8 | 2nd Rev Amount | WK238             | R/W     |
| 2419 | 49467   | 0x24FA | 2nd Rev Speed  | WK238             | R/W     |
| 2420 | 49469   | 0x24FC | 3rd Amount     | WK238             | R/W     |
| 2421 | 49471   | 0x24FE | 3rd Speed      | WK238             | R/W     |
| 2422 | 49473   | 0x2500 | 3rd Rev Amount | WK238             | R/W     |
| 2423 | 49475   | 0x2502 | 3rd Rev Speed  | WK238             | R/W     |
| 2424 | 49477   | 0x2504 | Pre-heat Time  | WK238             | R/W     |
| 2425 | 49479   | 0x2506 | Heating Time   | WK238             | R/W     |
| 2426 | 49481   | 0x2508 | Reserve        | WK238             | R/W     |
| 2427 | 49483   | 0x250A | Reserve        | WK238             | R/W     |
| 2428 | 49485   | 0x250C | SV2 Time       | WK239             | R/W     |
| 2429 | 49487   | 0x250E | 1st Amount     | WK239             | R/W     |
| 2430 | 49489   | 0x2510 | 1st Speed      | WK239             | R/W     |
| 2431 | 49491   | 0x2512 | 1st Rev Amount | WK239             | R/W     |
| 2432 | 49493   | 0x2514 | 1st Rev Speed  | WK239             | R/W     |
| 2433 | 49495   | 0x2516 | 2nd Amount     | WK239             | R/W     |
| 2434 | 49497   | 0x2518 | 2nd Speed      | WK239             | R/W     |
| 2435 | 49499   | 0x251A | 2nd Rev Amount | WK239             | R/W     |
| 2436 | 49501   | 0x251C | 2nd Rev Speed  | WK239             | R/W     |
| 2437 | 49503   | 0x251E | 3rd Amount     | WK239             | R/W     |
| 2438 | 49505   | 0x2520 | 3rd Speed      | WK239             | R/W     |
| 2439 | 49507   | 0x2522 | 3rd Rev Amount | WK239             | R/W     |
| 2440 | 49509   | 0x2524 | 3rd Rev Speed  | WK239             | R/W     |
| 2441 | 49511   | 0x2526 | Pre-heat Time  | WK239             | R/W     |
| 2442 | 49513   | 0x2528 | Heating Time   | WK239             | R/W     |
| 2443 | 49515   | 0x252A | Reserve        | WK239             | R/W     |
| 2444 | 49517   | 0x252C | Reserve        | WK239             | R/W     |
| 2445 | 49519   | 0x252E | SV2 Time       | WK240             | R/W     |
| 2446 | 49521   | 0x2530 | 1st Amount     | WK240             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2447 | 49523   | 0x2532 | 1st Speed      | WK240             | R/W     |
| 2448 | 49525   | 0x2534 | 1st Rev Amount | WK240             | R/W     |
| 2449 | 49527   | 0x2536 | 1st Rev Speed  | WK240             | R/W     |
| 2450 | 49529   | 0x2538 | 2nd Amount     | WK240             | R/W     |
| 2451 | 49531   | 0x253A | 2nd Speed      | WK240             | R/W     |
| 2452 | 49533   | 0x253C | 2nd Rev Amount | WK240             | R/W     |
| 2453 | 49535   | 0x253E | 2nd Rev Speed  | WK240             | R/W     |
| 2454 | 49537   | 0x2540 | 3rd Amount     | WK240             | R/W     |
| 2455 | 49539   | 0x2542 | 3rd Speed      | WK240             | R/W     |
| 2456 | 49541   | 0x2544 | 3rd Rev Amount | WK240             | R/W     |
| 2457 | 49543   | 0x2546 | 3rd Rev Speed  | WK240             | R/W     |
| 2458 | 49545   | 0x2548 | Pre-heat Time  | WK240             | R/W     |
| 2459 | 49547   | 0x254A | Heating Time   | WK240             | R/W     |
| 2460 | 49549   | 0x254C | Reserve        | WK240             | R/W     |
| 2461 | 49551   | 0x254E | Reserve        | WK240             | R/W     |
| 2462 | 49553   | 0x2550 | SV2 Time       | WK241             | R/W     |
| 2463 | 49555   | 0x2552 | 1st Amount     | WK241             | R/W     |
| 2464 | 49557   | 0x2554 | 1st Speed      | WK241             | R/W     |
| 2465 | 49559   | 0x2556 | 1st Rev Amount | WK241             | R/W     |
| 2466 | 49561   | 0x2558 | 1st Rev Speed  | WK241             | R/W     |
| 2467 | 49563   | 0x255A | 2nd Amount     | WK241             | R/W     |
| 2468 | 49565   | 0x255C | 2nd Speed      | WK241             | R/W     |
| 2469 | 49567   | 0x255E | 2nd Rev Amount | WK241             | R/W     |
| 2470 | 49569   | 0x2560 | 2nd Rev Speed  | WK241             | R/W     |
| 2471 | 49571   | 0x2562 | 3rd Amount     | WK241             | R/W     |
| 2472 | 49573   | 0x2564 | 3rd Speed      | WK241             | R/W     |
| 2473 | 49575   | 0x2566 | 3rd Rev Amount | WK241             | R/W     |
| 2474 | 49577   | 0x2568 | 3rd Rev Speed  | WK241             | R/W     |
| 2475 | 49579   | 0x256A | Pre-heat Time  | WK241             | R/W     |
| 2476 | 49581   | 0x256C | Heating Time   | WK241             | R/W     |
| 2477 | 49583   | 0x256E | Reserve        | WK241             | R/W     |
| 2478 | 49585   | 0x2570 | Reserve        | WK241             | R/W     |
| 2479 | 49587   | 0x2572 | SV2 Time       | WK242             | R/W     |
| 2480 | 49589   | 0x2574 | 1st Amount     | WK242             | R/W     |
| 2481 | 49591   | 0x2576 | 1st Speed      | WK242             | R/W     |
| 2482 | 49593   | 0x2578 | 1st Rev Amount | WK242             | R/W     |
| 2483 | 49595   | 0x257A | 1st Rev Speed  | WK242             | R/W     |
| 2484 | 49597   | 0x257C | 2nd Amount     | WK242             | R/W     |
| 2485 | 49599   | 0x257E | 2nd Speed      | WK242             | R/W     |
| 2486 | 49601   | 0x2580 | 2nd Rev Amount | WK242             | R/W     |
| 2487 | 49603   | 0x2582 | 2nd Rev Speed  | WK242             | R/W     |
| 2488 | 49605   | 0x2584 | 3rd Amount     | WK242             | R/W     |
| 2489 | 49607   | 0x2586 | 3rd Speed      | WK242             | R/W     |
| 2490 | 49609   | 0x2588 | 3rd Rev Amount | WK242             | R/W     |
| 2491 | 49611   | 0x258A | 3rd Rev Speed  | WK242             | R/W     |
| 2492 | 49613   | 0x258C | Pre-heat Time  | WK242             | R/W     |
| 2493 | 49615   | 0x258E | Heating Time   | WK242             | R/W     |
| 2494 | 49617   | 0x2590 | Reserve        | WK242             | R/W     |
| 2495 | 49619   | 0x2592 | Reserve        | WK242             | R/W     |
| 2496 | 49621   | 0x2594 | SV2 Time       | WK243             | R/W     |
| 2497 | 49623   | 0x2596 | 1st Amount     | WK243             | R/W     |



| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2498 | 49625   | 0x2598 | 1st Speed      | WK243             | R/W     |
| 2499 | 49627   | 0x259A | 1st Rev Amount | WK243             | R/W     |
| 2500 | 49629   | 0x259C | 1st Rev Speed  | WK243             | R/W     |
| 2501 | 49631   | 0x259E | 2nd Amount     | WK243             | R/W     |
| 2502 | 49633   | 0x25A0 | 2nd Speed      | WK243             | R/W     |
| 2503 | 49635   | 0x25A2 | 2nd Rev Amount | WK243             | R/W     |
| 2504 | 49637   | 0x25A4 | 2nd Rev Speed  | WK243             | R/W     |
| 2505 | 49639   | 0x25A6 | 3rd Amount     | WK243             | R/W     |
| 2506 | 49641   | 0x25A8 | 3rd Speed      | WK243             | R/W     |
| 2507 | 49643   | 0x25AA | 3rd Rev Amount | WK243             | R/W     |
| 2508 | 49645   | 0x25AC | 3rd Rev Speed  | WK243             | R/W     |
| 2509 | 49647   | 0x25AE | Pre-heat Time  | WK243             | R/W     |
| 2510 | 49649   | 0x25B0 | Heating Time   | WK243             | R/W     |
| 2511 | 49651   | 0x25B2 | Reserve        | WK243             | R/W     |
| 2512 | 49653   | 0x25B4 | Reserve        | WK243             | R/W     |
| 2513 | 49655   | 0x25B6 | SV2 Time       | WK244             | R/W     |
| 2514 | 49657   | 0x25B8 | 1st Amount     | WK244             | R/W     |
| 2515 | 49659   | 0x25BA | 1st Speed      | WK244             | R/W     |
| 2516 | 49661   | 0x25BC | 1st Rev Amount | WK244             | R/W     |
| 2517 | 49663   | 0x25BE | 1st Rev Speed  | WK244             | R/W     |
| 2518 | 49665   | 0x25C0 | 2nd Amount     | WK244             | R/W     |
| 2519 | 49667   | 0x25C2 | 2nd Speed      | WK244             | R/W     |
| 2520 | 49669   | 0x25C4 | 2nd Rev Amount | WK244             | R/W     |
| 2521 | 49671   | 0x25C6 | 2nd Rev Speed  | WK244             | R/W     |
| 2522 | 49673   | 0x25C8 | 3rd Amount     | WK244             | R/W     |
| 2523 | 49675   | 0x25CA | 3rd Speed      | WK244             | R/W     |
| 2524 | 49677   | 0x25CC | 3rd Rev Amount | WK244             | R/W     |
| 2525 | 49679   | 0x25CE | 3rd Rev Speed  | WK244             | R/W     |
| 2526 | 49681   | 0x25D0 | Pre-heat Time  | WK244             | R/W     |
| 2527 | 49683   | 0x25D2 | Heating Time   | WK244             | R/W     |
| 2528 | 49685   | 0x25D4 | Reserve        | WK244             | R/W     |
| 2529 | 49687   | 0x25D6 | Reserve        | WK244             | R/W     |
| 2530 | 49689   | 0x25D8 | SV2 Time       | WK245             | R/W     |
| 2531 | 49691   | 0x25DA | 1st Amount     | WK245             | R/W     |
| 2532 | 49693   | 0x25DC | 1st Speed      | WK245             | R/W     |
| 2533 | 49695   | 0x25DE | 1st Rev Amount | WK245             | R/W     |
| 2534 | 49697   | 0x25E0 | 1st Rev Speed  | WK245             | R/W     |
| 2535 | 49699   | 0x25E2 | 2nd Amount     | WK245             | R/W     |
| 2536 | 49701   | 0x25E4 | 2nd Speed      | WK245             | R/W     |
| 2537 | 49703   | 0x25E6 | 2nd Rev Amount | WK245             | R/W     |
| 2538 | 49705   | 0x25E8 | 2nd Rev Speed  | WK245             | R/W     |
| 2539 | 49707   | 0x25EA | 3rd Amount     | WK245             | R/W     |
| 2540 | 49709   | 0x25EC | 3rd Speed      | WK245             | R/W     |
| 2541 | 49711   | 0x25EE | 3rd Rev Amount | WK245             | R/W     |
| 2542 | 49713   | 0x25F0 | 3rd Rev Speed  | WK245             | R/W     |
| 2543 | 49715   | 0x25F2 | Pre-heat Time  | WK245             | R/W     |
| 2544 | 49717   | 0x25F4 | Heating Time   | WK245             | R/W     |
| 2545 | 49719   | 0x25F6 | Reserve        | WK245             | R/W     |
| 2546 | 49721   | 0x25F8 | Reserve        | WK245             | R/W     |
| 2547 | 49723   | 0x25FA | SV2 Time       | WK246             | R/W     |
| 2548 | 49725   | 0x25FC | 1st Amount     | WK246             | R/W     |

| No.  | Address |        | Name           | Reading / Writing | Remarks |
|------|---------|--------|----------------|-------------------|---------|
|      | DEC     | HEX    |                |                   |         |
| 2549 | 49727   | 0x25FE | 1st Speed      | WK246             | R/W     |
| 2550 | 49729   | 0x2600 | 1st Rev Amount | WK246             | R/W     |
| 2551 | 49731   | 0x2602 | 1st Rev Speed  | WK246             | R/W     |
| 2552 | 49733   | 0x2604 | 2nd Amount     | WK246             | R/W     |
| 2553 | 49735   | 0x2606 | 2nd Speed      | WK246             | R/W     |
| 2554 | 49737   | 0x2608 | 2nd Rev Amount | WK246             | R/W     |
| 2555 | 49739   | 0x260A | 2nd Rev Speed  | WK246             | R/W     |
| 2556 | 49741   | 0x260C | 3rd Amount     | WK246             | R/W     |
| 2557 | 49743   | 0x260E | 3rd Speed      | WK246             | R/W     |
| 2558 | 49745   | 0x2610 | 3rd Rev Amount | WK246             | R/W     |
| 2559 | 49747   | 0x2612 | 3rd Rev Speed  | WK246             | R/W     |
| 2560 | 49749   | 0x2614 | Pre-heat Time  | WK246             | R/W     |
| 2561 | 49751   | 0x2616 | Heating Time   | WK246             | R/W     |
| 2562 | 49753   | 0x2618 | Reserve        | WK246             | R/W     |
| 2563 | 49755   | 0x261A | Reserve        | WK246             | R/W     |
| 2564 | 49757   | 0x261C | SV2 Time       | WK247             | R/W     |
| 2565 | 49759   | 0x261E | 1st Amount     | WK247             | R/W     |
| 2566 | 49761   | 0x2620 | 1st Speed      | WK247             | R/W     |
| 2567 | 49763   | 0x2622 | 1st Rev Amount | WK247             | R/W     |
| 2568 | 49765   | 0x2624 | 1st Rev Speed  | WK247             | R/W     |
| 2569 | 49767   | 0x2626 | 2nd Amount     | WK247             | R/W     |
| 2570 | 49769   | 0x2628 | 2nd Speed      | WK247             | R/W     |
| 2571 | 49771   | 0x262A | 2nd Rev Amount | WK247             | R/W     |
| 2572 | 49773   | 0x262C | 2nd Rev Speed  | WK247             | R/W     |
| 2573 | 49775   | 0x262E | 3rd Amount     | WK247             | R/W     |
| 2574 | 49777   | 0x2630 | 3rd Speed      | WK247             | R/W     |
| 2575 | 49779   | 0x2632 | 3rd Rev Amount | WK247             | R/W     |
| 2576 | 49781   | 0x2634 | 3rd Rev Speed  | WK247             | R/W     |
| 2577 | 49783   | 0x2636 | Pre-heat Time  | WK247             | R/W     |
| 2578 | 49785   | 0x2638 | Heating Time   | WK247             | R/W     |
| 2579 | 49787   | 0x263A | Reserve        | WK247             | R/W     |
| 2580 | 49789   | 0x263C | Reserve        | WK247             | R/W     |
| 2581 | 49791   | 0x263E | SV2 Time       | WK248             | R/W     |
| 2582 | 49793   | 0x2640 | 1st Amount     | WK248             | R/W     |
| 2583 | 49795   | 0x2642 | 1st Speed      | WK248             | R/W     |
| 2584 | 49797   | 0x2644 | 1st Rev Amount | WK248             | R/W     |
| 2585 | 49799   | 0x2646 | 1st Rev Speed  | WK248             | R/W     |
| 2586 | 49801   | 0x2648 | 2nd Amount     | WK248             | R/W     |
| 2587 | 49803   | 0x264A | 2nd Speed      | WK248             | R/W     |
| 2588 | 49805   | 0x264C | 2nd Rev Amount | WK248             | R/W     |
| 2589 | 49807   | 0x264E | 2nd Rev Speed  | WK248             | R/W     |
| 2590 | 49809   | 0x2650 | 3rd Amount     | WK248             | R/W     |
| 2591 | 49811   | 0x2652 | 3rd Speed      | WK248             | R/W     |
| 2592 | 49813   | 0x2654 | 3rd Rev Amount | WK248             | R/W     |
| 2593 | 49815   | 0x2656 | 3rd Rev Speed  | WK248             | R/W     |
| 2594 | 49817   | 0x2658 | Pre-heat Time  | WK248             | R/W     |
| 2595 | 49819   | 0x265A | Heating Time   | WK248             | R/W     |
| 2596 | 49821   | 0x265C | Reserve        | WK248             | R/W     |
| 2597 | 49823   | 0x265E | Reserve        | WK248             | R/W     |
| 2598 | 49825   | 0x2660 | SV2 Time       | WK249             | R/W     |





**Apollo Seiko Ltd.**  
2271-7 Jinba, Gotenba-shi,  
Shizuoka, Japan 〒412-0047

TEL: +81-(0)550-88-2828  
FAX: +81-(0)550-88-2830  
E-mail: [sales@apolloseiko.co.jp](mailto:sales@apolloseiko.co.jp)  
URL: <https://www.apolloseiko.co.jp>